

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [39523-3418](#)  
**Status:** **Active**  
**Overview:** [Eurostyle™ Terminal Blocks](#)  
**Description:** 5.00mm Pitch Eurostyle™ Vertical Plug, with Reverse Imprinting, Rear Wire Entry, 18 Circuits

**Documents:**  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-39500-001 \(PDF\)](#)

| General        |                                            |
|----------------|--------------------------------------------|
| Product Family | Terminal Blocks                            |
| Series         | <a href="#">39523</a>                      |
| Application    | N/A                                        |
| Comments       | Rear Wire Entry with Reverse Imprinting    |
| Component Type | Plug                                       |
| Overview       | <a href="#">Eurostyle™ Terminal Blocks</a> |
| Product Name   | ESE, Eurostyle™Pluggable                   |
| Type           | Euro Block                                 |
| UPC            | 822350470834                               |

| Physical                      |                                |
|-------------------------------|--------------------------------|
| Circuits (Loaded)             | 18                             |
| Entry Angle                   | Horizontal                     |
| Lock to Mating Part           | Yes                            |
| Number of Rows                | 1                              |
| Orientation                   | Vertical                       |
| Panel Mount                   | No                             |
| Pitch - Mating Interface      | 5.00mm                         |
| Pitch - Termination Interface | 5.00mm                         |
| Polarized to Mating Part      | Yes                            |
| Stackable                     | No                             |
| Temperature Range - Operating | -40°C to +105°C                |
| Wire Size AWG                 | 12, 14, 16, 18, 20, 22, 24, 26 |
| Wire Size mm²                 | 0.13 - 3.31                    |

| Electrical                    |      |
|-------------------------------|------|
| Current - Maximum per Contact | 18A  |
| Voltage - Maximum             | 300V |

Material Info

| Reference - Drawing Numbers |              |
|-----------------------------|--------------|
| Product Specification       | PS-39500-001 |
| Sales Drawing               | SD-39523-001 |




image - Reference only

Series

**EU RoHS**  
**ELV and RoHS**  
**Compliant**  
**REACH SVHC**  
Not Reviewed  
**Low-Halogen Status**  
**Not Reviewed**



**Need more information on product environmental compliance?**  
  
Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)  
  
Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
[39523Series](#)

**Mates With**  
[39521](#) Vertical PCB Header, [39522](#) Horizontal PCB Header, Most 5.00mm Pitch Industry Standard PCB Headers, [39528](#) Dual Level PCB Header, Open Ends