

Item # GEM-V3, Gem-V Foot Switch



Gem-V Foot Switch

GEM-V foot switch model feature a round black actuating cap in a chrome plated heavy die cast housing with a full nonskid base pad. Moderate pressure from any direction operates the switch. Standard models supplied with cordset are wired normally open and grounded.

SPECIFICATIONS

Description	Momentary
Circuit	SPST Wired N.O.
Form	A
Electrical Rating	1/2 H.P. 125 VAC 10 A 125 VAC
Standard	EN 60529 Degree of Protection IP20
Size	3 13/16 x 1 7/32 Inch
Weight Approx.	1 lbs
Note	Supplied with 6 ft. 18/3 cord and 3 prong series plug. Green lead grounded.
