

4

3


2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
G	14		G	REV PER 0G3A-0636-04	13AUG04	JR TM

AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
16-14HD AWG SOLID OR STRANDED	16-14HD AWG SOLID OR STRANDED	16-14HD AWG SOLID OR STRANDED



- ① STAMP AMP 16-14HD* APPROX AS SHOWN
2 WIRE INSULATION DIA: .150-.250
3 TONGUE MATERIAL THK: 1.22^{±0.05} [.048^{±.002}]
④ MATERIAL: BODY - CU PER ASTM B152
SLEEVE - PVC,
COLOR - YELLOW W/BLK STRIPE

2500	ON TAPE, REEL	2-321518-1
-	LOOSE PIECE	321518
QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 09/29/92		Tyco Electronics Corporation	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS			VOLTAGE RATING: N/A		DIMENSIONS: INCHES		CHK RE HERSEY 11/10/92		Tyco Electronics Corporation	
PRODUCT INFORMATION CENTER 1-800-522-6752			CIRCULAR MIL AREA: 1.04-2.62mm ² [2,050-5,180] SOLID OR STRANDED		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. BARNABA 11/10/92		Harrisburg, Pa 17105-3608	
FOR APPLICATION TOOLING ASSISTANCE CENTER					0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 [.008] 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-1034		NAME TERMINAL, RING TONGUE, PLASTI-GRIP	
TOOLING INFORMATION 1-800-722-1111					MATERIAL - ④		APPLICATION SPEC NOT AVAILABLE		SIZE A3	
FOR ORDER ENTRY 1-800-526-5142					FINISH TIN PER ASTM B545		WEIGHT -		CAGE CODE 00779	
							CUSTOMER DRAWING		DRAWING NO C-321518	
									RESTRICTED TO -	
									SCALE 4:1	
									SHEET 1 OF 1	
									REV G	