

Liquidtight Flexible Non-Metallic Conduit & Fittings

T&B Catalog Number:

UPC Number:

LT43F-NEW

Status:

03448119418

Description:

Active



1 inch liquidtight non-metallic fitting.

Features

Non-conductive and non-corrosive.

Resistant to oil, acid, ozone and alkaline.

Easy to install.

Approved for indoor and outdoor locations

UL listed for wet locations

Nitrile rubber 'O' ring for a liquidtight termination.

Temperatures up to 225 degree F (107 degree C)

Meets UL standard 514B.

Application

For use with Carflex conduit and Carflex X-Flex conduit.

General

Trade Size (inches)

1

Material

Non-Metallic

Dimension Information

Size (inches)

1

Degree of Bend

Straight

A (inches)

0.7

B (inches)

1

C (inches)

2.2

D (inches)

1.9

E (inches)

1.71

Packaging

T&B Order Multiple

25

Package in Units

25

T&B Sold in UOM

Each

T&B Weight Per UOM

0.19 lbs. Each

Application Support

T&B Sales Drawings

wsd-ac04398

Product Overview-Carflex Liquidtight Flex-Available on Website

ible Tubing

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E 32447

For further technical assistance, please contact us...

8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com