


Crimphousing 2,54 mm

Series

430



Rated current	3,0 A
Rated voltage	250 VRMS / VDC
Please consider air- and creepage distances	
Withstand voltage	600 VRMS for 1 minute
Material contact	Copper alloy
Material insulator	Thermoplast UL94V-0
Operating temperature	-25°C to +105°C

pitch
2,54

mating pin
size
□ 0,64

max.
pincount
024

All dimensions in mm.



Variation

Contact



Series

607

AWG 22 - 26



1




Plating contact



Packaging (L,R)

Plating:
T = Sn

Packaging:
L = Bulk
R = Reel



2




3

607-1-TX-X

Crimp Tool

454



454-1-04

* No. of contacts:

Variation 1 = 002 - 012

Variation 2 = 004 - 024

Variation 3 = 004 - 024

Variation (1,2,3)

No. of contacts *
(002,... - 024)



www.mpe-connector.de

Order code:

430-?-?-?-X-KS0

Mating series	087	090	088	334	368	093
see page	3-37	3-39	3-41	3-42	3-43	3-47