



MICRO SWITCH

FED. MFR. CODE 91929

SWITCH-ENCLOSED

CATALOG LISTING

12HR34-1B



NOTES

- 1 SWITCH SEALED PER MIL-S-8805 SYMBOL 5 SWITCH CHAMBER. WATERTIGHT TEST NOT APPLICABLE
- 2 ALL EXPOSED PARTS ARE CORROSION RESISTANT
- 3 CIRCUIT DIAGRAM PERMANENTLY MARKED ON SWITCH HOUSING
- 4 LEAD IDENTIFICATION IS SHOWN ON CIRCUIT DIAGRAM
- 5 SWITCH WILL OPERATE SATISFACTORILY IN TEMPERATURES FROM -85°F TO +599°F
- 6 HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ———— 6-12 LB	CONTACT ARRANGEMENT S P N C	DO NOT SCALE PRINT
FULL OVERTRAVEL FORCE ——— 35 LB MAX	28 VOLTS DC (EACH CIRCUIT)	UNLESS OTHERWISE SPECIFIED
RELEASE FORCE ———— 5 LB MIN	RESISTIVE ———— ———— 5 AMP	DIMENSIONS ARE IN INCHES
PRETRAVEL ———— .050 MAX	INDUCTIVE ———— ———— 2 AMP	TOLERANCES ARE:
DIFFERENTIAL TRAVEL ——— .015 MAX		ONE PLACE (.01) ± .030
OVERTRAVEL ———— .250 MIN		TWO PLACE (.001) ± .015
		THREE PLACE (.000) ± .005
		ANGLES 2
		WEIGHT 6.0Z MAX

12HR34-1B

M

DRAWING NUMBER

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

X8

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[12HR34-1B](#)