

4


3

2

1

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.		ALL RIGHTS RESERVED.	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CE	16		S	REVISED PER ECR-05-15129	08NOV05	JWD	JD



1. DIMENSIONS IN [] ARE IN INCHES.
2. MAX INSERTION LOSS IS 0.4 dB PLUS CABLE ATTENUATION OF 0.7 dB/km AT 1300nm (SEE TABLE).
3. 55 dB MIN RETURN LOSS.

	0.41	12.19±0.15 [480.0±6.0]	3-492015-2
	0.40	1.37±0.05 [53.9±2.0]	3-492015-1
	0.40	0.46±0.03 [18.1±1.0]	3-492015-0
	0.47	100.0±1.00 [3937±39]	2-492015-9
OBSOLETE	0.46	90.0±0.90 [3543±35]	2-492015-8
OBSOLETE	0.46	80.0±0.80 [3150±31]	2-492015-7
OBSOLETE	0.45	70.0±0.70 [2756±28]	2-492015-6
	0.44	60.0±0.60 [2362±24]	2-492015-5
OBSOLETE	0.44	50.0±0.50 [1969±20]	2-492015-4
OBSOLETE	0.43	45.0±0.45 [1772±18]	2-492015-3
	0.43	40.0±0.40 [1575±16]	2-492015-2
	0.42	30.0±0.30 [1181±12]	2-492015-1
	0.42	35.0±0.35 [1378±14]	2-492015-0
	0.40	4.0±0.08 [157.5±3.0]	1-492015-9
OBSOLETE	0.40	0.56±0.03 [22±1]	1-492015-8
OBSOLETE	0.40	0.36±0.03 [14±1]	1-492015-7
	0.42	25±0.30 [984±12]	1-492015-6
	0.41	9±0.15 [354±6]	1-492015-4
	0.41	8±0.15 [315±6]	1-492015-3
	0.40	6±0.08 [236±3]	1-492015-2
	0.40	1.50±0.05 [59.1±2]	1-492015-1
	0.40	0.75±0.03 [29.6±1]	1-492015-0
	0.40	0.3+0.05/-0.0 [12+2/-0]	492015-9
	0.40	7±0.08 [276±3]	492015-8
	0.41	20±0.3 [787±12]	492015-7
	0.41	15±0.15 [591±6]	492015-6
	0.41	10±0.15 [394±6]	492015-5
	0.40	5±0.08 [197±3]	492015-4
	0.40	3±0.05 [118±2]	492015-3
	0.40	2±0.05 [79±2]	492015-2
	0.40	1±0.05 [39±2]	492015-1
	MAX IL (dB)		PART NUMBER
	L METERS [INCHES]		

D

C

B

A

D

C

492015

B

A