

MODULAR JACKS AND PLUGS: GAX Series

Right Angle Ganged Jack

Product Features

Available in 6 and 8 Position Housings
Right Angle Version
Ribbed Pin Guides
Metal Locking Brackets
CSA/NRTL Certified File No. LR78160

Performance Specifications

Materials and Finish

Housing Material

PBT Thermoplastic, UL 94V-0 Rated, Color: Gray

Metal Peg:

Phosphor Bronze, Tin Plated

Contact Material

Phosphor Bronze

Contact Plating Options

Standard

0.0001" Nickel Underplating, Gold Flash Plated overall

50

0.0001" Nickel Underplating, 0.000050" Gold Plated overall to Comply with FCC Requirements Under No. 47 C.F.R. Part 68, Subpart F

Electrical Characteristics

Current Rating

1.5A

Voltage Rating

125V DC

Insulation Resistance

500 Megohms Min.

Dielectric Withstanding Voltage

1000V AC RMS for 1 Minute

Contact Resistance

20 milliohms Max.

2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

Generated Part Number

Part Number Builder

	-			
Series		No. of Ports	No. of Positions	Plating Option

Series

GAX - Right Angle PCB Mount

Number of Ports

2 - 2 Port

3 - 3 Port

4 - 4 Port

5 - 5 Port (Available Only With 6 Positions)

6 - 6 Port (Available Only With 6 Positions)

7 - 7 Port (Available Only With 6 Positions)

8 - 8 Port (Available Only With 6 Positions)

Number of Positions / Contacts

62 - 6 Positions / 2 Contacts

64 - 6 Positions / 4 Contacts

66 - 6 Positions / 6 Contacts

88 - 8 Positions / 8 Contacts

Plating Option


Blank - Gold Flash

50 - 50µ" Gold Plating

Contact Kycon for Other Options

GAX Series

Dimensions in mm



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kycon:

[GAX-8-66-50](#) [GAX-7-66-50](#) [GAX-3-66-50](#) [GAX-5-66-50](#) [GAX-4-66-50](#) [GAX-6-66-50](#) [GAX-2-66-50](#) [GAX-7-62-50](#)
[GAX-7-62](#) [GAX-7-66](#) [GAX-7-64](#) [GAX-6-64](#) [GAX-6-66](#) [GAX-8-64](#) [GAX-8-62](#) [GAX-8-66](#) [GAX-8-64-50](#) [GAX-5-64](#)
[GAX-5-66](#) [GAX-8-62-50](#) [GAX-2-64-50](#) [GAX-6-64-50](#) [GAX-4-64-50](#) [GAX-7-64-50](#) [GAX-3-64-50](#) [GAX-5-64-50](#) [GAX-](#)
[3-88-50](#) [GAX-4-88-50](#) [GAX-2-88-50](#) [GAX-3-88](#) [GAX-3-66](#) [GAX-3-64](#) [GAX-2-88](#) [GAX-2-64](#) [GAX-2-66](#) [GAX-8-62-](#)
[50-BLK](#) [GAX-4-88](#) [GAX-4-62](#) [GAX-4-66](#) [GAX-4-64](#) [GAX-2-62](#) [GAX-2-62-50](#) [GAX-2-62-50-BLK](#) [GAX-2-64-50-BLK](#)
[GAX-2-66-50-BLK](#) [GAX-3-62](#) [GAX-3-62-50](#) [GAX-4-62-50](#) [GAX-4-62-50-BLK](#) [GAX-4-62-BLK](#) [GAX-4-88K](#) [GAX-5-62](#)
[GAX-5-62-50](#) [GAX-6-62](#) [GAX-6-62-50](#) [GAX-2-62-BLK](#) [GAX-4-64-BLK](#) [GAX-8-62-BLK](#)