


ADSL LINE TRANSFORMERS

For Texas Instruments' CPE Chipsets



- Matched to Texas Instruments' AP5, AR5 and AU5 chipsets
- Excellent THD performance in a small footprint
- Designed to meet UL1950 and EN60950 supplementary insulation requirements for working voltages up to 250 Vrms

Electrical Specifications @ 25°C — Operating Temperature -40°C to +85°C

Part Number	Mounting	Turns Ratio (1-4):(10-7) (± 2%)	DC Resistance (Ω)		Leakage Inductance @ 100 kHz, 0.1 Vrms MAX (1-4) with (7-10) shorted	Inductance @ 100 kHz, 1 V (1-4)
			(1-4)	(10-7)		
BX2361	THT	2:1	≤ 2.00	≤ 0.55	15 μH	1.5 mH ±5%
BX2382 ¹	SMT	2:1	≤ 2.00	≤ 0.55	15 μH	1.5 mH ±5%


Additional Specifications

Part Number	THD (@ 100 kHz, 5.3 Vrms)	Load Resistance (Ω)	Isolation Voltage (Vrms)	Longitudinal Balance (from 30 kHz to 1.1 MHz)
BX2361	≤ -80 dB	100	1500	≤ -60 dB
BX2382 ¹	≤ -80 dB	100	1500	≤ -60 dB

¹ Transformers are shipped in trays, unless Tape & Reel packaging is specified by adding the suffix "T" to this part number (BX2382T).


Mechanicals

BX2361



Weight 6.2 grams
Tray65/tray

BX2382



Weight 6.2 grams
Tray60/tray

Schematic



Dimensions: ^{Inches}
mm Unless otherwise specified, all tolerances are ± .010
0.25

For More Information :

UNITED STATES (Worldwide)

12220 World Trade Drive
San Diego, CA 92128
U.S.A.
http://www.pulseeng.com
TEL: 858 674 8100
FAX: 858 674 8262

UNITED KINGDOM (Northern Europe)

1 & 2 Huxley Road
The Surrey Research Park
Guildford, Surrey GU2 5RE
United Kingdom
TEL: 44 1483 401700
FAX: 44 1483 401701

FRANCE (Southern Europe)

Zone Industrielle
F-39270
Orgelet
France
TEL: 33 3 84 35 04 04
FAX: 33 3 84 25 46 41

SINGAPORE (Southern Asia)

150 Kampong Ampat
#07-01/02
KA Centre
Singapore 368324
TEL: 65 287 8998
FAX: 65 280 0080

TAIWAN, R.O.C. (Northern Asia)

3F-4, No. 81, Sec. 1
HsinTai Wu Road
Hsi-Chih, Taipei Hsien
Taiwan, R.O.C.
Tel: 886 2 2698 0228
FAX: 886 2 2698 0948

HONG KONG (China/Hong Kong)

19/F, China United Plaza
1008 Tai Nan West Street
Cheung Sha Wan, Kowloon
Hong Kong, China
TEL: 852 2788 6588
FAX: 852 2776 1055

DISTRIBUTOR

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.