


Abbr.	TOLERANCE	
	P=0.5	P=1.0
P	±0.05	±0.08
Pt	±0.08	±0.10
W	±0.08	±0.10
M	±0.08	±0.12
Cw	±0.02	±0.03
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm	

RoHS Compliant	
I	05-AUG-15
H	21-JAN-13
REV	DATE



DIMENSION & TOLERANCE
W= (N+1) x P
Pt=(N-1) x P

PROJECTION: 	GENERAL TOLERANCE $.X = +/_{0.2}$ $.XX = +/_{0.15}$		
APPROVAL: GMo	UNIT: MM SCALE: SHEET: 1/2 DRAW: CH	DESCRIPTION: 1.00MM FLAT FLEXIBLE CABLE TYPE 1 XX NB OF PIN: XXXX / LLL OVERALL LENGTH: XXXXXX MM WERI PART NO: 686 XXXX 001 XX LLL	SIZE A4

