




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		E	REVISED PER ECR-13-004343	30JUL13	KH	KR

- 1 FITS 0.81±0.025 X 4.75 [.032±.001 X .187] TAB
- 2 WIRE SIZE: 1.3–2.0mm² [16–14 AWG], STRANDED ONLY.
 ONE WIRE STRIP LENGTH 7.94 [.312]
 TWO WIRE STRIP LENGTH 8.51 [.335]
- 3 INSULATION SIZE: 6.60 [.260] MAX DIA.
- 4 CONTINUOUS STRIP.
- 6 PRELIMINARY – NOT FOR PRODUCTION



TYPE 6/6 NYLON	BLACK	BRASS	TIN PLATE	69-521247-2
TYPE 6/6 NYLON	BLUE TRANSLUCENT	BRASS	TIN PLATE	3-521247-2
MATERIAL	COLOR	MATERIAL	FINISH	PART NUMBER
HOUSING		TERMINAL		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH	16DEC99	 TE Connectivity			
		CHK MS FEHER	16DEC99				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD J HUMMEL	16DEC99	NAME RECEPTACLE, ASSEMBLY, FLAG, ULTRA-FAST, .187 SERIES			
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC 108-2043					
		APPLICATION SPEC 114-2123					
MATERIAL	FINISH	WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=521247	RESTRICTED TO -	
SEE TABLE	SEE TABLE	CUSTOMER DRAWING			SCALE 8:1	SHEET 1 of 1	REV E