

TK-type Twin Wheel Caster




Characteristic

Caster with cover, drivability, stability, and smooth turning are excellent.

Application

Lighter devices / TV tables



caster with stopper
(applicable for
both truck and bolt types)

Bolt Type Specification

Model No.	A	D	E	d	H2	K	L	W	Allowable Load (kg)	Code No.	
TK30N6	29	φ30	11	M6×1.0	39	10	14	33	20	19034	
TK40N8	39.5	φ42	14	M8×1.25	55	14	15	39	30	19037	
TK40N8S	47									19050	
TK40N10	39.5			M10×1.5						19038	
TK40N10S	47									19051	
TK40N2.5	39.5			W5/16x-18						19039	
TK40N2.5S	47									19052	
TK40N3	39.5									W3/8x-16	19040
TK40N3S	47			19053							
TK50N8	51.5			φ52							21
TK50N8S	59	M10×1.5	19055								
TK50N10	51.5		M12×1.25		19	19043					
TK50N10S	59	W5/16x-18				19056					
TK50N12	51.5		W3/8x-16			14	19044				
TK50N12S	59				19057						
TK50N2.5	51.5	19045									
TK50N2.5S	59	19058									
TK50N3	51.5	19046									
TK50N3S	59	19059									

※N shows the screw type on the model No. Caster with stopper has S at the end of the model No.


Truck Type Specification

Model No.	A	D	E	G	H1	L1	L2	P1	P2	W	Allowable Load (kg)	Code No.		
TK30	29	φ30	11	φ5	42.5	28	28	18	18	33	20	19031		
TK40	39.5	φ42	14		58.5	38	38	26	26	40.5	30	19032		
TK40S	47				68.5							19047		
TK50	52.5	φ52	21		68.5					47	40	19033		
TK50S	59				19048									

※Caster with stopper has S at the end of the model No.

Model No.	Material	
	Body	Wheel
TK-Type	PA	PA

Bolt type



Truck type

