

Home

Events

Careers

How To Buy

Contact

Products

Industries

Resources

News

About Us

▶ Cable Ties

▼ Cable Ties with Fasteners

▶ Arrowhead Push Mount Ties

▶ Button Head Cable Ties

▶ Edge Clip Cable Ties

▶ Fir Tree Mount Cable Ties

▶ Screw Mount Cable Ties

▶ Stud Mount Cable Ties

▶ Cable Tie Tools

▶ Clamps and Clips

▶ Heatshrink Moulded Shapes

▶ Mounts

▶ Heavy Duty Mounts

▶ Wire Connectors

▶ Wiring Duct

▶ Wiring Protection

▶ Labels, Printers and Software

▶ Pre-Terminated Networking

▶ Copper Network Solutions

▶ Fiber Network Solutions

▶ Jacks and Wall Plates

▶ Racks - Cable Management

▶ Surface Raceway Systems

156-00555

Cable Tie and Edge Clip, 50lb, 8.0" Long, EC20, Panel Thickness .12"-.24", PA66HS, Black, 500/bag

Article Number: 156-00555

Part Number: 156-00555

Type: T50REC20

➔ Base Data

Part No.	156-00555
Type	T50REC20
Color	Black (BK)
Features	• Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole. • Edge Clip provides low insertion force and high extraction force ideal for assembly environments. • Two piece assembly allows the mount to slide along the strap ensuring proper orientation.
Application Method	Cable tie and edge clip assemblies are primarily applied around a bundle by hand and tensioned using one of HellermannTyton's manual or pneumatic hand tools. The bundle is then secured to the mounting surface by inserting the clip onto the appropriate edge.
Identification Plate Position	none
Typical Application	This cable tie and edge clip assembly is ideal for use where holes are not acceptable or where adhesives will fail due to temperature problems. Edge clips are widely used for fixing and bundling cables and wires within automotive, trucking, heavy equipment, solar panel, wind power, and white goods equipment manufacturing.
Variant	Inside Serrated

➔ Product Dimensions

Min. Tensile Strength	50.0lbs / 225N
Length (L)	8.0" / 200.0mm
Length (L2)	0.58" / 14.8mm
Width (W) (imperial)	0.18"
Width (W)	4.6mm
Width (W2)	0.55" / 14.0mm
Height (H)	0.05" / 1.2mm
Height (H2)	0.7" / 17.8mm
Min. Ø Bundle	0.06" / 1.0mm
Max. Ø Bundle	2.0" / 45.0mm
Max. Panel Thickness	0.24" / 6.00mm
Min. Panel Thickness	0.12" / 3.00mm

➔ Material and Specifications

Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS) / Polyamide 6.6 heat stabilized (PA66HS)
----------	--

➔ Find a Distributor

➔ Order Samples

➔ Get Technical Drawings

Share

http://www.hellermannntyton.us/productDetail.aspx?lon=156-00555&ref=search.aspx[11/11/2013 2:30:14 PM]

Material Specification	RoHS
------------------------	------

 Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	500
Carton Qty.	4000
EAN code	4031026326856
UPC	089306313281

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)