




D Series

High Voltage relays 10kV & 15kV



- **10kV or 15kV Isolation**
- **Low Contact Resistance**
- **PCB or Panel Mount**
- **HV connections via Flying Leads, Solder Turret (wire wrap), or 1/4" Spade Terminals**
- **Excellent AC characteristics**

Very high isolation voltages, up to 15kV, are achieved through the use of high vacuum reed switches with either Rhodium or Tungsten contacts and make these relays suitable for high reliability applications, such as cardiac defibrillators, test equipment and high voltage power supplies.

The Rhodium contact relays have low contact resistance, while the Tungsten contact relays can switch higher voltages.

PCB or Panel Mount, via Nylon studs, versions are available.

Connection options, for the HV, include PCB, solder turret(wire wrap), flying lead and 0.25" spade terminals.

Contact Specification	Unit Condition	10kV SPNO			10kV SPNC			15kV SPNO		
Contact Material		Rhodium	Tungsten		Rhodium	Tungsten		Tungsten		
Isolation across contacts kV	DC or AC peak	10	10		10	10		15		
Switching Power Max.	W	50	50		50	50		50		
Switching Voltage Max.	V DC or AC peak	1000	7000		1000	7000		10000		
Switching Current Max.	A DC or AC peak	3	2		3	2		2		
Carry Current Max	A DC or AC peak	4	3		4	3		2		
Capacitance across contacts	pF coil to screen grounded	<0.2	<0.2		<0.2	<0.2		<0.2		
Lifetime operations	dry switching	10 ⁹	10 ⁹		10 ⁹	10 ⁹		10 ⁹		
	50W switching	10 ⁶	10 ⁶		10 ⁶	10 ⁶		10 ⁶		
Contact Resistance	m max (typical)	50 (15)	250(100)		50 (15)	250(100)		250 (100)		
Insulation Resistance	min (typical)	10 ¹⁰ (10 ¹³)			10 ¹⁰ (10 ¹³)			10 ¹⁰ (10 ¹³)		
Coil Specification		5V	12V	24V	5V	12V	24V	5V	12V	24V
Must Operate Voltage	V DC	3.7	9	20	3.7	9	20	3.7	9	20
Must Release Voltage	V DC	0.5	1.25	4	0.5	1.25	4	0.5	1.25	4
Operate Time	ms diode fitted	3.0	3.0	3.0	2.0	2.0	2.0	3.0	3.0	3.0
Release Time	ms diode fitted	2.0	2.0	2.0	3.0	3.0	3.0	2.0	2.0	2.0
Resistance		28	150	780	38	240	925	16	95	350
Relay Specification										
Isolation contact/coil	kV	17			17			17		
Insulation resistance contact to all terminals	min (typical)	10 ¹⁰ (10 ¹³)			10 ¹⁰ (10 ¹³)			10 ¹⁰ (10 ¹³)		
Environmental Operating Temp range	°C	-20 to +70			-20 to +70			-20 to +70		

Part Numbering System

	D	A	T	7	12	10	F
Reed Switch Size							
Contact Form A=n/o, B=n/c							
Contact Material R=Rhodium, T=Tungsten							
Moulding Ref. No.							
Coil Voltage 05=5Vdc, 12=12Vdc, 24=24Vdc							
Isolation between Contacts 3=3kV, 5=5kV, 10=10kV, 15=15kV							
Mounting or Connection Style No suffix indicates PCB mount F=PCB mount & coil connection with Flying lead HV connection P=Panel mount with wire wrap terminals S=PCB mount & coil connection with stud fixing & 1/4" spade HV connection (not available on 15kV models) T=PCB mount & coil connection with stud fixing & wire wrap HV connection							

Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE
Telephone +44 (0) 1202 897969

Email:sales@cynergy3.com

ISO9001 CERTIFIED

www.cynergy3.com

