

## Broadband Solutions

CX3799681 | 200B110 RIB WP1100TAPE COEX

ConQuest® Empty Conduit, 2 in, SDR 11, ribbed, black, with pull tape



## Dimensions

Nominal Size	2 in
Wall Thickness Designation	SDR 11
Inner Diameter, nominal	48.692 mm   1.917 in
Length	762.00 m   2500.00 ft
Outer Diameter, nominal	60.325 mm   2.375 in
Wall Thickness, minimum	5.486 mm   0.216 in
Weight	640.0 lb/kft

## General Specifications

Color	Black
Conduit Type	Non-toneable
Wall Type	Ribbed
Brand	ConQuest®
Warranty	One year

## Material Specifications

Density Test Method	ASTM D792A
Density, maximum	0.955 g/cm <sup>3</sup>
Density, minimum	0.941 g/cm <sup>3</sup>
Design Standard	ASTM D3350-05
Environmental Stress Crack Resistance	Failure rate of 10% within 96 hours
Environmental Stress Test Method	ASTM D1693, ESCR Condition B
Flexural Modulus, minimum	552 N/mm <sup>2</sup>   80000 psi
Flexural Property Test Method	ASTM D790
Hydrostatic Design Basis	Not pressure rated
Hydrostatic Design Test Method	ASTM D2837
Material Type	High density polyethylene (HDPE)
Melt Flow Rate Test Method	ASTM D1238
Melt Flow Rate, maximum	0.39 g/10 min
Tensile Property Test Method	ASTM D638
Tensile Strength at yield, minimum	21 N/mm <sup>2</sup>   3000 psi

## Mechanical Specifications

Minimum Bend Radius, unsupported	660.4 mm   26.0 in
----------------------------------	--------------------

CX3799681 | 200B110 RIB WP1100TAPE COEX

Pulling Tension, maximum 1408.4 kg | 3105.0 lb

## Pull Line Specifications

---

Breaking Strength 499.0 kg | 1100.0 lb  
Material Type Polyester  
Pull Line Type Tape

## Regulatory Compliance/Certifications

---

Agency	Classification
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

### \* Footnotes

---

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance