


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A	B	C	D	E	F	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	RECM. FASTENER	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)											
BC1M-S4	.06 (1.5)	0.90 (23)	.046 (1.2)	.095 (2.4)	.122 (3.1)	.156 (4.0)	.234 (5.9)	4.6 (117)	18 (80)	MINIATURE	CURVED	#4 (M2.5) SCREW	.08 (36)
BC2M-S4	.06 (1.5)	2.00 (51)	.046 (1.2)	.095 (2.4)	.122 (3.1)	.156 (4.0)	.234 (5.9)	8.3 (211)	18 (80)	MINIATURE	CURVED	#4 (M2.5) SCREW	.14 (64)
BC1.5I-S8	.03 (0.8)	1.5 (38)	.041 (1.0)	.141 (3.6)	.174 (4.4)	.166 (4.2)	.330 (8.4)	6.6 (168)	40 (178)	INTERMEDIATE	CURVED	#8 (M4) SCREW	.16 (73)

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

DOME-TOP Barb Ty LOCKING
CLAMP TIE-BC SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± --- (.XXX) ± .020(.5)
(.XX) ± .02(.5) ANGLES ± ---

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
FKS

MAT'L:

SCALE

NONE

DATE
7-19-96

NYLON 6.6

DRAWING NO.

BT-0070

DWG
A
SIZE

SHEET 1 OF 2

7	5/31/05	ERW		CHANGED 'C' DIMENSION FROM TOLERANCE TO NOMINAL HOLE DIAMETER	0070	7							
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP					