


AMP WIRE RANGE	UL Listed FILE E13288	SR LR7189 Certified
2 AWG SOLID OR STRANDED	2 AWG STRANDED	2 AWG SOLID OR STRANDED



- 1

STAMP AMP 2W* APPROX AS SHOWN.
- 2

STAMP 60-75 APPROX AS SHOWN.
- 3 MATERIAL THK: 1.78±0.08[.070±.003].
- 4

TIN PLATE 0.00254[.000100] MIN THK PER ASTM B-545.
- 5

GOLD PLATE 0.00127[.000050] MIN THK PER ASTM B-488, TYPE 2, GRADE C, OVER NICKEL PL. 0.00076[.000030] MIN THK PER QQ-N-290.
- 6

MEETS MS20659-114, CLASS 2.
- 7

SUPERSEDED BY P/N 321600.

OBSOLETE	10	LOOSE PIECE, BAG		4	8-321600-5
7	50	LOOSE PIECE, BOX	--	4	8-321600-2
	50	LOOSE PIECE	--	5	2-321600-1
	50	LOOSE PIECE	6	4	321600
	QTY	PACKAGE TYPE	MILITARY	FINISH	PART NO

CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C[338°F]	THIS DRAWING IS A CONTROLLED DOCUMENT.		TE Connectivity	
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	NAME TERMINAL, RING TONGUE, SOLISTRAND	
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 26.7-42.4mm² [52,600-83,700] SOLID OR STRANDED		MATERIAL COPPER ASTM B-152	FINISH SEE TABLE	RESTRICTED TO -
FOR ORDER ENTRY	1-800-526-5142					
			CUSTOMER DRAWING		SCALE 2:1	SHEET 1 of 1
					REV N2	