


SHEET 1 OF 2
NUMBER 480712195
+.005
-.010

1. MATES WITH CAP 480713.
2. TO BE USED WITH MATE-N-LOK
DUAL LANCE SOCKETS.

HOUSING	MATERIAL	COLOR
1-480712-0	NYLON	NATURAL

Unpublished copy not to be reproduced nor published
without written permission of AMP Inc.

©1973 BY AMP INCORPORATED. ALL RIGHTS
RESERVED. AMP PRODUCTS COVERED BY
PATENTS AND/OR PATENTS PENDING

MATERIAL AND FINISH.

SEE TABLE

WIRE RANGE INSULATION

TOLERANCE EXCEPT
AS NOTED
± .010 ± 1° 0'SCALE
NTSLOC
CM

A

NO. 480712

REV
FCUSTOMER COPY
REFERENCE ONLYAMP INCORPORATED
HARRISBURG, PENNA.

CLASS .084 SOCKET HOUSING

TYPE PANEL MOUNT

F OBS-2 PEREC0730-0129-96

JH RS 3/26/73

REVISION RECORD

ECN

DP

CHK

DATE

DR 3/21/73

DE 3-21-73


CHK 3/19/73

APP 3-21-73

NAME 15 CIRCUIT MATE-N-LOK PLUG
DUAL LANCE HOUSING

DIMENSIONS IN INCHES. DO NOT SCALE PRINT.

PRINT LIST
53

SHEET 2 OF 2
NUMBER 480712

- NOTE: 1. Recommended panel thickness .025 - .065.
2. Both locking legs to be squeezed together and housing to be inserted straight-in, as opposed to a rocking manner of insertion.
3. The panel must be punched so that the housing enters the panel in the same direction as the punch.
4. Dimensions I and II to be equal within .005.
5. Panel must not have any material (paint, porcelain, etc.) applied in the mounting hole area that would decrease retention of the housing in the panel.
6. IF NOTES 3 AND/OR 5 ARE NOT COMPLIED WITH, THE 1.550 DIMENSION SHOULD BE REDUCED TO 1.530 TO ASSURE PROPER HOUSING RETENTION IN THE PANEL.

©1973 BY AMP, INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING

CUSTOMER COPY
REFERENCE ONLY

MATERIAL AND FINISH



AMP INCORPORATED
HARRISBURG, PENNA.

CLASS

WIRE — RANGE — INSULATION

TYPE

TOLERANCE EXCEPT
AS NOTED
± .005

SCALE
NTS

LOC
CM

A

NO SHEET 2 OF 2
480712

REV
F

NAME RECOMMENDED MOUNTING INFORMATION
15 CIRCUIT MATE-N-LOK PANEL MOUNT PLUG

LTR REVISION RECORD ECN DR CHK DATE

DR L. J. P. 3-21-73 DE J. K. 3-21-73
CHK M. P. 3-21-73 APP J. K. 3-21-73

DIMENSIONS IN INCHES. DO NOT SCALE PRINT

PRINT DIST
53