




2013

wiha 
Premium Tools



Complete **TORX®** Program




Torx® Index

	DESCRIPTION	Page
	SoftFinish® Cushion Grip	5
	ESD Safe SoftFinish® Cushion Grip	6
	Insulated Cushion Grip	7
	Powerhandle	7
	Stainless Steel Cushion Grip	7
	MicroFinish Non-Slip Grip	8
	Protturn	9
	3K Series	10
	Drive-Loc VI Blades	11
	T-handle & ComfortGrip	12-13
	L-Keys Offset Screwdrivers	13-14 14
	PocketStar Fold Outs	15
	Wing Handle	16
	Flag Handle	16
	TorqueControl Blades	24
	Precision Tools	
	ESD Safe	26
	Standard	27
	PicoFinish	27
	SYSTEM 4 Micro Bits	28
	SYSTEM 4 Blades	29
	Bit Sets	31
	Insert & Power Bits	34-36
	Bit Sockets & Sets	39-41


TorxPlus® Index

	DESCRIPTION	Page
	Wing Handle	18
	Flag Handle	18
	PocketStar Fold Outs	18
	SoftFinish® Cushion Grip	19
	T-handles	19
	L-Keys Short/Long Arm	20
	TorqueControl Blade	24
	ESD Safe Precision	26
	Bit-Selectors	31
	Insert Bits	38
	Power Bits	38
	Bit Sockets & Sets	39,41



Ball End Torx® Index

	DESCRIPTION	Page
	SoftFinish Drivers Cushion Grip	17
	L-Keys	17
	Power Bits	17

Security Torx® Index

	DESCRIPTION	Page
	SoftFinish® Cushion Grip	6
	Drive-Loc VI Blades	11
	L-Keys	14
	PocketStar Fold Outs	15
	SYSTEM 4 Micro Bits	28
	Bit Sets	32
	Insert Bits - 1/4" & 5/16"	37
	Power Bits	37
	Bit Sockets	39,41



MagicSpring Screw Holding

	DESCRIPTION	Page
	SoftFinish® Screw Holding Cushion Grip	21
	PicoFinish Soft Grip Screw Holding	21
	L-keys Screw Holding	22
	Wing Handle Screw Holding	22
	TorqueControl Blades Screw Holding	24
	Power Bits	38

Wing/Flag & L-keys Index

DESCRIPTION	Page
	L-Keys 13-14
	Offset Screwdrivers 14
	Wing Handle 16,18,22 Torx®, TorxPlus® & MagicSpring
	Flag Handle 16,18 Torx® & TorxPlus®

Screwdrivers Index

	DESCRIPTION	Page
	SoftFinish® CushionGrip 5-6,19,21 Torx®, Security Torx®, TorxPlus®, MagicSpring	
	ESD Safe SoftFinish® Cushion Grip - Torx®	6
	Insulated Cushion Grip - Torx®	7
	Powerhandle- Torx®	7
	Stainless Steel Cushion Grip - Torx®	7
	MicroFinish Non-Slip Grip - Torx®	8
	Protturn - Torx®	9
	3K Series - Torx®	10
	Offset Screwdrivers	14
	T-handle/ComfortGrip Torx® & TorxPlus®	12-15,19
	Precision Tools	
	ESD Safe	26
	Standard	27
	PicoFinish	27


Drive-Loc VI Interchangeable

DESCRIPTION	Page
	Drive-Loc VI Handle SoftFinish® Cushion Grip 11
	Drive-Loc VI Handle ESD Safe Cushion Grip 11
	Drive-Loc VI Handle MicroFinish Non-Slip Grip 11
	Drive-Loc VI Blades Torx® / Security Torx® 11

Fold Outs Index

DESCRIPTION	Page
	PocketStars 15,18 Torx, Security Torx, TorxPlus

TorqueControl Index

DESCRIPTION	Page
 TorqueVario Handle	23
 Torx® / TorxPlus® Blades	23
 Insulated Torque Tools	24
 Easy Torque Tools	24
 ESD Safe TorqueControl	24
 ESD Safe Torx® Blades	24
 T-handle Torque Tools	25
 Interchangeable Blades For Torque T-handle	25
 TorqueControl Sets	25


High Performance Bits Index

DESCRIPTION	Page
 Torx® Dura Insert Bits Tungsten Carbide Coated	34
 Torx® Diamond Bits	34
 Torx® TiN Coated- Titanium	34



Standard Bits Index

DESCRIPTION	Page
 Torx® Insert/Power Bits	35-36

Specialty Bits Index

DESCRIPTION	Page
  Ball End Torx®	17,38
  Torx® Align Bits Insert/Power Bits	36
  Security Torx® Insert/Power Bits	37
  TorxPlus® Bits Insert/Power Bits	38

Bit Sets Index

DESCRIPTION	Page
 BitFlip Sets	30
 Topra Bit Sets	30,32
 Six-in-One Bit Sets	30,32
 Bit Selector Sets	31-32
 Power Bit Belt Packs	31-32
 SYSTEM 4 Sets Micro Bits & Interchangeable Blades	28-29
 XSelectors	31-32




See Bit Holders on Page 33

ESD Blade Set Index

DESCRIPTION	Page
 Interchangeable Blade Set	6

Sockets Index

DESCRIPTION	Page
 Torx® 1/4" Drive	39
 Torx® 3/8" Drive	39
 Torx® 3/8" - 5/16" Bits	39
 Security Torx® 3/8", 1/2"	39
 External Torx® Sockets 1/4", 3/8", 1/2"	40
 6" Bit Sockets 1/4" & 3/8" Drive	40
 Bit Socket Sets	41

Wiha TORX® SoftFinish® Screwdrivers - Ergonomic Cushion Grip Handle

362 TORX® Screwdriver, With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item	No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36264	T5	60	2.4	2.5	.098	164	6.5	.05	10	
36266	T6	60	2.4	3.5	.139	164	6.5	.06	10	
36268	T7	60	2.4	3.5	.139	164	6.5	.06	10	
36270	T8	60	2.4	3.5	.139	164	6.5	.06	10	
36272	T9	60	2.4	4.0	.157	171	6.7	.10	10	
36274	T10	80	3.1	4.0	.157	191	7.5	.11	10	
36276	T15	80	3.1	4.0	.157	191	7.5	.11	10	
36278	T20	100	3.9	4.0	.157	211	8.3	.11	10	
36280	T25	100	3.9	4.5	.177	211	8.3	.12	10	
36282	T27	115	4.5	5.5	.216	233	9.2	.19	10	
36284	T30	115	4.5	6.0	.236	233	9.2	.20	10	
36286	T40	130	5.1	7.0	.275	254	10.0	.27	10	
36288	T45	130	5.1	8.0	.315	254	10.0	.31	10	


36294 Set 8 Pcs. TORX® Round blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item	No.	Size	mm	Size	mm	lbs.
36294	36266	T6	60	36278	T20	100
	36270	T8	60	36280	T25	100
	36274	T10	80	36282	T27	115
	36276	T15	80	36284	T30	115


36291 Set 6 Pcs. TORX®

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item	No.	Size	mm	Size	mm	lbs.
36291	36266	T6	60	36272	T9	60
	36268	T7	60	36274	T10	80
	36270	T8	60	36276	T15	80

36201 Set 6 Pcs. TORX®

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item	No.	Size	mm	Size	mm	lbs.
36201	36266	T6	60	36276	T15	80
	36270	T8	60	36278	T20	100
	36274	T10	80	36280	T25	100


36267 Set 12 Pcs. TORX® Round blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item	No.	Size	mm	Size	mm	lbs.
36267	36264	T5	60	36276	T15	80
	36266	T6	60	36278	T20	100
	36268	T7	60	36280	T25	100
	36270	T8	60	36282	T27	115
	36272	T9	60	36284	T30	115
	36274	T10	80	36286	T40	130

Wiha Security **TORX**® Drivers



362 Security **TORX**® Screwdriver With Wiha-SoftFinish® Handle

Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips.

Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36269	T7s	60	2.4	3.5	.139	164	6.5	.06	10
36271	T8s	60	2.4	3.5	.139	164	6.5	.06	10
36273	T9s	60	2.4	4.0	.157	171	6.7	.10	10
36275	T10s	80	3.1	4.0	.157	191	7.5	.11	10
36277	T15s	80	3.1	4.0	.157	191	7.5	.11	10
36279	T20s	100	3.9	4.0	.157	211	8.3	.11	10
36281	T25s	100	3.9	4.5	.177	211	8.3	.11	10
36283	T27s	115	4.5	5.5	.216	233	9.2	.19	10
36285	T30s	115	4.5	6.0	.236	233	9.2	.20	10
36287	T40s	130	5.1	7.0	.275	254	10.0	.28	10



36298 Set 7 Pcs. Security **TORX**®

Item No.	Size	mm	Size	mm	lbs.
36298	36269 T7s	60	36277 T15s	80	.95
	36271 T8s	60	36279 T20s	100	
	36273 T9s	60	36281 T25s	100	
	36275 T10s	80			



36259 Set 10 Pcs. Security **TORX**®

Item No.	Size	mm	Size	mm	lbs.
36259	36269 T7s	60	36279 T20s	100	1.5
	36271 T8s	60	36281 T25s	100	
	36273 T9s	60	36283 T27s	115	
	36275 T10s	80	36285 T30s	115	
	36277 T15s	80	36287 T40s	130	

Wiha SoftFinish® ESD Safe Handle



ESD Safe (10⁶-10⁹ Ohm)

362 ESD Safe **TORX**® Driver, With Wiha-SoftFinish® Handle

DIN EN 61340-5-1/ 61340-5-2 Round blade, CVM steel, hardened, hard chromed. Offers protection against electrostatic discharge. Dissipative SoftFinish® cushion grip handle, multi-component.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36260	T3	60	2.4	3.5	.139	164	6.5	.06	10
36204	T4	60	2.4	3.5	.139	164	6.5	.06	10
36200	T5	60	2.4	3.5	.139	164	6.5	.06	10
36206	T6	60	2.4	3.5	.139	164	6.5	.06	10
36208	T8	60	2.4	3.5	.139	164	6.5	.06	10
36209	T9	60	2.4	4.0	.157	171	6.7	.10	10
36218	T10	80	3.1	4.0	.157	191	7.5	.11	10
36219	T15	80	3.1	4.0	.157	191	7.5	.11	10
36224	T20	100	3.9	4.0	.157	211	8.3	.11	10



36289 Set 6 Pcs. ESD Safe **TORX**® Screwdrivers

Item No.	TORX: T6, T8, T9, T10, T15, T20	lbs.
36289		.81

Wiha Stainless Steel **TORX**® Screwdrivers



376 **TORX**® Screwdriver, With Wiha-SoftFinish® Handle

High quality stainless steel. SoftFinish® cushion grip handle.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
37608	T8	60	2.4	4.0	.139	164	5.3	.09	10
37609	T9	60	2.4	4.0	.157	171	5.5	.11	10
37610	T10	80	3.1	4.0	.157	191	6.7	.11	10
37615	T15	80	3.1	4.0	.157	191	6.7	.11	10
37620	T20	100	3.9	4.0	.157	218	7.9	.16	10
37625	T25	100	3.9	4.5	.177	218	7.9	.17	10
37627	T27	115	4.5	5.5	.216	233	8.5	.20	10
37630	T30	115	4.5	6.0	.236	233	8.9	.21	10
37640	T40	130	5.1	7.0	.276	254	10.0	.24	10



37690 Set 5 Pcs. Stainless Steel **TORX**® Screwdrivers

Item No.	TORX: T6, T8, T9, T10, T15, T20	lbs.
37690		.81

Wiha Insulated **TORX**® Screwdrivers


 **1000Volt**

325 **TORX**® Screwdriver, With Wiha-SoftFinish® Handle

Insulation According to ASTM F-1505-01, New VDE Specification 0682/part 201 and EN/IEC 60900, NFPA70E,  up to 1000 Volt. Individually Tested. Blade high alloy cvm steel, hardened, black finish. Insulation molded directly onto blade.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
32505	T5	60	2.4	164	6.5	.06	10
32511	T6	60	2.4	164	6.5	.06	10
32516	T7	60	2.4	164	6.5	.06	10
32521	T8	60	2.4	164	6.5	.06	10
32526	T9	60	2.4	164	6.5	.06	10
32531	T10	60	2.4	164	6.5	.06	10
32536	T15	80	3.1	191	7.5	.12	10
32541	T20	80	3.1	191	7.5	.12	10
32546	T25	80	3.1	198	7.8	.17	10
32551	T27	100	3.9	218	8.6	.20	10
32556	T30	100	3.9	218	8.6	.20	10
32561	T40	150	5.9	274	10.8	.30	10


 **1000Volt**

32590 Set 6 Pcs. **TORX**®

Item No.	Size	mm	Size	mm	lbs.
32590	32521 T8	60	32536 T15	80	.83
	32526 T9	60	32541 T20	80	
	32531 T10	60	32546 T25	80	


 **1000Volt**

32592 Set 10 Pcs. **TORX**®

Item No.	Size	mm	Size	mm	lbs.
32592	32511 T6	60	32536 T15	80	1.2
	32516 T7	60	32541 T20	80	
	32521 T8	60	32546 T25	80	
	32526 T9	60	32551 T27	100	
	32531 T10	60	32556 T30	100	

Wiha Powerhandle **TORX**®

Made in Germany



362 **TORX**® Screwdriver, With Wiha-Powerhandle CVM steel blade, hardened, hard chromed. Wiha-powerhandle cellulose-acetate.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
36205	T5	50	2.0	2.5	.098	110	4.3 .03 10
36210	T6	50	2.0	3.5	.139	125	4.9 .06 10
36212	T7	50	2.0	3.5	.139	125	4.9 .06 10
36215	T8	60	2.4	3.5	.139	135	5.3 .06 10
36220	T9	60	2.4	4.0	.157	140	5.5 .09 10
36225	T10	80	3.1	4.0	.157	170	6.7 .13 10
36230	T15	80	3.1	4.0	.157	170	6.7 .13 10
36235	T20	100	3.9	4.0	.157	200	7.9 .17 10
36240	T25	100	3.9	4.5	.177	200	7.9 .18 10
36245	T27	115	4.5	5.5	.216	215	8.5 .20 10
36250	T30	115	4.5	6.0	.236	225	8.9 .28 10



36292 8 Pc. Set **TORX**® With Wiha-Powerhandle

Item No.	Includes:	lbs.
36292	T6, T8, T10, T15, T20, T25, T27, T30	1.45



36293 6 Pc. Set **TORX**® With Wiha-Powerhandle

Item No.	Includes:	lbs.
36293	T6, T7, T8, T9, T10, T15	.78

Wiha ESD Safe Interchangeable Blade Set



In Durable Pouch

10893 ESD Safe **TORX**® Interchangeable Blade Set

5 Pc. Set Includes ESD Safe handle & 4 interchangeable blades.

Item No.	lbs.
10893	.75

TORX®: T6, T7, T8, T9, T10, T15, T20, T25

Wiha ESD Safe Handle

Wiha TORX® MicroFinish Handle Non-Slip Grip

Wiha MicroFinish handle has a patented non-slip surface - it won't peel, crack or deteriorate when exposed to petroleum solvents. Oil and moisture flow away from the handle surface for a powerful, non-slip grip. You get maximum force and comfort with dry, oily or wet hands.

Safe, high density material, eliminates risk of sharp objects becoming embedded in the handle

Blades are hardened & hard chromed

Exact fit precision ground tips

MicroFinish Handle with patented non-slip surface. Ergo handle shape for maximum comfort & exceptional torque transfer

Blade CVM, hardened & tempered tool steel, gives exceptional tool life, wear resistance & high torque performance



527 TORX® Screwdriver, With Wiha-MicroFinish Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant. Round blades.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
52711	T9	60	2.4	4.0	.157	171	6.7	.15	10
52713	T10	80	3.1	4.0	.157	191	7.5	.15	10
52716	T15	80	3.1	4.0	.157	191	7.5	.15	10
52719	T20	100	3.9	4.0	.157	211	8.3	.15	10
52722	T25	100	3.9	4.5	.177	211	8.3	.16	10
52726	T27	115	4.5	5.5	.216	233	9.2	.25	10
52729	T30	115	4.5	6.0	.236	233	9.2	.27	10
52732	T40	130	5.1	7.0	.275	254	10.0	.40	10



52790 Set 5 Pcs. TORX®

Blade chrome-vanadium-molybdenum steel, hardened, round blades hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.


Item No.	Size	mm	Size	mm	lbs.
52790	52713 T10	80	52722 T25	100	1.0
	52716 T15	80	52729 T30	115	
	52719 T20	100			



52791 Set 8 Pcs. TORX®

Blade chrome-vanadium-molybdenum steel, hardened, round blades hard chromed. Wiha-MicroFinish handle, cellulose-acetate, impact resistant, non-slip, oil and grease resistant.


Item No.	Size	mm	Size	mm	lbs.
52791	52711 T9	60	52722 T25	100	1.89
	52713 T10	80	52726 T27	115	
	52716 T15	80	52729 T30	115	
	52719 T20	100	52732 T40	130	

Wiha TORX® Protturn Screwdrivers

45591 Set 6 Pcs. TORX®

Item No.	Size	mm	Size	mm	lbs.
45591	45506 T7	50	45521 T10	80	.72
	45511 T8	60	45526 T15	80	
	45516 T9	60	45531 T20	100	

45592 Set 8 Pcs. TORX®

Item No.	Size	mm	Size	mm	lbs.
45592	45511 T8	60	45531 T20	100	1.07
	45516 T9	60	45536 T25	100	
	45521 T10	80	45541 T27	115	
	45526 T15	80	45546 T30	115	


45589 Set 14 Pcs. TORX®

Item No.	Size	mm	Size	mm	lbs.
45589	45505 T6	50	45531 T20	100	2.2
	45506 T7	50	45536 T25	100	
	45511 T8	60	45541 T27	115	
	45516 T9	60	45546 T30	115	
	45521 T10	80	45551 T40	130	
	45522 T10	275	45556 T45	130	
	45526 T15	80	45561 T50	130	


48400 1/4" Bit Holding Screwdriver, With Wiha-Protturn Handle

Magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM steel, nickel-plated. Handle, molded on, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pcs.
48400	1/4	125	5.0	243	9.6	.24	10


455 TORX® Screwdriver, With Wiha-Protturn Handle

Blade high alloy CVM steel, hardened, black finish. Molded on ergonomic Wiha-Protturn handle, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
45505	T6	50	2.0	3.5	.139	129	5.1	.05	10
45506	T7	50	2.0	3.5	.139	129	5.1	.05	10
45511	T8	60	2.4	3.5	.139	139	5.5	.06	10
45516	T9	60	2.4	4.0	.157	149	5.8	.08	10
45521	T10	80	3.1	4.0	.157	170	6.7	.10	10
45522	T10	275	10.8	4.0	.157	363	14.2	.13	10
45526	T15	80	3.1	4.0	.157	170	6.7	.10	10
45531	T20	100	3.9	4.0	.157	190	7.5	.11	10
45536	T25	100	3.9	4.5	.177	190	7.5	.11	10
45541	T27	115	4.5	5.5	.216	215	8.4	.11	10
45546	T30	115	4.5	6.0	.236	215	8.4	.20	10
45551	T40	130	5.1	7.0	.275	240	9.4	.28	10
45556	T45	130	5.1	8.0	.315	240	9.4	.27	10
45561	T50	130	5.1	9.0	.354	240	9.4	.31	10

Wiha TORX® 3K Series Drivers and Sets

3K Series

Molded on soft grip ergonomic handle, impact resistant

Precision black tip

Hole for hanging

Blade high alloy CVM steel, hardened



45598 Set 6 Pcs. TORX® Blade CVM steel, hardened, precision black tip. Wiha-3k Ergo handle, cushion grip.

Item No.	Size	mm	Size	mm	lbs.
45598	45504 T6	60	45509 T9	60	.88
	45507 T7	60	45510 T10	80	
	45508 T8	60	45515 T15	80	



455 TORX® Screwdriver, With Wiha-3K Series Handle

Blade high alloy CVM steel, hardened, precision black tip.

Molded on ergonomic Wiha-3K Series handle, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
45504	T6	60	2.4	3.2	9/64	145	5.7	.06	10
45507	T7	60	2.4	3.5	9/64	129	5.1	.05	10
45508	T8	60	2.4	3.5	9/64	139	5.5	.06	10
45509	T9	60	2.4	4.0	5/32	149	5.8	.08	10
45510	T10	80	3.1	4.0	5/32	170	6.7	.10	10
45515	T15	80	3.1	4.0	5/32	190	7.5	.11	10
45520	T20	100	3.9	5.5	7/32	215	8.4	.11	10
45525	T25	100	3.9	6.0	1/4	215	8.4	.20	10
45527	T27	115	4.5	7.0	9/32	240	9.4	.28	10
45530	T30	115	4.5	6.0	1/4	233	9.1	.21	10
45540	T40	130	5.1	7.0	9/32	248	9.7	.25	10
45545	T45	130	5.1	8.0	5/16	249	9.8	.30	10
45550	T50	130	5.1	9.0	3/8	249	9.8	.33	10



45593 Set 5 Pcs. TORX® Blade CVM steel, hardened, precision black tip. Wiha-3k Ergo handle, cushion grip.

Item No.	Size	mm	Size	mm	lbs.
45593	45508 T8	60	45520 T20	100	.86
	45510 T10	80	45525 T25	100	
	45515 T15	80			



45595 Set 8 Pcs. TORX® Wiha-3k Ergo handle, cushion grip.

Item No.	Size	mm	Size	mm	lbs.
45595	45504 T8	60	45520 T20	100	1.36
	45509 T9	60	45525 T25	100	
	45510 T10	80	45527 T27	115	
	45515 T15	80	45530 T30	115	



45597 Set 11 Pcs. TORX® 3K Ergo Series Screwdriver Set
Blade chrome-vanadium-molybdenum steel, hardened, precision black tip. Wiha-3k Ergo handle, cushion grip.

Item No.	Size	mm	Size	mm	lbs.
45597	45504 T6	60	45520 T20	100	1.72
	45507 T7	60	45525 T25	100	
	45508 T8	60	45527 T27	115	
	45509 T9	60	45530 T30	115	
	45510 T10	80	45540 T40	130	
	45515 T15	80			

Drive-Loc VI

For Adjustable Length Locking Blades



Locking mechanism allows blade length to be adjusted from 40mm-120mm. (1.7 to 4.7" In 1/8" increments)

Blades high quality CVM steel, hard chrome finish.

Ergonomic handles in ESD Safe, cushioned & non-slip grip.



28488 Drive-Loc VI Cushion Grip Handle

Wiha-SoftFinish® impact resistant, with roll off protection.

Advantages:

Ergonomic cushion grip, Drive-Loc mechanism guarantees a secure hold and rapid blade exchange.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
28488	6.0	115	4.5	36.0	1.41	.20



28486 ESD Safe Drive-Loc VI Cushion Grip Handle

Wiha-SoftFinish® impact resistant, with roll off protection.

Advantages:

Ergonomic cushion grip, Drive-Loc mechanism guarantees a secure hold and rapid blade exchange. Static Dissipative.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
28486	6.0	115	4.5	36.0	1.41	.20



28487 Drive-Loc VI MicroFinish Non-Slip Grip Handle

Wiha-MicroFinish handle, won't peel, crack or deteriorate when exposed to petroleum solvents. Ideal for Hex, TORX® & Nut Drivers.

Advantages:

Ergonomic handle shape for maximum comfort, Drive-Loc mechanism guarantees a secure hold and rapid blade exchange.

Item						
No.	mm	mm	Inch	mm	Inch	lbs.
28487	6.0	115	4.5	36.0	1.41	.20



281 TORX® Drive-Loc VI Interchangeable Blade

High alloy CVM steel, through hardened, hard chrome finish.

Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item				
No.	Size + Size	lbs.	pkg.	
28126	T6 T8	.09	1	
28127	T7 T9	.09	1	
28128	T10 T15	.10	1	
28129	T20 T25	.10	1	
28130	T30 T40	.10	1	



281 Security TORX® Drive-Loc VI Interchangeable Blade,

high alloy CVM steel, through hardened, hard chrome finish.

Over all blade length 150mm/5.9". Blades fit all Drive-Loc VI handles.

Item				
No.	Size + Size	lbs.	pkg.	
28132	T6s T8s	.09	1	
28133	T7s T9s	.09	1	
28134	T10s T15s	.10	1	
28135	T20s T25s	.10	1	
28136	T30s T40s	.10	1	



28195 Drive-Loc VI Interchangeable Blade Set, 6 Pcs. In Durable Pouch

Set includes Drive-Loc VI handle & 5 interchangeable blades.

Item		lbs.
No. 28195		.85

TORX®: T6&T8, T7&T9, T10&T15, T20&T25, T30&T40

Wiha SoftFinish® Cushion Grip Blade Lock Handle



28197 Drive-Loc VI Interchangeable Blade Set, 6 Pcs. In Durable Pouch

Set includes Drive-Loc VI handle & 5 interchangeable blades.

Item		lbs.
No. 28197		.83

Security TORX®: T6s+T8s, T7s+T9s, T10s+T15s,

T20s+T25s, T30s+T40s & SoftFinish® Cushion Grip Blade Lock Handle

Wiha Insulated SlimLine Tools

Insulation Test Standards:

Insulation according to EN/IEC 60900, ASTM F-1505-01, VDE 0682/part 201, DIN 7437, NFPA70E & CSA specification

Ideal for jobs where access is limited


Integrated *Slim* Insulation molded directly onto blade

Insulation does not exceed screw head diameter

High quality chrome vanadium steel, through-hardened

 **1000Volt Rated**
10,000Volt Tested

Wiha SlimTECHNOLOGY
Achieves blade diameters up to 33% narrower utilizing integrated insulation



 **1000Volt**

28301 *SlimLine* Blade Holder, With Wiha-SoftFinish® Handle
Insulation According to VDE, ASTM F-1505-01 and EN/IEC 60900, NFPA70E & CSA,  up to 1000 Volt.

Chrome-vanadium steel, through-hardened. Insulation molded directly onto blade. Quick release holder securely lock blades.

Wiha-SoftFinish® handle, multi-component, cushion grip.

Item No.								
No.	Size	mm	Inch	mm	Inch	lbs.	lbs.	pkg.
28301	1/4"	50	2.0	160	6.3	.15	1	



283 Insulated **TORX®** SlimLine Blades

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

Item No.								
No.	Size	mm	Dia.	Length	Nm	lbs.	lbs.	Pkg.
28339	T8	90	4.1	2.8"	1.3	11.5	.02	1
28340	T10	90	4.1	2.8"	3.8	33.7	.02	1
28341	T15	90	6.1	2.8"	5.5	48.8	.02	1
28342	T20	90	6.1	2.8"	5.5	48.8	.02	1

Wiha **TORX®** Soft Grip Dual Drive T-handle

Two Tools In One!



Maximum Comfort & Maximum Power

Torx - Blades of CVM tool steel, through hardened durability, hard chrome finish

Two component soft grip handle



364 Soft Grip **TORX®** T-handle

Blade CVM steel, through hardened, satin chrome finish. Soft grips are molded on and include through the handle side torque drive.


Item No.				
No.	Size	mm	lbs.	pkg.
36480	T10	100	.08	10
36481	T15	100	.08	10
36482	T20	100	.13	10
36483	T25	150	.16	10
36484	T27	150	.19	10
36486	T30	150	.20	10
36487	T40	150	.24	10



36497 Set 7 Pcs. **TORX®** Soft Grip T-handles

Item No.				
No.	Size	mm	Size	mm
36497	36480 T10	100	36484 T27	150
	36481 T15	100	36486 T30	150
	36482 T20	100	36487 T40	150
	36483 T25	150		


Wiha TORX® T-handle



364 TORX® with Wiha T-handles

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chrome finish. Wiha T-handle high quality plastic, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs	pkg.
36409	T9	100	3.9	4.0	5/32	80	3.1	.07	10
36410	T10	100	3.9	4.0	5/32	80	3.1	.07	10
36415	T15	100	3.9	4.0	5/32	80	3.1	.07	10
36417	T15	200	7.9	5.5	7/32	80	3.1	.13	10
36420	T20	100	3.9	4.0	5/32	100	3.9	.10	10
36422	T20	200	7.9	5.5	7/32	100	3.9	.17	10
36425	T25	100	3.9	4.0	5/32	100	3.9	.11	10
36427	T25	200	7.9	5.5	7/32	100	3.9	.17	10
36430	T27	100	3.9	5.5	7/32	100	3.9	.14	10
36432	T27	200	7.9	5.5	7/32	100	3.9	.17	10
36435	T30	100	3.9	7.9	6.0	100	3.9	.14	10
36437	T30	200	7.9	6.0	1/4	100	3.9	.19	10
36440	T40	100	3.9	7.0	9/32	100	3.9	.16	10
36442	T40	200	7.9	7.0	9/32	100	3.9	.23	10
36445	T45	150	5.9	8.0	5/16	120	4.7	.29	10
36450	T50	150	5.9	9.0	3/8	120	4.7	.30	10
36452	T50	250	9.8	9.0	3/8	120	4.7	.45	10



#36490

#36492

36492 TORX® T-handle Set, 7 Pc.

Equipped with T9, T10, T15, T20, T25, T27, T30

Item No.	lbs.	pkg.
36492	1.24	1

36490 TORX® T-handle Set, 7 Pc. In Metal Stand

Equipped with T10, T15, T20, T25, T30, T40, T50

Item No.	lbs.	pkg.
36490	2.65	1

- Blade high alloy CVM steel, hardened, hard chrome finish

- Wiha T-handle high quality plastic, impact resistant



36494 TORX® T-handle Set, 8 Pc. In Metal Stand

Equipped with T9, T10, T15, T20, T25, T27, T30, T40

Item No.	lbs.	pkg.
36494	3.10	1



Wiha TORX® Short Arm L-keys



363 TORX® L-key, Short Arm

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
36305	T5	37	1.5	16	.6	.01	10
36306	T6	39	1.5	16	.6	.01	10
36307	T7	42	1.7	16	.6	.01	10
36308	T8	45	1.8	16	.6	.01	10
36309	T9	48	1.9	16	.6	.01	10
36310	T10	51	2.0	17	.7	.01	10
36315	T15	54	2.1	19	.7	.01	10
36320	T20	58	2.3	19	.7	.01	10
36325	T25	63	2.5	21	.8	.02	10
36327	T27	67	2.6	22	.9	.03	10
36330	T30	73	2.9	24	.9	.05	10
36340	T40	79	3.1	26	1.0	.06	10
36345	T45	82	3.2	28	1.1	.09	10
36350	T50	95	3.7	32	1.3	.13	10
36355	T55	108	4.3	35	1.4	.27	10
36360	T60	120	4.7	38	1.5	.40	10



#36392



#36394



#36399

36392 TORX® Set, 7 Pc. In Plastic Holder

Equipped with T6, T7, T8, T9, T10, T15, T20

Item No.	lbs.	pkg.
36392	.10	1

36394 TORX® Set, 9 Pc. In Plastic Holder

Equipped with T8, T9, T10, T15, T20, T25, T27, T30, T40

Item No.	lbs.	pkg.
36394	.30	1

36399 TORX® Set, 16 Pc.

Equipped with T5, T6, T7, T8, T9, T10, T15, T20, T25, T27, T30, T40, T45, T50, T55, T60

Item No.	lbs.	pkg.
36399	1.14	1



36390 TORX® Set, 9 Pc. In Metal Stand

Equipped with T10, T15, T20, T25, T30, T40, T50, T55, T60

Item No.	lbs.	pkg.
36390	1.86	1



Wiha TORX® Long Arm L-keys



366 TORX® L-key, Long Arm

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
36645	T5	71	2.8	12	.5	.06	10
36646	T6	78	3.1	13	.5	.07	10
36647	T7	87	3.4	16	.6	.10	10
36648	T8	99	3.9	18	.7	.13	10
36649	T9	106	4.2	18	.7	.17	10
36650	T10	118	4.6	21	.8	.23	10
36651	T15	131	5.2	23	.9	.33	10
36652	T20	144	5.7	25	1.0	.44	10
36653	T25	158	6.2	28	1.1	.65	10
36654	T27	169	6.7	30	1.2	.98	10
36655	T30	184	7.2	32	1.3	1.27	10
36659	T40	201	7.9	35	1.4	2.09	10
36660	T45	222	8.7	40	1.6	2.70	10
36661	T50	213	8.4	40	1.6	3.14	10

Wiha ErgoStar Ball End TORX® Long L-keys



36689 ErgoStar TORX® Long Arm Set, 13 Pc. In Molded Holder

Equipped with T5, T6, T7, T8, T9, T10, T15, T20, T25, T27, T30, T40, T45

Item		
No.	lbs.	pkg.
36689	1.08	1

Wiha Security TORX® L-keys



36699 Long Arm TORX® Set, 13 Pc. in Molded Holder

Equipped with T5, T6, T7, T8, T9, T10, T15, T20, T25, T27, T30, T40, T50

Item		
No.	lbs.	pkg.
36699	1.13	1



36698 Long Arm TORX® Set, 10 Pc. In Molded Holder

Equipped with T6, T7, T8, T9, T10, T15, T20, T25, T27, T30

Item		
No.	lbs.	pkg.
36698	4.4	1



363 Security TORX® L-key, Short Arm

High alloy CVM steel, hardened, black finish.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
36321	T7s	42	1.7	16	.6	.01	10
36323	T8s	45	1.8	16	.6	.01	10
36326	T9s	48	1.9	16	.6	.01	10
36328	T10s	51	2.0	17	.7	.01	10
36329	T15s	54	2.1	19	.7	.01	10
36332	T20s	58	2.3	19	.7	.02	10
36335	T25s	63	2.5	21	.8	.02	10
36337	T27s	67	2.6	22	.9	.03	10
36339	T30s	73	2.9	24	.9	.04	10
36342	T40s	79	3.1	26	1.0	.06	10
36346	T45s	82	3.2	28	1.1	.09	10
36352	T50s	95	3.7	35	1.3	.13	10
36357	T55s	108	4.3	38	1.4	.27	10



Security Torx® L-Key Set

36393 Security TORX® Set, 9 Pcs. In Plastic Holder

Equipped with T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s

Item		
No.	lbs.	pkg.
36393	.30	1



36694 26 Piece Combo Pack Long Arm TORX® And Hex Inch L-key Sets, In Pouch

Set includes: 36699-13pc set T5-T50 and 36991-13pc set .050 - 3/8"

Item		
No.	lbs.	pkg.
36694	2.13	1

Wiha Offset Screwdrivers



207 TORX® Offset Screwdriver With Molded Handle

For working in confined spaces. Blade CVM special steel, hardened, black finish.

Item No.	Size	lbs.	pkg.
20756	T6 + T8	.02	1
20757	T7 + T9	.02	1
20758	T10 + T15	.02	1
20759	T20 + T25	.07	1
20760	T27 + T30	.10	1




20799 TORX® Offset Screwdriver Set, 5 Pcs.

With Molded Handle Blade CVM special steel, hardened, black finish.

Item No.	Set Includes: T6+T8, T7+T9, T10+T15, T20+T25, T27+T30	lbs.	pkg.
20799		.24	1

Wiha PocketStar Fold Outs



Push button
key release



Blade length range
1.68 - 1.94"

36396 TORX® PocketStar Fold Outs, 7 Pc. Set

High alloy CVM steel, hardened, molded ergonomic handle. OAL 3.8"

Item No.	PocketStar	lbs.	.22
36396			

TORX®: T7, T8, T9, T10, T15, T20, T25



Push button
key release



Blade length range
1.68 - 1.94"

36395 Security TORX® PocketStar Fold Outs, 7 Pc. Set

High alloy CVM steel, hardened, molded ergonomic handle. OAL 3.8"

Item No.	PocketStar	lbs.	.22
36395			

TR TORX®: T7s, T8s, T9s, T10s, T15s, T20s, T25s



Push button
key release



Blade length range
1.95 - 2.39"

36398 TORX® PocketStar Fold Outs, 8 Pc. Set

High alloy CVM steel, hardened, molded ergonomic handle. OAL 4.74"

Item No.	PocketStar	lbs.	.24
36398			

TORX®: T9, T10, T15, T20, T25, T27, T30, T40



Push button
key release



Blade length range
1.95 - 2.39"

36397 Security TORX® PocketStar Fold Outs, 8 Pc. Set

High alloy CVM steel, hardened, molded ergonomic handle. OAL 4.74"

Item No.	PocketStar	lbs.	.24
36397			

TR TORX®: T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s

Wiha TORX® Tools



Ideal for use with indexable carbide tooling and also for working in confined spaces



Ideal for use with indexable carbide tooling and also for working in confined spaces



365 TORX® Screwdriver, With Wing Handle

Blade high alloy CVM steel, hardened, black finish.

Wing handle high quality plastic, impact resistant.

Item	No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36510	T6	35	1.4	70	2.7	40	1.6	.02	10	
36512	T7	35	1.4	70	2.7	40	1.6	.02	10	
36515	T8	40	1.6	75	2.9	40	1.6	.02	10	
36520	T9	40	1.6	75	2.9	40	1.6	.02	10	
36525	T10	40	1.6	75	2.9	40	1.6	.02	10	
36530	T15	45	1.8	80	3.1	40	1.6	.02	10	
36535	T20	45	1.8	80	3.1	40	1.6	.02	10	



370 TORX® Screwdriver, With Flag Handle

Blade high alloy CVM steel, hardened, black finish.

Flag handle high quality plastic, impact resistant.

Item	No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
37013	T5	35	1.4	63	2.6	15.0	.75	.01	10	
37016	T6	35	1.4	63	2.6	15.0	.75	.01	10	
37019	T7	35	1.4	67	2.6	19.0	.75	.01	10	
37022	T8	40	1.6	72	2.8	19.0	.75	.01	10	
37026	T9	40	1.6	74	2.9	23.5	.93	.01	10	
37029	T10	40	1.6	74	2.9	23.5	.93	.01	10	
37032	T15	45	1.8	80	3.1	28.0	1.10	.02	10	
37036	T20	45	1.8	80	3.1	28.0	1.10	.02	10	



36591 Wing Handle TORX® Set, 7 Pc.

Set includes: T6, T7, T8, T9, T10, T15, T20 wt. .16



37091 Flag Handle TORX® Set, 7 Pc.

Set includes: T6, T7, T8, T9, T10, T15, T20 wt. .14



36590 Wing Handle TORX® Set, 7 Pc. In Metal Stand

Set includes: T6, T7, T8, T9, T10, T15, T20 wt. .32



37090 Flag Handle TORX® Set, 7 Pc. in Metal Stand

Set includes: T6, T7, T8, T9, T10, T15, T20 wt. .31

Wiha Ball End **TORX**® Screwdrivers

- Ball End For 25° Angle Driving
- Precision Machined Exact Fit Tips
- Through Hardened For Maximum Durability
- WIHA High Performance CRM-72 Tool Steel
- Guaranteed Quality Made By Wiha



362 Ball End **TORX**® Screwdriver, With Wiha-SoftFinish® Handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item									
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36216	T9	60	2.4	4.0	.157	164	6.5	.10	10
36217	T10	60	2.4	4.0	.157	184	7.2	.11	10
36221	T15	80	3.1	4.0	.157	191	7.5	.11	10
36222	T20	80	3.1	4.0	.157	211	8.3	.11	10
36226	T25	100	3.9	4.5	.177	218	8.6	.12	10
36227	T27	115	4.5	5.5	.216	233	9.2	.19	10
36236	T30	115	4.5	6.0	.236	233	9.2	.20	10



36237 Set 7 Pcs. **TORX®** Blade high alloy CVM steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item					
No.	Size	mm	Size	mm	lbs.
36237	36216 T9	60	36226 T25	100	1.24
	36217 T10	60	36227 T27	115	
	36221 T15	80	36236 T30	115	
	36222 T20	80			


Wiha Ball End **TORX**® L-keys



366 Ball End **TORX**® L-key, Long Arm

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
36631	T9	111	4.4	21	.83	.17	10
36632	T10	121	4.8	23	.91	.23	10
36633	T15	136	5.4	27	1.1	.33	10
36634	T20	148	5.8	29	1.1	.44	10
36635	T25	163	6.4	33	1.3	.65	10
36636	T27	176	6.9	36	1.4	.98	10
36637	T30	191	7.5	38	1.5	1.27	10
36638	T40	210	8.3	43	1.7	2.09	10



36692 Ball End **TORX**® L-key Set, 8 Pc. in Plastic Holder

Equipped with T9, T10, T15, T20, T25, T27, T30, T40

Item		
No.	lbs.	pkg.
36692	6.16	1

Wiha Ball End **TORX**® Power Bits



745 Ball End **TORX**® Power Bits 1/4" Hex Drive, Length 2.0"/50mm

Item				
No.	Size	mm	pkg.	lbs.
74524	T9	50	10	.18
74526	T10	50	10	.18
74528	T15	50	10	.18
74532	T20	50	10	.18
74534	T25	50	10	.18
74537	T27	50	10	.18
74539	T30	50	10	.18
74541	T40	50	10	.18

2 bit pack


745 Ball End **TORX**® Power Bit Packs, 1"

Item			
No.	Size	mm	lbs.
74505	T9	50	.05
74520	T10	50	.05
74522	T15	50	.05
74543	T20	50	.05
74545	T25	50	.06
74547	T27	50	.06
74549	T30	50	.08
74550	T40	50	.08



The TORXPlus® Advantage

The TorxPlus® Drive System offers 100% improvement in driver bit fatigue & 25% average improvement in driver bit torsional strength. In addition its unique design provides optimum torque transfer & eliminates the need for excessive end load pressure while driving the fastener. The TorxPlus® configuration also virtually eliminates tool "camout" & slippage that can damage the head of the fastener and cause reduced tool life.



- Broad Surface For Driving
- Features 0° Drive Angle Between The Fastener & Driver
- Greater Engagement Depth



Wiha PocketStar Fold Out



Push button
key release

36697 TORXPlus® PocketStar Fold Outs, 8 Pc. Set

High alloy CVM steel, hardened, molded ergonomic handle.

Item No.		
36697	PocketStar	lbs. .31
TORXPlus®: IP6, IP7, IP8, IP9, IP10, IP15, IP20, IP25		

Wiha TORXPlus® Tools

TORXPlus®

 Not for use in standard Torx fasteners

#37092

370 TORXPlus® Screwdriver, With Flag Handle

Ideal for use with indexable carbide tooling and also for working in confined spaces. Blade high alloy CVM steel, hardened, black finish. Flag handle high quality plastic, impact resistant.

Item No.									
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
37040	IP5	35	1.4	63	2.6	15.0	.75	.01	10
37042	IP6	35	1.4	63	2.6	15.0	.75	.01	10
37044	IP7	35	1.4	67	2.6	19.0	.75	.01	10
37046	IP8	40	1.6	72	2.8	19.0	.75	.01	10
37048	IP9	40	1.6	74	2.9	23.5	.93	.01	10
37050	IP10	40	1.6	74	2.9	23.5	.93	.01	10
37052	IP15	45	1.8	80	3.1	28.0	1.10	.02	10
37054	IP20	45	1.8	80	3.1	28.0	1.10	.02	10

37092 Flag Handle TORXPlus® Set, 7 Pc. in Metal Stand

Set includes:  wt. .31
IP6, IP7, IP8, IP9, IP10, IP15, IP20

TORXPlus®

 Not for use in standard Torx fasteners

365 TORXPlus® Screwdriver, With Wing Handle

Blade high alloy CVM steel, hardened, black finish.
Wing handle high quality plastic, impact resistant.

Item No.									
No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36540	IP5	35	1.4	70	2.7	40	1.6	.02	10
36542	IP6	35	1.4	70	2.7	40	1.6	.02	10
36544	IP7	35	1.4	70	2.7	40	1.6	.02	10
36546	IP8	40	1.6	75	3.0	40	1.6	.02	10
36548	IP9	40	1.6	75	3.0	40	1.6	.02	10
36550	IP10	40	1.6	75	3.0	40	1.6	.02	10
36552	IP15	45	1.8	80	3.1	40	1.6	.02	10
36554	IP20	45	1.8	80	3.1	40	1.6	.02	10

36592 TORXPlus® 7 Pc. Wing Handle

Set In Metal Stand
Equipped with IP6, IP7, IP8, IP9,
IP10, IP15, IP20

Item No.		
36592	lbs. .38	pkg. 1



Wiha TORXPlus® Cushion Grip Drivers



Not for use in standard Torx fasteners

362 TORXPlus® Screwdriver With Wiha SoftFinish Handle

Round blade high alloy Chrome-vanadium-molybdenum tool steel, hardened, hard chromed. Wiha-Chromtop finish on tips.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36211	IP6	60	2.4	3.5	.139	164	6.5	.06	10
36223	IP7	60	2.4	3.5	.139	164	6.5	.06	10
36228	IP8	60	2.4	4.0	.157	171	6.7	.10	10
36229	IP9	60	2.4	4.0	.157	171	6.7	.11	10
36233	IP10	80	3.1	4.0	.157	191	7.5	.11	10
36238	IP15	80	3.1	4.0	.157	191	7.5	.11	10
36239	IP20	100	3.9	4.5	.177	211	8.3	.11	10
36243	IP25	100	3.9	5.5	.216	211	8.3	.19	10
36248	IP27	115	4.5	6.0	.236	233	9.2	.20	10
36253	IP30	115	4.5	7.0	.275	233	9.2	.28	10
36255	IP40	130	5.1	7.0	.275	254	10.0	.28	10



36299 Set 7 Pcs. TORXPlus® Blade high alloy CVM steel, hardened, hard chromed. Wiha-SoftFinish handle, multi-component.

Item No.	Size	mm	Size	mm	lbs.
36299	36228 IP8	60	36243 IP25	100	1.23
	36233 IP10	80	36253 IP30	115	
	36238 IP15	80	36255 IP40	130	
	36239 IP20	100			



36296 Set 6 Pcs. TORXPlus®

Blade high alloy CVM steel, hardened, hard chromed. Wiha-SoftFinish handle, multi-component.

Item No.	Size	mm	Size	mm	lbs.
36296	36211 IP6	60	36229 IP9	60	.72
	36213 IP7	60	36233 IP10	80	
	36228 IP8	60	36238 IP15	80	

Wiha T-handle TORXPlus®



Not for use in standard Torx fasteners

364 TORXPlus® Screwdriver, With Wiha T-handle

Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha T-handle high quality plastic, impact resistant.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36461	IP9	100	3.9	4.0	.157	80	3.1	.07	10
36463	IP10	100	3.9	4.0	.157	80	3.1	.07	10
36466	IP15	100	3.9	4.0	.157	80	3.1	.07	10
36469	IP20	100	3.9	4.0	.157	80	3.1	.10	10
36472	IP25	150	5.9	8.0	.315	120	4.7	.13	10
36474	IP27	150	5.9	8.0	.315	120	4.7	.14	10
36476	IP30	150	5.9	8.0	.315	120	4.7	.16	10
36478	IP40	150	5.9	8.0	.315	120	4.7	.20	10




36496 Set 6 Pcs. TORXPlus® T-handles

Blade CVM steel, hardened, hard chromed. Chromtop blade tips. Wiha T-handle high quality plastic, impact resistant.

Item No.	Size	mm	Size	mm	lbs.
36496	36463 IP10	100	36472 IP25	150	1.01
	36466 IP15	100	36474 IP27	150	
	36469 IP20	100	36476 IP30	150	

TORXPlus®

For Improved Torque and Longer Tool Life



Not for use in standard
Torx fasteners

361 TORXPlus® L-key, Short Arm

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
36106	IP6	39	1.5	16	.6	.01	10
36107	IP7	42	1.7	16	.6	.01	10
36108	IP8	45	1.8	16	.6	.01	10
36109	IP9	48	1.9	16	.6	.01	10
36110	IP10	51	2.0	17	.7	.01	10
36115	IP15	55	2.2	19	.7	.01	10
36120	IP20	58	2.3	19	.7	.01	10
36125	IP25	63	2.5	21	.8	.01	10
36127	IP27	68	2.7	22	.9	.02	10
36130	IP30	73	2.9	24	.9	.03	10
36140	IP40	81	3.2	26	1.0	.05	10



Not for use in standard
Torx fasteners

366 TORXPlus® L-key, Long Arm

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
36606	IP6	64	2.5	14	.6	.01	10
36607	IP7	68	2.7	14	.6	.01	10
36608	IP8	74	2.9	15	.6	.01	10
36609	IP9	78	3.1	16	.6	.01	10
36610	IP10	83	3.3	18	.7	.01	10
36615	IP15	88	3.5	18	.7	.02	10
36620	IP20	94	3.7	18	.7	.02	10
36625	IP25	98	3.9	19	.7	.03	10
36627	IP27	107	4.2	23	.9	.05	10
36630	IP30	114	4.5	24	.9	.06	10
36640	IP40	118	4.6	27	1.0	.09	10



36197 TORXPlus® L-key, Short Arm, 7 Pc. Set In Holder

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

Item No.	lbs.	pkg.	Set includes the following L-keys:
36197	.10	1	IP6, IP7, IP8, IP9, IP10, IP15, IP20



36690 TORXPlus® L-key, Long Arm, 7 Pc. Set In Holder

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

Item No.	lbs.	pkg.	Set includes the following L-keys:
36690	.22	1	IP6, IP7, IP8, IP9, IP10, IP15, IP20



36199 TORXPlus® L-key, Short Arm, 9 Pc. Set In Holder

Set includes the following L-keys:

Item No.	lbs.	pkg.	Set includes the following L-keys:
36199	.30	1	IP8, IP9, IP10, IP15, IP20, IP25, IP27, IP30, IP40



36691 TORXPlus® L-key, Long Arm, 9 Pc. Set In Holder

Set includes the following L-keys:

Item No.	lbs.	pkg.	Set includes the following L-keys:
36691	.35	1	IP8, IP9, IP10, IP15, IP20, IP25, IP27, IP30, IP40

Wiha MagicSpring TORX® Tools

- Laser welded assembly
- Holds screws securely
- Won't damage screws
- Doesn't weaken tool
- Exact fit tips
- Hardened tool steel blades
- Holds standard Torx screws*

Screw Holding TORX®



Stainless Rotary Spring

Laser Welded MagicSpring Assembly



362 MagicSpring Screw Holding TORX® Driver, With Wiha-

SoftFinish® Handle Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36202	T6	60	2.4	3.5	.139	164	6.5	.07	10
36203	T7	60	2.4	3.5	.139	164	6.5	.07	10
36207	T8	60	2.4	3.5	.139	164	6.5	.07	10
36234	T9	60	2.4	4.0	.157	171	6.7	.11	10
36244	T10	80	3.1	4.0	.157	191	7.5	.11	10
36249	T15	80	3.1	4.0	.157	191	7.5	.11	10
36254	T20	100	3.9	4.0	.157	211	8.3	.16	10
36256	T25	100	3.9	4.5	.177	211	8.3	.17	10
36257	T27	115	4.5	5.5	.216	233	9.2	.20	10
36258	T30	115	4.5	6.0	.236	233	9.2	.21	10

267 MagicSpring Screw Holding TORX® Driver, With Wiha-

Precision PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-Pico Finish precision handle, molded on, soft grips.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
26721	T6	40	1.6	140	5.5	.03	10
26723	T7	40	1.6	140	5.5	.03	10
26725	T8	40	1.6	140	5.5	.03	10
26727	T9	50	2.0	150	5.9	.04	10
26729	T10	50	2.0	150	5.9	.04	10
26731	T15	60	2.4	160	6.3	.04	10



36290 Set 6 Pcs. MagicSpring Screw Holding TORX® SoftFinish Screwdrivers Round blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Chromtop finish on tips. Wiha-SoftFinish® handle, multi-component, cushion grips. Molded on.

Item No.	Size	mm	Size	mm	lbs.
36290	36207 T8	60	36254 T20	100	.98
	36244 T10	80	36256 T25	100	
	36249 T15	80	36258 T30	115	

26798 Set 6 Pcs. MagicSpring Screw Holding TORX®

Screwdriver, With Wiha-Precision PicoFinish Handle Blade high alloy CVM steel, hardened, hard chromed. Molded on ergonomic Wiha-Pico Finish precision handle, molded on, soft grips.

Item No.	Size	mm	Size	mm	lbs.
26798	26721 T6	40	26727 T9	50	.45
	26723 T7	40	26729 T10	50	
	26725 T8	40	26731 T15	60	

*MagicSpring tools will hold Torx® screws made to CamCar Textron Torx® specifications

Wiha MagicSpring TORX® Tools



371 MagicSpring Screw Holding TORX® L-key, Long Arm

High alloy chrome-vanadium-molybdenum steel, hardened, black finish.

Item No.	Size	mm	Inch	lbs.	pkg.
37106	T6	14	.55	.001	10
37107	T7	16	.63	.002	10
37108	T8	18	.71	.003	10
37109	T9	19	.75	.005	10
37110	T10	21	.83	.007	10
37115	T15	22	.87	.009	10
37120	T20	25	.98	.01	10
37125	T25	28	1.1	.02	10
37127	T27	30	1.2	.03	10
37130	T30	34	1.3	.04	10
37140	T40	36	1.4	.07	10



37190 MagicSpring Long Arm Screw Holding TORX® Set, 7 Pc. in Plastic Holder

Equipped with T6, T7, T8, T9, T10, T15, T20

Item No.	lbs.	pkg.
37190	.20	1



37192 MagicSpring Long Arm Screw Holding TORX® Set, 10 Pc. in Plastic Holder

Equipped with T6, T7, T8, T9, T10, T15, T20, T25, T27, T30

Item No.	lbs.	pkg.
37192	.35	1

Wiha MagicSpring TORX® Tools



365 MagicSpring Screw Holding TORX® driver, With Wing Handle

Ideal for use with indexable carbide tooling and also for working in confined spaces. Blade high alloy CVM steel, hardened, black finish. Wing handle high quality plastic, impact resistant. Molded on.

Item No.	Size	mm	Inch	mm	Inch	mm	Inch	lbs.	pkg.
36556	T6	35	1.4	70	2.7	40	1.6	.01	10
36557	T7	35	1.4	70	2.7	40	1.6	.02	10
36558	T8	40	1.6	75	3.0	40	1.6	.02	10
36559	T9	40	1.6	75	3.0	40	1.6	.02	10
36560	T10	40	1.6	75	3.0	40	1.6	.02	10
36561	T15	45	1.8	80	3.1	40	1.6	.02	10
36562	T20	45	1.8	80	3.1	40	1.6	.02	10



36598 MagicSpring Screw Holding TORX® Wing Handle Set, 7 Pc. in Metal Stand

Equipped with T6, T7, T8, T9, T10, T15, T20 .36 lbs.



Screw Holding TORX® Tools

Wiha TorqueControl Screwdrivers


Molded cushion grip two component handles allow for maximum achievable torque to be reached with comfort

Precise repeatability!

All TorqueVario tools are tested and comply with:

- EN ISO 6798
- BS EN 26789
- ASME B107.14M

Each tool has unique serial number and certificate of calibration



TorqueVario models include torque setting adjustment tool

and Micro Bit holder

See 4mm Micro Bits on Page 28

Direct Reading Scale



+/-6% accuracy tolerance
Certificate of calibration

285 Adjustable TorqueVario With Direct Reading Scale

EN ISO 6798, BS EN 26789, ASME B107.14M. Ergonomic molded multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible and perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

Item No.	Range				
	Inch lbs.	Increments	mm	lbs.	pkg.
28501	15 - 80 (in/oz)	2.5 Inch oz	122 - 127	.22	1
28502	5 - 10	.2 Inch lbs	122 - 127	.41	1
28504	7.5 - 20	.5 Inch lbs	126 - 131	.50	1
28506	10 - 50	2 Inch lbs	133 - 138	.59	1
28508	20 - 70	2 Inch lbs	137 - 142	.74	1

Above includes Micro Bit Holder 28583

See 4mm Micro Bits on Page 28

* +/- 10% (This unit only)



+/-6% accuracy tolerance
Certificate of calibration

285 Adjustable TorqueVario-S Handle - In Newton Meter Scale

EN ISO 6798, BS EN 26789, ASME B107.14M. Ergonomic molded multi-component handle, light and compact. Handle sizes proportioned to optimize torque range. Audible and perceptible click when the torque setting has been attained, automatically resets for next torque cycle.

Item No.	Newton Meter Scale	Increments	mm	lbs.	pkg.
28550	0.1 - 0.6 Nm	.02 Nm	122 - 127	.35	1
28551	0.4 - 1.0 Nm	.05 Nm	122 - 127	.35	1
28552	0.8 - 2.0 Nm	.05 Nm	126 - 131	.45	1
28553	1.0 - 5.0 Nm	.20 Nm	133 - 138	.55	1
28554	2.0 - 8.0 Nm	.25 Nm	137 - 142	.70	1

* +/- 10% (This unit only)



285 TORX® Interchangeable Blades For TorqueFix & TorqueVario

TORX® tip blades on narrow 5/32 Hex shafts. High alloy chrome-vanadium-molybdenum steel, hardened, satin hard chrome finish.

Item No.	Size	mm	mm	lbs.	Nm	pkg.
28561	T5	175	4.0	.07	0.4	1
28562	T6	175	4.0	.07	0.6	1
28563	T7	175	4.0	.07	0.9	1
28564	T8	175	4.0	.07	1.3	1
28565	T9	175	4.0	.07	2.5	1
28566	T10	175	4.0	.07	3.5	1
28567	T15	175	4.0	.07	5.5	1
28568	T20	175	4.0	.07	8.0	1
28569	T25	175	4.0	.07	8.0	1



285 TORXPlus® Blades For TorqueFix & TorqueVario

TORXPlus® tip blades on narrow 5/32 Hex shafts.

Item No.	Size	mm	mm	lbs.	Nm	pkg.
28571	IP5	175	4.0	.07	0.5	1
28572	IP6	175	4.0	.07	0.8	1
28573	IP7	175	4.0	.07	1.3	1
28574	IP8	175	4.0	.07	2.0	1
28575	IP9	175	4.0	.07	3.0	1
28576	IP10	175	4.0	.07	4.5	1
28577	IP15	175	4.0	.07	6.6	1
28578	IP20	175	4.0	.07	8.0	1
28579	IP25	175	4.0	.07	8.0	1



285 MagicSpring TORX® Interchangeable Blades For TorqueFix & TorqueVario blades on narrow 5/32 Hex shafts.

Item No.	Size	mm	mm	lbs.	Nm	pkg.
28512	T6	175	4.0	.07	0.6	1
28527	T7	175	4.0	.07	0.9	1
28528	T8	175	4.0	.07	1.3	1
28529	T9	175	4.0	.07	2.5	1
28530	T10	175	4.0	.07	3.8	1
28531	T15	175	4.0	.07	5.5	1
28532	T20	175	4.0	.07	8.0	1
28533	T25	175	4.0	.07	8.0	1



Screw Holding



286 MagicSpring TORXPlus® Interchangeable Blades For TorqueFix & TorqueVario blades on narrow 5/32 Hex shafts.

Item No.	Size	mm	mm	lbs.	Nm	pkg.
28611	IP6	175	4.0	.07	0.8	1
28612	IP7	175	4.0	.07	1.3	1
28613	IP8	175	4.0	.07	2.0	1
28614	IP9	175	4.0	.07	3.0	1
28616	IP10	175	4.0	.07	4.5	1
28617	IP15	175	4.0	.07	6.6	1
28618	IP20	175	4.0	.07	8.0	1
28619	IP25	175	4.0	.07	8.0	1



Screw Holding

Wiha Easy Torque Handles



- Audible Click At Torque
- Replaceable Blades
- +/- 10% Repeatability
- Improve Productivity
- Reduces Waste
- Controls Costs
- Save Time!

292 Easy Torque Screwdriver Handle

Easy Torque value pre-set. Release accuracy +/- 10%.
SoftFinish cushion grip handle for good power transfer.

Item No.	Pre-Sets					
	Inch/lbs.	Nm	mm	Inch	lbs.	pkg.
29205	4.4	0.5	137	5.4	.20	1
29206	5.3	0.6	137	5.4	.20	1
29209	8.0	0.9	137	5.4	.20	1
29211	9.7	1.1	137	5.4	.20	1
29212	10.6	1.2	137	5.4	.20	1
29214	12.4	1.4	137	5.4	.20	1
29220	17.7	2.0	137	5.4	.20	1
29225	22.1	2.5	137	5.4	.20	1
29230	26.6	3.0	137	5.4	.20	1
29238	33.6	3.8	137	5.4	.20	1
29241	35.4	4.0	137	5.4	.20	1
29245	39.8	4.5	137	5.4	.20	1
29251	44.2	5.0	137	5.4	.20	1

* No Calibration Certificates

ESD Safe Adjustable TorqueControl Tools

Handle sizes proportioned
to optimize torque range



Includes Certificate

285 ESD Safe TorqueVario-S, With Window Scale

EN ISO 6798, BS EN 26789, ASME B107.14M, +/- 6% Accuracy
Ergonomic multi-component handle, light and compact.
Audible and perceptible click when torque setting has been attained.

Item No.	Range				
	Inch lbs.	Increments	mm	lbs.	pkg.
28522*	15 - 80(in/oz)	2.5 Inch oz	122 - 127	.33	1
28524	5 - 10	.2 Inch lbs	122 - 127	.34	1
28526	7.5 - 20	.5 Inch lbs	126 - 131	.42	1

* +/- 10% (This unit only)



288 ESD Safe TORX® Interchangeable Blades For

TorqueVario-S TORX® tip blades on narrow 5/32" Hex shafts. High alloy chrome-vanadium-molybdenum steel, hardened, hard chromed.

Item No.	Size	mm	mm	lbs.	Nm	pkg.
28825	T5	175	4.0	.07	0.4	1
28826	T6	175	4.0	.07	0.6	1
28827	T7	175	4.0	.07	0.9	1
28828	T8	175	4.0	.07	1.3	1
28829	T9	175	4.0	.07	2.5	1
28830	T10	175	4.0	.07	3.8	1

Wiha Insulated TorqueControl Tools



1000V

Includes Certificate

287 Insulated TorqueVario-S, With Window Scale Insulation

up to 1000 Volt. EN ISO 6798, BS EN 26789, ASME B107.14M, VDE, ASTM F-1505-01 & NFPA70E, +/- 6% Accuracy. Handle sizes proportioned to optimize torque range. Audible and perceptible click when torque setting has been attained. Includes *SlimLine* blade holder.

Item No.	Range				
	Inch lbs.	Increments	mm	lbs.	pkg.
28724	7.5 - 20	.5 Inch lbs	126 - 131	.43	1
28726	10 - 50	2 Inch lbs	133 - 138	.40	1
28727	20 - 70	2 Inch lbs	137 - 142	.69	1

Each TorqueVario handle has unique serial number and certificate of calibration

287 Insulated TorqueVario-S Handle - In Newton Meter Scale

Includes *SlimLine* blade holder.

Item No.	Range				
	Nm	mm	lbs.	pkg.	
28734	0.6 - 2.0	131	.45	1	
28736	1.0 - 5.0	138	.45	1	
28737	2.0 - 8.0	142	.72	1	

Each TorqueVario handle has unique serial number and certificate of calibration



283 Insulated TORX® SlimLine Blades

High quality CV steel, through hardened. *SlimLine* blades have up to 33% narrower insulation diameter then standard insulated tools.

Item No.	Size	mm	Dia.	Length	Max Nm	Inch/ lbs.	lbs.	Pkg.
28339	T8	90	4.1	2.8"	1.3	11.5	.02	1
28340	T10	90	4.1	2.8"	3.8	33.7	.02	1
28341	T15	90	6.1	2.8"	5.5	48.8	.02	1
28342	T20	90	6.1	2.8"	5.5	48.8	.02	1

TorqueControl Tools



With Certificate
of Calibration

28597 Set 8 Pc. TorqueControl Set With **TORX**® Blades

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M

TORX®: T7, T8, T9, T10, T15, T20



lbs.

1.01

28597 28506 Handle Range 10 - 50 Inch lbs.



With Certificate
of Calibration

28598 Set 8 Pc. TorqueControl Set With **TORXPlus**® Blades

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M

TORXPlus®: IP7, IP8, IP9, IP10, IP15, IP20



lbs.

1.00

28506 Handle Range 10 - 50 Inch lbs.



With Certificate
of Calibration

28599 14 Pc. TorqueControl Set With **TORX**® & **TORXPlus**® Blades

Certified to EN ISO 6798, BS EN 26789, ASME B107.14M. Set includes Ergonomic multi-component adjustable TorqueVario-S handle, 12 blades & Torque adjustment tool. Packed in a durable canvas pouch.

Item No.

28599 **TORX**®: T7, T8, T9, T10, T15, T20

TORXPlus®: IP7, IP8, IP9, IP10, IP15, IP20

28506 - Handle Range 10 - 50 Inch lbs.



lbs.

1.25

With Certificate of Calibration



With Certificate
of Calibration

Certified to
EN ISO 6798,
BS EN 26789,
ASME B107.14M

28690 Set 8 Pc. TorqueControl Set With MagicSpring **TORX**® Screw Holding Blades

28690 MagicSpring **TORX**®:

T7, T8, T9, T10, T15, T20

28506 Handle Range 10 - 50 Inch lbs.



lbs.

1.00

T-handle TorqueControl Tools



Includes
Calibration
Certificate

Ergonomic multi-component
handle, light and compact.



289 TorqueFix T-handle

EN ISO 6798, BS EN 26789, ASME B107.14M, +/- 6% Accuracy.

Item No.	Torque In-lbs.	Torque Nm	mm x mm	lbs.	pkg.
28931	53.1	6	56 x 120	.81	1
28933	70.8	8	56 x 120	.82	1
28935	88.5	10	56 x 120	.79	1
28937	106.2	12	56 x 120	.79	1
28938	110.6	12.5	56 x 120	.80	1
28939	123.9	14	56 x 120	.80	1

28940 Adjustable TorqueVario STplus T-handle

Item No.	Torque In-lbs.	Torque Nm	mm x mm	lbs.	pkg.
28940	44.3-123.9	5-14	56 x 120	.81	1

* (1 Nm 8.8507)



289 **TORX**® Interchangeable Blades For TorqueFix T-Handle

TORX® tip blades on 6mm Hex shafts.

Item No.	Size	mm	Inch	mm	lbs.	pkg.
28903	T15	130	5.1	6.0	.07	1
28904	T20	130	5.1	6.0	.07	1
28905	T25	130	5.1	6.0	.07	1
28906	T27	130	5.1	6.0	.07	1
28907	T30	130	5.1	6.0	.07	1
28908	T40	130	5.1	6.0	.07	1



289 **TORXPlus**® Interchangeable Blades For TorqueFix

TORXPlus® T-Handle tip blades on 6mm Hex shafts.

Item No.	Size	mm	Inch	mm	lbs.	pkg.
28910	IP15	130	5.1	6.0	.07	1
28911	IP20	130	5.1	6.0	.07	1
28912	IP25	130	5.1	6.0	.07	1
28913	IP27	130	5.1	6.0	.07	1
28914	IP30	130	5.1	6.0	.07	1
28915	IP40	130	5.1	6.0	.07	1

Precision ESD Safe TORX® Drivers



278 TORX® Screwdriver, With Precision ESD Safe Dissipative

Handle Blade high alloy CVM steel. Hard chrome finished. Handle impact resistant, dissipative material. ESD standard IEC 61340-5-1

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
27801	T1	40	1.6	120	4.7	.03	10
27802	T2	40	1.6	120	4.7	.03	10
27803	T3	40	1.6	120	4.7	.03	10
27804	T4	40	1.6	120	4.7	.03	10
27805	T5	40	1.6	120	4.7	.03	10
27811	T6	40	1.6	120	4.7	.03	10
27817	T7	40	1.6	120	4.7	.03	10
27823	T8	40	1.6	120	4.7	.03	10
27829	T9	50	2.0	145	5.7	.04	10
27835	T10	50	2.0	145	5.7	.04	10
27841	T15	60	2.4	170	6.7	.07	10
27847	T20	60	2.4	170	6.7	.07	10

*Metric dimensions actual - Inch dimensions approximate



27890 Set 7 Pcs. TORX® Precision ESD Safe Dissipative Handle

Blade high alloy CVM steel, hardened, hard chromed. **Handle** manufactured from impact resistant, dissipative material.

Item						
No.	Size	mm	Size	mm	lbs.	
27890	27804 T4	40	27823 T8	40	.31	
	27805 T5	40	27829 T9	50		
	27811 T6	40	27835 T10	50		
	27817 T7	40				



27899 Set 8 Pcs. TORX® Precision ESD Safe Dissipative

Handle Set In Pouch Blade high alloy CVM steel, hardened, hard chromed. Handle impact resistant, dissipative material.

Item					
No.	Size	mm	Size	mm	lbs.
27899	27801 T1	40	27805 T5	40	.30
	27802 T2	40	27806 T6	40	
	27803 T3	40	27807 T7	40	
	27804 T4	40	27920 Chip Lifter		

Precision ESD Safe TORXPlus® Drivers



278 TORXPlus® Driver, With Precision ESD Safe Dissipative

Handle Blade high alloy CVM steel, hardened, hard chromed. Handle impact resistant, dissipative material. ESD standard IEC 61340-5-1

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
27850	IP4	40	1.6	120	4.7	.03	10
27851	IP5	40	1.6	120	4.7	.03	10
27852	IP6	40	1.6	120	4.7	.03	10
27853	IP7	40	1.6	120	4.7	.03	10
27854	IP8	40	1.6	120	4.7	.03	10
27855	IP9	50	2.0	145	5.7	.04	10
27856	IP10	50	2.0	145	5.7	.04	10
27857	IP15	60	2.4	170	6.7	.07	10

*Metric dimensions actual - Inch dimensions approximate



27894 Set 7 Pcs. TORXPlus® Precision ESD Safe Dissipative

Handle Blade high alloy CVM steel, hardened, hard chromed.

Item						
No.	Size	mm	Size	mm	lbs.	
27894	27851 IP5	40	27855 IP9	50	.32	
	27852 IP6	40	27856 IP10	50		
	27853 IP7	40	27857 IP15	60		
	27854 IP8	40				

Wiha TORX® Precision Series



26799 Set 8 Pcs. TORX® Drivers In Canvas Pouch

Blade high alloy chrome-vanadium-molybdenum steel. Hard chrome finished. In storage pouch

Item						
No.	Size	mm	Size	mm	lbs.	
26799	26703 T3	40	26707 T7	40	.50	
	26704 T4	40	26708 T8	40		
	26705 T5	40	26709 T9	50		
	26706 T6	40	26710 T10	50		

Wiha TORX® Precision Series

267 TORX® Screwdriver, With Precision Handle

Blade high alloy chrome-vanadium-molybdenum steel.

Item No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
26701	T1	40	1.6	120	4.7	.01	10
26702	T2	40	1.6	120	4.7	.02	10
26703	T3	40	1.6	120	4.7	.02	10
26704	T4	40	1.6	120	4.7	.02	10
26705	T5	40	1.6	120	4.7	.02	10
26706	T6	40	1.6	120	4.7	.02	10
26707	T7	40	1.6	120	4.7	.02	10
26708	T8	40	1.6	120	4.7	.03	10
26709	T9	50	2.0	145	5.7	.03	10
26710	T10	50	2.0	145	5.7	.03	10
26715	T15	60	2.4	170	6.7	.05	10
26720	T20	60	2.4	170	6.7	.05	10

*Metric dimensions actual - Inch dimensions approximate

Wiha Pico Soft Grip TORX®

267 TORX® Screwdriver, With Precision Soft PicoFinish

Handle Blade high alloy chrome-vanadium-molybdenum tool steel, hardened, hard chrome finish.

Item No.	Size	mm	Inch	mm	Inch	pkg.
26732	T1	40	1.6	134	5.3	10
26733	T2	40	1.6	134	5.3	10
26735	T3	40	1.6	134	5.3	10
26736	T4	40	1.6	134	5.3	10
26737	T5	40	1.6	134	5.3	10
26739	T6	40	1.6	140	5.5	10
26741	T7	40	1.6	140	5.5	10
26743	T8	40	1.6	140	5.5	10
26745	T9	50	2.0	150	5.9	10
26747	T10	50	2.0	150	5.9	10
26749	T15	60	2.4	160	6.3	10
26751	T20	60	2.4	160	6.3	10

*Metric dimensions actual - Inch dimensions approximate


26790 Set 6 Pcs. TORX® Driver

Blade high alloy CVM steel.

Item No.	Size	mm	lbs.
26790	26706 T6	40	.25
	26707 T7	40	
	26708 T8	40	
	26709 T9	50	
	26710 T10	50	
	26715 T15	60	


26793 Set 8 Pcs. TORX® Precision Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.	Size	mm	lbs.
26793	26732 T1	40	.50
	26733 T2	40	
	26735 T3	40	
	26736 T4	40	
	26737 T5	40	
	26739 T6	40	
	26741 T7	40	
	26743 T8	40	


26791 Set 8 Pcs. TORX® Screwdriver Set

Item No. 26791 T1, T2, T3, T4, T5, T6, T7, T8


26796 Set 8 Pcs. TORX® Precision Soft PicoFinish Handle

Blade high alloy CVM steel, hardened, hard chromed. ChromTop finish on tip for a perfect fit. In storage pouch

Item No.	Size	mm	lbs.
26796	26737 T5	40	.57
	26739 T6	40	
	26741 T7	40	
	26743 T8	40	
	26745 T9	50	
	26747 T10	50	
	26749 T15	60	
	26751 T20	60	


26792 Set 7 Pcs. TORX® Driver

Blade high alloy CVM steel.

Item No.	Size	mm	lbs.
26792	26705 T5	40	.27
	26706 T6	40	
	26707 T7	40	
	26708 T8	40	
	26709 T9	50	
	26710 T10	50	
	26715 T15	60	

Wiha SYSTEM 4 Handle, Bits & Sets

SYSTEM 4 Handles & Micro Bits

Tips

Exact fit,
precision
machined

Rotating Cap

for precise
turning & control

Tapered Handle

allows rapid rotation,
requires less clearance.
Static Dissipative
10⁶ - 10⁹ ohms

Bits CVM steel,
hardened

Use bits directly in handle or with 4" bit extension



High alloy CVM steel,
hardened, on 4 mm stock

757 SYSTEM 4 TORX® Micro Bits

Item No.	Size	mm	Inch	lbs.
75703	T3	28	1.1	.01
75704	T4	28	1.1	.01
75705	T5	28	1.1	.01
75706	T6	28	1.1	.01
75707	T7	28	1.1	.01
75708	T8	28	1.1	.01
75709	T9	28	1.1	.01
75710	T10	28	1.1	.01
75715	T15	28	1.1	.01
75720	T20	28	1.1	.01



High alloy CVM steel,
hardened, on 4 mm stock

757 SYSTEM 4 Security TORX® Micro Bits

Item No.	Size	mm	Inch	lbs.
75727	T7s	28	1.1	.01
75728	T8s	28	1.1	.01
75729	T9s	28	1.1	.01
75735	T10s	28	1.1	.01
75739	T15s	28	1.1	.01
75742	T20s	28	1.1	.01



75801 SYSTEM 4 ESD Safe Dissipative Precision Bit Handle with rotating control cap. For Wiha Micro Bits.

Advantages:

- For working in ESD sensitive applications
- Surface resistant 10⁶-10⁹ Ohms
- Ball retainer holds bits securely in place
- Accepts all SYSTEM 4 Series bits
- 110mm/4.3" OAL



Item No.	mm	Inch	mm	Inch	lbs.
75801	4.0	.1574	14.0	.55	.06

75792 SYSTEM 4 TORX® Precision Interchangeable Bit Set, 11 Pcs. In Compact Fold Out Box

Set includes your choice of Wiha precision handle, bit extension and 9 Wiha interchangeable bits.

Item SYSTEM 4

No. TORX® Bit Sets

75792 Set with ESD Safe Precision Handle 
Set includes the following bits:

TORX® Sizes:

T3, T4, T5, T6, T7, T8, T9, T10, T15

100mm Bit Extension

 lbs. .64



11 Pc. Set



75093 SYSTEM 4 Slotted, Phillips, TORX® Compact ESD Precision Interchangeable Bit Set, 16 Pcs.

Item No. Combination Bit Set

75093 Set with Standard Precision Handle 

  Slotted: 1.5, 2.0, 2.5, 3.0mm

 Phillips: 00, 0, 1

 TORX®: T6, T7, T8, T9, T10, T15, T20

 100mm Bit Extension

 lbs. .17



75985 Micro Bit Handle Storage TORX® Bit Set, 7 Pcs.

Wiha precision storage handle & 6 interchangeable bits.

Item No. Set with Precision Storage Handle

75985  TORX®: T3, T4, T5, T6, T7, T8

 lbs. .08

ESD Safe Precision Handles & Blades



28000 ESD Safe Dissipative Precision Handle with rotating control cap. Surface resistant 10^6 - 10^9 Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Tapered handle, high quality plastic, impact resistant. Ball retainer hold. 110mm/4.3" OAL

Item No.	mm	Inch	mm	Inch	lbs.
28000	4.0	.1574	14.0	.55	.04



28001 ESD Safe Dissipative Precision Adjustable Handle with rotating control cap.

- Use in ESD sensitive applications. Surface resistant 10^6 - 10^9 Ohms.
 - Collet lock allows for quick & easy adjustment.
 - Holds blade securely in place. Accepts all SYSTEM 4 blades.
- 110mm/4.3" OAL

Item No.	mm	Inch	mm	Inch	lbs.
28001	4.0	.1574	14.0	.55	.04



269 SYSTEM 4 TORX Reversible Blade

High alloy CVM steel, hardened, vapor chrome protected, Wiha vapor Chrome-Top finish on tips. 120mm/4.7" OAL.

Item No.	Size	Size	lbs.
26951	T6 + T8		.03
26952	T7 + T9		.03
26953	T10 + T15		.03
26954	T15 + T20		.03



269 SYSTEM 4 TORX Interchangeable Blade High alloy CVM steel, hardened, Wiha chrome-Top finish on tips. 120mm/4.7" OAL

Item No.	Size	lbs.
26955	T3	.03
26956	T4	.03
26957	T5	.03



28087 TORX Precision Interchangeable Blade Set, 8 Pcs. Wiha ESD Safe precision collet lock handle & 7 Wiha blades.

28087 Set includes the following blades:

TORX Sizes on standard blades: T3, T4, T5

TORX Sizes on reversible blades:

T6, T7, T8, T9, T10, T15, T20

lbs. .31



TORX ESD Safe SYSTEM 4 Blade Sets



26995 TORX Precision Interchangeable Blade Set, 5 Pcs. Wiha ESD Safe precision collet lock handle & 4 interchangeable blades.

26995 Set includes the following blades:

TORX Sizes:

T6, T7, T8, T9, T10, T15, T20

lbs. .54



26987 TORX Precision Interchangeable Blade Set, 8 Pcs. Wiha ESD Safe precision collet lock handle and 7 interchangeable blades.

26987 Set includes the following blades:

TORX Sizes-standard blades: T3, T4, T5

TORX Sizes-reversible blades:

T6, T7, T8, T9, T10, T15, T20

lbs. .53



ESD Safe SYS 4 Drive-Loc Handle & Blades



26961 ESD Safe Dissipative Precision Drive-Loc Handle

Surface resistant 10^6 - 10^9 Ohms. 4 mm hex retainer for all SYSTEM 4 interchangeable blades. Ball retainer hold. 110mm/4.3" OAL

Item No.	mm	Inch	mm	Inch	lbs.
26961	4.0	.1574	23	.91	.08



269 SYSTEM 4 TORX Drive-Loc Reversible Blades

Item No.	Size	Size	lbs.
26977	T1 + T2		.03
26978	T3 + T4		.03
26979	T5 + T6		.03
26980	T6 + T8		.03
26981	T7 + T9		.03
26982	T10 + T15		.03


Wiha CushionGrip Stubby Bit Holders



38045 TORX® SoftFinish® CushionGrip Stubby Bit Holder
with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

★ **TORX®** Sizes: T8, T10, T15, T20, T25, T30 lbs. .20



38047 Security TORX® SoftFinish® CushionGrip Stubby Bit Holder
with Wiha cushion grip handle and CVM tool steel shaft.

Set includes the following 1/4" bits:

★ **Security TORX®** Sizes: lbs.
T8s, T10s, T15s, T20s, T25s, T30s .20



28103 1/4" Magnetic Bit Holder With Wiha SoftFinish® Stubby Handle
Works in confined spaces. Stainless steel with strong magnet.

Item					
No.	Inch	mm	Inch	lbs.	pkg.
28103	1/4"	57	2.2	.11	1


Wiha Topra Ratchet Handle Sets



28295 TORX® Topra Ratchet Bit Set, 12 Pcs.

Set Includes Topra Handle, Magnetic Bit Holder & The Following Bits: lbs.

★ **TORX®** Sizes: T7, T8, T9, T10, T15, T20, T25, T27, T30, T40 .65



28297 Security TORX® Topra Ratchet Bit Set, 12 Pcs.

Set Includes Topra Handle, Magnetic Bit Holder & The Following Bits: lbs.

★ **Security TORX®** Sizes: .65
T7s, T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s

Wiha BitFlip Bit Set

BitFlip Standard



38028 TORX® BitFlip Standard

with Wiha cushion grip handle and insulated shaft.

Set includes the following 1/4" bits:

★ **TORX®** Sizes: T8, T10, T15, T20, T25, T27, T30, T40 lbs. .44

Wiha Multi-Bit Screwdriver Sets



38003 TORX® Multi-Bit Screwdriver with Wiha Powerhandle

Set includes the following 1/4" bits:

★ **TORX®** Sizes: lbs.
T5, T6, T7, T8, T9, T10 .36

38004 TORX® Multi-Bit Screwdriver with Wiha Powerhandle

Set includes the following 1/4" bits:

★ **TORX®** Sizes: lbs.
T8, T9, T10, T15, T20, T25 .36

38008 TORX® Multi-Bit Screwdriver with Wiha Powerhandle

Set includes the following 1/4" bits:

★ **TORX®** Sizes: lbs.
T10, T15, T20, T25, T30, T40 .36



38009 Security TORX® Screwdriver With Wiha Powerhandle

Set includes the following 1/4" bits:

★ **Security TORX®** Sizes: lbs.
T7s, T8s, T9s, T10s, T15s, T20s .36

38010 Security TORX® Screwdriver With Wiha Powerhandle

Set includes the following 1/4" bits:

★ **Security TORX®** Sizes: lbs.
T10s, T15s, T20s, T25s, T30s, T40s .36

(bits not included)



38015 1/4" Magnetic Bit Holder, Cavity holds up to 6 bits.

Item							
No.	Size	mm	Inch	mm	Inch	lbs.	pkg.
38015	1/4"	120	4.7	230	9.0	.25	1

Wiha Insert Bit Selectors



79242 Bit-Selector With **TORX**® Bits

Set includes magnetic 1/4" bit holder lbs.

✱ **TORX**® Sizes: T5, T6, T7, T8, T9, T10, T15, T20, T25, T30 .32

79245 Bit-Selector With **TORX**® Bits

Set includes magnetic 1/4" bit holder lbs.

✱ **TORX**® Sizes: T7, T8, T9, T10, T15, T20, T25, T27, T30, T40 .32



79247 Bit-Selector With Security **TORX**® Bits

Set includes magnetic 1/4" bit holder lbs.

✱ Security **TORX**® Sizes: T7s, T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s .32

70190 Bit-Selector With Security **TORX**® Bits

Set includes the following 7 bits: lbs.

✱ Security **TORX**® Sizes: T7s, T8s, T9s, T10s, T15s, T20s, T25s .21



71690 Bit-Selector With **TORXPlus**® Bits

Set includes magnetic 1/4" bit holder lbs.


✱ **TORXPlus**® Sizes: IP7, IP8, IP9, IP10, IP15, IP20, IP25, IP27, IP30, IP40 .31

71692 Bit-Selector With **TORXPlus**® Bits

Set includes magnetic 1/4" bit holder lbs.

✱ **TORXPlus**® Sizes: IP3, IP4, IP5, IP6, IP7, IP8, IP9, IP10, IP15, IP20 .31


Wiha Power Bit Belt Packs



74985 Power Bit Belt Pack With **TORX**® Bits

Set includes the following 10 bits: lbs.

✱ **TORX**® Sizes: T6, T7, T8, T9, T10, T15, T20, T25, T27, T30 .28



74981 Power Bit Belt Pack With **TORX**® Align Bits

Set includes the following 10 bits: lbs.

✱ **TORX**® Sizes: T6, T7, T8, T9, T10, T15, T20, T25, T27, T30 .28



74987 Power Bit Belt Pack With Security **TORX**® Bits

Set includes the following 10 bits: lbs.

✱ Security **TORX**® Sizes: T7s, T8s, T9s, T10s, T15s, T20s, T27s, T25s, T30s, T40s .29



74982 Power Bit Belt Pack With **TORXPlus**® Bits

Set includes the following 10 bits: lbs.

✱ **TORXPlus**® Sizes: IP6, IP7, IP8, IP9, IP10, IP15, IP20, IP25, IP30 .28

Wiha XSelector Bit Sets



Easy bit
access with
hinged cover



Includes Clicfix quick release holder

- 79445 XSelector Bit Set With TORX® Bits**  lbs.
Set Includes Quick Release Holder
and the following 10 bits: .29
- TORX® Sizes:** T7, T8, T9, T10, T15, T20, T25, T27, T30, T40



XSelector Pocket Sized
3 1/8" x 2 1/8" x 1/2"

- 79447 XSelector Bit Set With Security TORX® Bits**  lbs.
Set Includes Quick Release Holder
and the following 10 bits: .27
- Security TORX® Sizes:** T7s, T8s, T9s, T10s, T15s, T20s, T25s, T27s, T30s, T40s

Wiha Insert PokitPaks



- 71195 PokitPak - TORX® Insert Bits In Molded Case -**
Set includes 6 - 1/4" Insert Bits & Magnetic Bit Holder
- TORX®:**  lbs.
T8, T10, T15, T20, T25, T30 .15



- 79283 PokitPak TORX® Align Coated Insert Bits In Molded Case -**
Set Includes 6 - 1/4" Insert Bits
- TORX® Align:**
T10, T15, T20, T25, T30, T40
-  lbs. .12

Wiha 1/4" Bit Holders



Magnetic

- 384 1/4" Magnetic Bit Holding Screwdrivers, With Wiha-SoftFinish® Handle** Ergonomic cushion grip, magnetic, holds bit and screw. Retainer out of stainless steel. Shaft CVM steel, nickel-plated.

Item						
No.	Size	mm	Inch	mm	Inch	lbs. pkg.
38450	1/4"	125	5.0	240	9.46	.23 1
38460	1/4"	300	11.8	400	15.69	.37 1



Adjustable Blade Length
Magnetic Bit Holder

- 28489 Drive-Loc VI Bit Holder**
High alloy CVM steel, through hardened, hard chrome finish.
Wiha-SoftFinish® handle multi-component, cushion grips.

Item				
No.	Inch	Extends	lbs.	pkg.
28489	1/4"	1-3/4" to 4-7/8"	.36	1



- 714 ClicFix Bit Holder,**
Magnetic For Insert Bits. Quick release

Item				
No.	Size	Size	mm	Inch
71490	1/4"	1/4"	60	2.4
71491	1/4"	1/4"	75	2.9



- 71480 CentroFix Bit Holder For Power Bits**
Quick release

Item				
No.	Size	Size	mm	Inch
71480	1/4"	1/4"	60	2.3



- 71470 Auto Lock Magnetic Bit Holder, Spring Loaded Bit Ejection, 1/4" For Insert & Power Bits**

Item					
No.	Size	Size	mm	Inch	lbs.
71470	1/4"	1/4"	60	2.4	.08

Wiha Terminator TORX® Impact Bits - Insert & Power

**Up To 30X
Performance Over
Standard
Screwdriver Bits**



Impact rated bits for long life in impact applications

Provide up to 30 times impact performance over standard bits



Standard 1/4" drive - No special adaptor required

Wiha enhanced bi-material torsion zone


Precision machined exact fit tips

Wiha exclusive CVM tool steel

Guaranteed to out perform impact imposters

1/4" Drive Insert & Power Bits

768 TORX® Terminator Impact Bits, 1/4" Insert - 2 bit pack

Item No.	Size	mm	pkg.
76810	T10	29	2
76811	T15	29	2
76812	T20	29	2
76813	T25	29	2
76816	T30	29	2
76817	T40	29	2


768 TORX® Terminator Impact Bits, 1/4" Power - 2 bit pack

Item No.	Size	mm	pkg.
76853	T10	49	2
76854	T15	49	2
76855	T20	49	2
76856	T25	49	2
76858	T30	49	2
76859	T40	49	2


765 TORX® Terminator Impact Bits, 1/4" Insert - 10 Pack

Item No.	Size	mm	pkg.
76510	T10	29	10
76511	T15	29	10
76512	T20	29	10
76513	T25	29	10
76516	T30	29	10
76517	T40	29	10


765 TORX® Terminator Impact Bits, 1/4" Power - 10 Pack

Item No.	Size	mm	pkg.
76553	T10	49	10
76554	T15	49	10
76555	T20	49	10
76556	T25	49	10
76558	T30	49	10
76559	T40	49	10


76895 7 Pc. Bit Buddy Set

With Terminator Impact Insert Bits - 29mm

Set includes the following bits:

Torx®: T10, T15, T20, T25 (2), T30, T40


76896 7 Pc. Bit Buddy Set

With Terminator Impact Power Bits - 49mm

Set includes the following bits:

Torx®: T10, T15, T20, T25 (2), T30, T40

Stainless Steel 1/4" Insert & Power Bits and 1/4" Bit Holder



704 Stainless Steel **TORX**® Power Bits
1/4" Hex Drive, Length 2.0"/50mm

Item			
No.	Size	mm	pkg.
70411	T15	50	10
70413	T20	50	10
70414	T25	50	10
70416	T30	50	10
70417	T40	50	10



71494 Stainless Steel Bit Holder, 1/4"

For Insert Bits Internal C-ring for bit holding & magnet.

Item				
No.	Size	Size	mm	Inch lbs.
71494	1/4"	1/4"	54	2.1" .05



715 Stainless Steel **TORX**® Bits, 1/4"

Item			
No.	Size	mm	pkg.
71500	T8	25	10
71501	T9	25	10
71502	T10	25	10
71503	T15	25	10
71504	T20	25	10
71511	T25	25	10
71512	T30	25	10
71513	T40	25	10

Stainless Steel

High-quality, non-rusting stainless steel, completely vacuum-hardened.

Dura Torsion Insert Bits



71596 PokitPak **-TORX**® Dura Insert Bits
In Molded Case -

Set Includes 6 - 1/4" Insert Bits

	T10, T15, T20, T25, T30, T40
	lbs. .36


Dura Torsion Insert Bits

With the Dura bit Wiha has again proved it's power of innovation.

The extra hard, elastic Quattro Torsion bit is equipped with an extremely wear resistant tungsten carbide coating that grips the screw head.

Positive location in the screw head with decrease of:

- necessary pressure forces
- working time
- costs
- wear & tear of bits & screw heads
- anti-cam-out effect



715 **TORX**® Dura Bits, 1/4"

Item			
No.	Size	mm	lbs.
71574	T10	25	.02
71576	T15	25	.02
71578	T20	25	.02
71580	T25	25	.02
71582	T30	25	.02
71584	T40	25	.03

Diamond Torsion Insert Bits

Diamond bits supplement Wiha's range of high-quality special bits. When used with machines, the increased tool life of the Wiha Diamond bit reduces cost.

- High wear resistance
- Micro particle coating with sapphire and diamond contents
- Optimized torsion zone

Reduction of:

- pressure forces to be applied
- wear and tear of bit and screw head
- working time & costs
- Cam-out effect

The ideal bit even for the most difficult of applications




715 **TORX**® Diamond Bits, 1/4"

Item			
No.	Size	mm	lbs.
71516	T10	25	.02
71517	T15	25	.02
71518	T20	25	.02
71519	T25	25	.02
71521	T30	25	.02
71522	T40	25	.03

TiN Coated Insert Bits

The abbreviation TiN stands for Titanium-Nitride, which has a hardness up to 85 HRC. This coating guarantees a high wear and tear resistance.



- Tough, hard torsion quality with very hard TiN coating
- Optimized torsion zone
- High wear resistance



715 **TORX**® TiN Coated Insert Bits, 1/4"

Item			
No.	Size	mm	lbs.
71585	T5	25	.02
71586	T6	25	.02
71587	T7	25	.02
71588	T8	25	.02
71562	T9	25	.02
71563	T10	25	.02
71564	T15	25	.02
71565	T20	25	.02
71566	T25	25	.02
71569	T27	25	.02
71567	T30	25	.02
71568	T40	25	.02

TiN - Titanium Nitride

TORX® Bits

The ideal multi-purpose bits for all around quality & performance

Made in Germany - Production Quality

Highly resistant to wear and tear for a long tool life



Impact resistant modified CVM, tool steel, hardened

Suitable for all applications for both manual and machine
Hardness HRC 59-61



725 TORX® Bits, 5/16"

Item	No.	Size	mm	pkg.	lbs.
72525	T25	35	10	.27	
72527	T27	35	10	.27	
72530	T30	35	10	.27	
72540	T40	35	10	.28	
72545	T45	35	10	.31	
72550	T50	35	10	.32	
72555	T55	35	10	.52	



2 bit pack



725 TORX® Insert Bit Packs, 5/16"

Item	No.	Size	mm	lbs.
72531	T30	35	.28	
72541	T40	35	.28	
72546	T45	35	.31	
72551	T50	35	.32	
72556	T55	35	.52	



745 TORX® Power Bits

1/4" Hex Drive, Length 2.0"/50mm

Item	No.	Size	mm	pkg.	lbs.
74511	T6	50	10	.18	
74512	T7	50	10	.18	
74513	T8	50	10	.18	
74517	T9	50	10	.18	
74519	T10	50	10	.18	
74521	T15	50	10	.18	
74523	T20	50	10	.18	
74529	T25	50	10	.18	
74531	T27	50	10	.18	
74533	T30	50	10	.18	
74535	T40	50	10	.18	



745 TORX® Power Bits

1/4" Hex Drive, Length 2.75"/70mm

Item	No.	Size	mm	pkg.	lbs.
74536	T6	70	1	.02	
74538	T7	70	1	.02	
74542	T8	70	1	.02	
74544	T9	70	1	.02	
74546	T10	70	1	.02	
74548	T15	70	1	.02	
74551	T20	70	1	.03	
74553	T25	70	1	.03	
74556	T27	70	1	.04	
74558	T30	70	1	.04	
74561	T40	70	1	.04	



745 TORX® Power Bits

1/4" Hex Drive, Length 3.5"/90mm

Item	No.	Size	mm	pkg.	lbs.
74563	T6	90	10	.03	
74565	T7	90	10	.03	
74567	T8	90	10	.03	
74569	T9	90	10	.03	
74571	T10	90	10	.03	
74573	T15	90	10	.03	
74575	T20	90	10	.04	
74577	T25	90	10	.04	
74579	T27	90	10	.04	
74581	T30	90	10	.04	
74583	T40	90	10	.04	



745 TORX® Power Bits

1/4" Hex Drive, Length 6.0"/150mm

Item	No.	Size	mm	pkg.	lbs.
74586	T10	150	10	.04	
74587	T15	150	10	.04	
74588	T20	150	10	.04	
74589	T25	150	10	.04	
74590	T27	150	10	.04	
74591	T30	150	10	.04	

Wiha TORX® Bit Packs



2 bit pack

715 TORX® Insert Bit Packs

1" CVM S2 modified tool steel.

Item	No.	Size	mm	lbs.
71548	T3	25	.03	
71549	T4	25	.03	
71550	T5	25	.03	
71551	T6	25	.03	
71552	T7	25	.03	
71553	T8	25	.03	
71554	T9	25	.03	
71555	T10	25	.03	
71556	T15	25	.03	
71557	T20	25	.03	
71558	T25	25	.03	
71559	T27	25	.04	
71560	T30	25	.04	
71561	T40	25	.04	



715 TORX® Bits, 1/4"

Item	No.	Size	mm	pkg.	lbs.
71523	T3	25	10	.12	
71524	T4	25	10	.12	
71505	T5	25	10	.12	
71506	T6	25	10	.12	
71507	T7	25	10	.12	
71508	T8	25	10	.12	
71509	T9	25	10	.12	
71510	T10	25	10	.12	
71515	T15	25	10	.12	
71520	T20	25	10	.12	
71525	T25	25	10	.12	
71527	T27	25	10	.13	
71530	T30	25	10	.14	
71540	T40	25	10	.15	

725 TORX® Bits, 1/4" Bulk Packs

Item	No.	Size	mm	pkg.	lbs.
72573	T8	25	30	.36	
72575	T10	25	30	.36	
72576	T15	25	30	.36	
72577	T20	25	30	.36	
72578	T25	25	30	.36	
72579	T27	25	30	.36	
72580	T30	25	30	.36	
72581	T40	25	30	.36	

Wiha TORX® Bit Packs



71571 TORX® Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc. bit pack.

71571 Set includes the following bits:

TORX® Sizes:

T15, T20, T25, T27,
wt. .08 T30, T40 x 1" (25mm)

71570 TORX® Insert Bit Packs, 1" CVM

S2 modified tool steel. Extra hard with natural finish. Exact fit machined tips. 6 pc bit pack.

71570 Set includes the following bits:

TORX® Sizes:

T5, T6, T7, T8, T9,
wt. .07 T10 x 1" (25mm)



2 bit
pack

745 TORX® Power Bit Packs, 2"

CVM S2 modified tool steel

Item			
No.	Size	mm	lbs.
74501	T6	50	.05
74502	T7	50	.05
74503	T8	50	.05
74504	T9	50	.05
74506	T10	50	.05
74508	T15	50	.05
74510	T20	50	.05
74514	T25	50	.06
74515	T27	50	.06
74516	T30	50	.06
74518	T40	50	.06

Wiha TORX® Align Insert Bits and Power Bits

Torx® Align Tapered For Snug Fit In Screw

Highly resistant
to wear and
tear for a
long tool life



Impact resistant modified
chrome-vanadium-
molybdenum, tool steel,
hardened

**Made in Germany -
Production Quality**

Suitable for all applications
for both manual and machine
Hardness HRC 59-61



715 TORX® Align Bits, 1/4"

Item				
No.	Size	mm	pkg.	lbs.
71536	T6	25	10	.12
71537	T7	25	10	.12
71538	T8	25	10	.12
71539	T9	25	10	.12
71541	T10	25	10	.12
71542	T15	25	10	.12
71543	T20	25	10	.12
71544	T25	25	10	.13
71545	T27	25	10	.13
71546	T30	25	10	.14
71547	T40	25	10	.15

*Also Known As Torx Wedge Fit



747 TORX® Align Bits, 1/4" Hex Drive, Length 2.0"/50mm

Item				
No.	Size	mm	pkg.	lbs.
74711	T6	50	10	.18
74714	T7	50	10	.18
74717	T8	50	10	.18
74721	T9	50	10	.18
74724	T10	50	10	.18
74728	T15	50	10	.20
74732	T20	50	10	.22
74736	T25	50	10	.22
74739	T27	50	10	.22
74742	T30	50	10	.22

*Also Known As Torx Wedge Fit



2 bit
pack



2 bit
pack

Torx® Profiles



Torx®



Security
Torx®



TorxPlus®



Security
TorxPlus®



Ball End
Torx®

733 TORX® Align Insert Bit Packs, 1"

CVM S2 modified tool steel

Item			
No.	Size	mm	lbs.
73310	T6	25	.03
73311	T7	25	.03
73312	T8	25	.03
73313	T9	25	.03
73314	T10	25	.03
73315	T15	25	.03
73316	T20	25	.03
73317	T25	25	.03
73318	T27	25	.03
73319	T30	25	.03
73320	T40	25	.04

747 TORX® Align Power Bit Packs, 2"

CVM S2 modified tool steel

Item			
No.	Size	mm	lbs.
74760	T6	50	.05
74761	T7	50	.05
74762	T8	50	.05
74763	T9	50	.05
74764	T10	50	.05
74765	T15	50	.05
74766	T20	50	.06
74767	T25	50	.06
74768	T27	50	.06
74769	T30	50	.06

Wiha Security TORX® Insert Bits and Power Bits

Security Torx®

*Made in Germany -
Production Quality*



Impact resistant modified
CVM tool steel, hardened

Highly resistant
to wear and
tear for a
long tool life

Suitable for all applications
for both manual and machine
Hardness HRC 59-61



2 bit
pack


705 Security TORX® Power Bit Packs, 2"

Item No.	Size	mm	lbs.
70556	T7s	50	.07
70557	T8s	50	.07
70558	T9s	50	.07
70559	T10s	50	.07
70560	T15s	50	.07
70561	T20s	50	.07
70562	T25s	50	.07
70563	T27s	50	.07
70564	T30s	50	.07
70565	T40s	50	.07
70566	T45s	50	.07
70567	T50s	50	.07
70568	T55s	50	.07


701 Security TORX® Bits, 1/4"

Item No.	Size	mm	pkg.	lbs.
70127	T7s	25	10	.12
70128	T8s	25	10	.12
70129	T9s	25	10	.12
70135	T10s	25	10	.12
70139	T15s	25	10	.12
70142	T20s	25	10	.12
70148	T25s	25	10	.12
70160	T27s	25	10	.13
70163	T30s	25	10	.13
70168	T40s	25	10	.14



2 bit
pack


701 Security TORX® Insert Bit Packs, 1"

CVM S2 modified tool steel.

Item No.	Size	mm	lbs.
70150	T7s	25	.03
70151	T8s	25	.03
70152	T9s	25	.03
70153	T10s	25	.03
70154	T15s	25	.03
70155	T20s	25	.03
70156	T25s	25	.03
70157	T27s	25	.03
70158	T30s	25	.03
70159	T40s	25	.03



5/16"

725 Security TORX® Bits, 5/16"

Item No.	Size	mm	pkg.	lbs.
72542	T40s	35	10	.28
72547	T45s	35	10	.32
72552	T50s	35	10	.34
72557	T55s	35	10	.52



2 bit
pack


725 Security TORX® Bits, 5/16" 2 Bit Pack

Item No.	Size	mm	lbs.
72562	T40s	35	.28
72563	T45s	35	.29
72564	T50s	35	.30
72567	T55s	35	.32


Wiha Security TORXPlus® Insert Bit
716 Security TORXPlus® Insert Bits, 1/4" Hex, 1" OAL

Item No.	Size	mm	pkg.	lbs.
71648	IPR8	25	1	.11
71650	IPR10	25	1	.11
71652	IPR15	25	1	.11
71654	IPR20	25	1	.12
71656	IPR25	25	1	.13
71657	IPR27	25	1	.13
71658	IPR30	25	1	.14
71660	IPR40	35	1	.14



XSelector
Pocket Sized
3 1/8" x 2 1/8" x 1/2"

79450 XSelector Bit Set With Security TORXPlus® Bits

Set Includes Quick Release Holder
and the following 7 bits:

.18 Security TORXPlus® Sizes:
IPR8, IPR10, IPR15, IPR20,
IPR25, IPR27, IPR30


Wiha TORXPlus® Insert Bits and Power Bits
TORXPlus®

*Made in Germany -
Production Quality*

Highly resistant
to wear and
tear for a
long tool
life

Impact resistant modified
chrome-vanadium-molybdenum,
tool steel, hardened

Suitable for all applications
for both manual and machine
Hardness HRC 59-61


716 TORXPlus® Insert Bits, 1/4" Hex, 1"

Item No.	Size	mm	pkg.	lbs.
71603	IP3	25	10	.12
71604	IP4	25	10	.12
71605	IP5	25	10	.12
71606	IP6	25	10	.12
71607	IP7	25	10	.12
71608	IP8	25	10	.12
71609	IP9	25	10	.12
71610	IP10	25	10	.12
71615	IP15	25	10	.12
71620	IP20	25	10	.12
71625	IP25	25	10	.12
71627	IP27	25	10	.13
71630	IP30	25	10	.13
71640	IP40	25	10	.15


746 TORXPlus® Power Bits, 1/4" Hex, 2"

Item No.	Size	mm	pkg.	lbs.
74601	IP5	50	10	.18
74602	IP6	50	10	.18
74603	IP7	50	10	.18
74604	IP8	50	10	.18
74608	IP9	50	10	.18
74612	IP10	50	10	.20
74616	IP15	50	10	.20
74620	IP20	50	10	.20
74624	IP25	50	10	.20
74628	IP27	50	10	.25
74632	IP30	50	10	.25
74636	IP40	50	10	.25



2 bit
pack


716 TORXPlus® Insert Bit Packs, 1"

CVM S2 modified tool steel

Item No.	Size	mm	lbs.
71631	IP3	25	.03
71632	IP4	25	.03
71633	IP5	25	.03
71634	IP6	25	.03
71635	IP7	25	.03
71636	IP8	25	.03
71637	IP9	25	.03
71638	IP10	25	.03
71639	IP15	25	.03
71641	IP20	25	.03
71642	IP25	25	.03
71643	IP27	25	.03
71644	IP30	25	.03
71645	IP40	25	.04



2 bit
pack


746 TORXPlus® Power Bit Packs, 2"


Item No.	Size	mm	lbs.
74659	IP5	50	.05
74660	IP6	50	.05
74661	IP7	50	.05
74662	IP8	50	.05
74663	IP9	50	.05
74664	IP10	50	.05
74665	IP15	50	.05
74666	IP20	50	.05
74667	IP25	50	.05
74668	IP27	50	.05
74669	IP30	50	.05
74670	IP40	50	.05

Wiha Ball End TORX® Bits


See additional Ball End TORX
Tools on Page 17

**Wiha TORX® MagicSpring
Screw Holding Power Bits**

Screw Holding
TORX Bits



Stainless
rotary spring 2 bit pack

**745 TORX® MagicSpring Screw Holding
Power Bits, 1/4" Hex Drive, 2.0"/50mm OAL**

Item No.	Size	mm	pkg.	lbs.
74552	T10	50	2	.05
74554	T15	50	2	.05
74555	T20	50	2	.05
74557	T25	50	2	.05
74562	T30	50	2	.05
74564	T40	50	2	.05

Wiha Double End TORX® Bits

744 TORX® Double End Bits
1/4" Hex Drive, Length 2.56"/65mm

Item No.	Size	Size	mm	pkg.	lbs.
74411	T6	T6	65	10	.32
74413	T7	T7	65	10	.32
74415	T8	T8	65	10	.32
74417	T9	T9	65	10	.32
74419	T10	T10	65	10	.32
74421	T15	T15	65	10	.32
74423	T20	T20	65	10	.32
74429	T25	T25	65	10	.33
74431	T27	T27	65	10	.34
74433	T30	T30	65	10	.35
74435	T40	T40	65	10	.38

2 bit
pack


744 TORX® Double End Bits

1/4" Hex Drive, Length 2.56"/65mm

Item No.	Size	Size	mm	lbs.
74460	T6	T6	65	.05
74461	T7	T7	65	.05
74462	T8	T8	65	.05
74463	T9	T9	65	.05
74464	T10	T10	65	.05
74465	T15	T15	65	.05
74466	T20	T20	65	.05
74467	T25	T25	65	.05
74468	T27	T27	65	.05
74469	T30	T30	65	.05
74470	T40	T40	65	.05

Wiha Sockets



Set Screw
Replaceable
Bit

761 TORX® Sockets 1/4" Square Drive				
Item				
No.	Size	mm	lbs.	
76106	T6	38	.04	
76107	T7	38	.04	
76109	T8	38	.04	
76111	T9	38	.04	
76113	T10	38	.04	
76117	T15	38	.04	
76119	T20	38	.04	
76121	T25	38	.04	
76123	T27	38	.04	
76129	T30	38	.05	
76131	T40	38	.05	



763 TORX® Sockets 3/8" Square Drive, Set Screw Replaceable Bit. 1/4" bits				
Item				
No.	Size	mm	lbs.	
76312	T9	42	.09	
76314	T10	42	.09	
76316	T15	42	.09	
76318	T20	42	.09	
76322	T25	42	.09	
76324	T27	42	.09	
76326	T30	42	.09	
76328	T40	42	.09	



763 TORX® Sockets 3/8" Square Drive, Set Screw Replaceable Bit. 5/16" Bit. 2" OAL				
Item				
No.	Size	mm	lbs.	
76346	T40	51	.11	
76348	T45	51	.11	
76352	T50	51	.11	
76354	T55	51	.13	



716 TORXPlus® Sockets 1/4" Square Drive, Set Screw Replaceable Bit. 1/4" bits				
Item				
No.	Size	mm	lbs.	
71661	IP6	38	.04	
71662	IP7	38	.04	
71663	IP8	38	.04	
71664	IP9	38	.04	
71665	IP10	38	.04	
71666	IP15	38	.04	
71667	IP20	38	.04	
71668	IP25	38	.04	
71669	IP27	38	.04	
71670	IP30	38	.04	
71671	IP40	38	.04	



716 TORXPlus® Sockets 3/8" Square Drive, Set Screw Replaceable Bit. 1/4" bits				
Item				
No.	Size	mm	lbs.	
71673	IP9	42	.09	
71674	IP10	42	.09	
71675	IP15	42	.09	
71676	IP20	42	.09	
71677	IP25	42	.09	
71678	IP27	42	.09	
71680	IP30	42	.09	
71681	IP40	42	.09	



Set Screw
Replaceable
Bit

763 Security TORX® Sockets 1/4" Square drive, 1/4" bits			
Item			
No.	Size	mm	
76329	T7s	38	
76330	T8s	38	
76331	T9s	38	
76332	T10s	38	
76333	T15s	38	
76334	T20s	38	
76335	T25s	38	
76335	T27s	38	
76337	T30s	38	
76338	T40s	38	



Set Screw
Replaceable
Bit

701 Security TORX® Sockets 3/8" Square drive, 1/4" bits. 2" OAL				
Item				
No.	Size	mm	lbs.	
70107	T7s	42	.09	
70108	T8s	42	.09	
70109	T9s	42	.09	
70110	T10s	42	.09	
70113	T15s	42	.09	
70115	T20s	42	.09	
70117	T25s	42	.09	
70119	T27s	42	.09	
70121	T30s	42	.09	
70123	T40s	42	.09	



Set Screw
Replaceable
Bit

763 Security TORX® Sockets 3/8" Square drive, 5/16" bits			
Item			
No.	Size	mm	
76339	T40s	51	
76340	T45s	51	
76341	T50s	51	
76342	T55s	51	

1/2" Square Drive Sockets



Set Screw
Replaceable
Bit

764 TORX® Sockets 1/2" Square Drive					
Item					
No.	Size	mm	lbs.	pkg.	
76403	T30	59	.10	1	
76404	T40	59	.10	1	
76405	T45	59	.10	1	
76406	T50	59	.10	1	
76407	T55	59	.11	1	



Set Screw
Replaceable
Bit

764 Security TORX® Sockets 1/2" Square Drive					
Item					
No.	Size	mm	lbs.	pkg.	
76411	T40s	59	.11	1	
76412	T45s	59	.11	1	
76413	T50s	59	.11	1	
76414	T55s	59	.12	1	

Wiha Long Blade Sockets



771 TORX® Sockets

1/4" Drive 6" Long Bit Socket.

Item No.	Size	Inch	lbs.
77151	T8	6	.12
77153	T9	6	.12
77152	T10	6	.12
77154	T15	6	.12
77156	T20	6	.12
77158	T25	6	.12
77160	T27	6	.12
77162	T30	6	.12
77164	T40	6	.12

77193 7 Pc. TORX® Socket Blade Set

TORX®: T10, T15, T20, T25, T27, T30, T40  wt. .69



771 TORX® Sockets

3/8" Drive 6" Long Bit Socket.

Item No.	Size	Inch	lbs.
77101	T8	6	.12
77103	T9	6	.12
77105	T10	6	.12
77107	T15	6	.12
77109	T20	6	.12
77111	T25	6	.12
77113	T27	6	.12
77115	T30	6	.12
77117	T40	6	.12

77195 9 Pc. TORX® Socket Blade Set

TORX®: T8, T9, T10, T15, T20, T25, T27, T30, T40  wt. .93

Wiha External Sockets



773 TORX® External Sockets 1/4" Square drive socket.

Item No.	Size	mm	lbs.
77304	E4	25	.03
77305	E5	25	.03
77306	E6	25	.03
77307	E7	25	.04
77308	E8	25	.04
77310	E10	25	.04

773 TORX® External Sockets 3/8" Square drive socket.

Item No.	Size	mm	lbs.
77331	E8	28	.07
77333	E10	28	.07
77335	E12	28	.07
77337	E14	28	.08



773 TORX® External Sockets 1/2" Square drive socket.

Item No.	Size	mm	lbs.
77341	E12	37	.12
77343	E14	37	.12
77345	E16	37	.14
77347	E18	37	.14
77349	E20	37	.15
77353	E24	40	.26



77390 22 pc. TORX® Set 1/4" Drive Socket

Ratchet 5.5", extension 2" & 4", swivel and hand driver in steel box. Hard chromed and polished.

Item No.

77390 lbs. Set includes the following:
2.14 E4, E5, E6, E7, E8, E10,
T6, T7, T8, T9, T10, T15,
T20, T25, T27, T30, T40

Wiha E-TORX® Socket Set On Molded Rails



77391 8 pc. E-TORX® Socket Set

Item No.

77391 lbs. Set includes the following:
.62 1/4" drive: E6, E7, E8, E10
3/8" drive: E12, E14
1/2" drive: E16, E18

Wiha Socket Sets On Molded Rails



76191 10 pc. **TORX**® Socket Set

1/4" Square Drive Replaceable Bit Socket. Bits CVM tool steel.
OAL 1.5"

Item No.

76191 lbs. Set includes the following:
.48 T7, T8, T9, T10, T15,
T20, T25, T27, T30, T40



76194 6 pc. **TORX**® Socket Set

1/4" Square Drive Replaceable Bit Socket. Bits CVM tool steel.

Item No.

76194 lbs. Set includes the following:
.20 T10, T15, T20, T25, T27, T30



76395 8 pc. **TORX**® Socket Set 3/8" Square Drive Replaceable Bit Socket. Bits CVM tool steel. OAL 1.5"

Item No.

76395 lbs. Set includes the following:
.75 T9, T10, T15, T20, T25,
T27, T30, T40



76396 8 pc. **TORX**® Socket Set 3/8" Square Drive Replaceable Bit Socket. 1/4" & 5/16" Bits CVM tool steel. OAL 1.65"

Item No.

76396 lbs. Set includes the following:
.84 1/4": T20, T25, T27, T30, T40
5/16": T45, T50, T55

Security Torx®




70195 10 pc. Security **TORX**® Socket Set

1/4" Square drive replaceable bit socket. 1/4" Bits CVM tool steel.

Item No.

70195 lbs. Set includes the following:
.48 T7s, T8s, T9s, T10s, T15s,
T20s, T25s, T27s, T30s, T40s




76397 9 pc. Security **TORX**® Socket Set

3/8" Sq. Drive Replaceable Bit Socket. 1/4" & 5/16" Bits CVM tool steel.

Item No.

76397 lbs. Set includes the following:
.85 1/4": T10s, T15s, T20s, T27s, T30s
3/8": T40s (1/4" bit)
3/8": T45s, T50s (5/16" bit)



76399 12 pc. Security **TORX**® Socket Set 1/4" & 3/8" Square Drive Replaceable Bit Socket. 1/4" & 5/16" Bits CVM tool steel.

Item No.

76399 lbs. Set includes the following:
.77 1/4": T7s, T8s, T10s, T15s, T20s, T25s, T27s, T30s, T40s
5/16": T45s, T50s, T55s



71698 8 pc. **TORXPlus**® Socket Set On Rail

In Vinyl Pouch 1/4" & 3/8" Square Drive Replaceable Bit Socket. Bits Chrome-vanadium-molybdenum tool steel.

Item No.

71698 lbs. Set includes the following:
.60 1/4": IP9, IP10, IP15, IP20
3/8": IP25, IP27, IP30, IP40

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
10893	7	27856	26	28616	23	36202	21	36294	5	36497	12	37044	18
20756	15	27857	26	28617	23	36203	21	36296	19	36510	16	37046	18
20757	15	27890	26	28618	23	36204	6	36298	6	36512	16	37048	18
20758	15	27894	26	28619	23	36205	7	36299	19	36515	16	37050	18
20759	15	27899	26	28690	25	36206	6	36305	13	36520	16	37052	18
20760	15	28000	29	28724	24	36207	21	36306	13	36525	16	37054	18
20799	15	28001	29	28726	24	36208	6	36307	13	36530	16	37090	16
26701	27	28087	29	28727	24	36209	6	36308	13	36535	16	37091	16
26702	27	28103	33	28734	24	36210	7	36309	13	36540	18	37092	18
26703	27	28126	11	28736	24	36211	19	36310	13	36542	18	37106	22
26704	27	28127	11	28737	24	36212	7	36315	13	36544	18	37107	22
26705	27	28128	11	28825	24	36215	7	36320	13	36546	18	37108	22
26706	27	28129	11	28826	24	36216	17	36321	14	36548	18	37109	22
26707	27	28130	11	28827	24	36217	17	36323	14	36550	18	37110	22
26708	27	28132	11	28828	24	36218	6	36325	13	36552	18	37115	22
26709	27	28133	11	28829	24	36219	6	36326	14	36554	18	37120	22
26710	27	28134	11	28830	24	36220	7	36327	13	36556	22	37125	22
26715	27	28135	11	28903	25	36221	17	36328	14	36557	22	37127	22
26720	27	28136	11	28904	25	36222	17	36329	14	36558	22	37130	22
26721	21	28195	11	28905	25	36223	19	36330	13	36559	22	37140	22
26723	21	28197	11	28906	25	36224	6	36332	14	36560	22	37190	22
26725	21	28295	30	28907	25	36225	7	36335	14	36561	22	37192	22
26727	21	28297	32	28908	25	36226	17	36337	14	36562	22	37608	6
26729	21	28301	12	28910	25	36227	17	36339	14	36590	16	37609	6
26731	21	28339	12,24	28911	25	36228	19	36340	13	36591	16	37610	6
26732	27	28340	12,24	28912	25	36229	19	36342	14	36592	18	37615	6
26733	27	28341	12,24	28913	25	36230	7	36345	13	36598	22	37620	6
26735	27	28342	12,24	28914	25	36233	19	36346	14	36606	20	37625	6
26736	27	28486	11	28915	25	36234	21	36350	13	36607	20	37627	6
26737	27	28487	11	28931	25	36235	7	36352	14	36608	20	37630	6
26739	27	28488	11	28933	25	36236	17	36355	13	36609	20	37640	6
26741	27	28489	33	28935	25	36237	17	36357	14	36610	20	37690	6
26743	27	28501	23	28937	25	36238	19	36360	13	36615	20	38003	30
26745	27	28502	23	28938	25	36239	19	36390	13	36620	20	38004	30
26747	27	28504	23	28939	25	36240	7	36392	13	36625	20	38008	30
26749	27	28506	23	28940	25	36243	19	36393	14	36627	20	38009	32
26751	27	28508	23	29205	24	36244	21	36394	13	36630	20	38010	32
26790	27	28512	23	29206	24	36245	7	36395	15	36631	17	38015	33
26791	27	28522	24	29209	24	36248	19	36396	15	36632	17	38028	30
26792	27	28524	24	29211	24	36249	21	36397	15	36633	17	38045	30
26793	27	28526	24	29212	24	36250	7	36398	15	36634	17	38047	32
26796	27	28527	23	29214	24	36253	19	36399	13	36635	17	38450	33
26798	21	28528	23	29220	24	36254	21	36409	13	36636	17	38460	33
26799	26	28529	23	29225	24	36255	19	36410	13	36637	17	45504	10
26951	29	28530	23	29230	24	36256	21	36415	13	36638	17	45505	9
26952	29	28531	23	29238	24	36257	21	36417	13	36640	20	45506	9
26953	29	28532	23	29241	24	36258	21	36420	13	36645	14	45507	10
26954	29	28533	23	29245	24	36259	6	36422	13	36646	14	45508	10
26955	29	28550	23	29251	24	36260	6	36425	13	36647	14	45509	10
26956	29	28551	23	32505	7	36264	5	36427	13	36648	14	45510	10
26957	29	28552	23	32511	7	36266	5	36430	13	36649	14	45511	9
26961	29	28553	23	32516	7	36267	5	36432	13	36650	14	45515	10
26977	29	28554	23	32521	7	36268	5	36435	13	36651	14	45516	9
26978	29	28561	23	32526	7	36269	6	36437	13	36652	14	45520	10
26979	29	28562	23	32531	7	36270	5	36440	13	36653	14	45521	9
26980	29	28563	23	32536	7	36271	6	36442	13	36654	14	45522	9
26981	29	28564	23	32541	7	36272	5	36445	13	36655	14	45525	10
26982	29	28565	23	32546	7	36273	6	36450	13	36659	14	45526	9
26987	29	28566	23	32551	7	36274	5	36452	13	36660	14	45527	10
26995	29	28567	23	32556	7	36275	6	36461	19	36661	14	45530	10
27801	26	28568	23	32561	7	36276	5	36463	19	36689	14	45531	9
27802	26	28569	23	32590	7	36277	6	36466	19	36690	20	45536	9
27803	26	28571	23	32592	7	36278	5	36469	19	36691	20	45540	10
27804	26	28572	23	36106	20	36279	6	36472	19	36692	17	45541	9
27805	26	28573	23	36107	20	36280	5	36474	19	36694	14	45545	10
27811	26	28574	23	36108	20	36281	6	36476	19	36697	18	45546	9
27817	26	28575	23	36109	20	36282	5	36478	19	36698	14	45550	10
27823	26	28576	23	36110	20	36283	6	36480	12	36699	14	45551	9
27829	26	28577	23	36115	20	36284	5	36481	12	37013	16	45556	9
27835	26	28578	23	36120	20	36285	6	36482	12	37016	16	45561	9
27841	26	28579	23	36125	20	36286	5	36483	12	37019	16	45589	9
27847	26	28597	25	36127	20	36287	6	36484	12	37022	16	45591	9
27850	26	28598	25	36130	20	36288	5	36486	12	37026	16	45592	9
27851	26	28599	25	36140	20	36289	6	36487	12	37029	16	45593	10
27852	26	28611	23	36197	20	36290	21	36490	13	37032	16	45595	10
27853	26	28612	23	36199	20	36291	5	36492	13	37036	16	45597	10
27854	26	28613	23	36200	6	36292	7	36494	13	37040	18	45598	10
27855	26	28614	23	36201	5	36293	7	36496	19	37042	18	48400	9

Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
52711	8	71475	33	71582	34	72555	35	74536	35	74762	36	76405	39
52713	8	71476	33	71584	34	72556	35	74537	17	74763	36	76406	39
52716	8	71477	33	71585	34	72557	37	74538	35	74764	36	76407	39
52719	8	71478	33	71586	34	72562	37	74539	17	74765	36	76411	39
52722	8	71479	33	71587	34	72563	37	74541	17	74766	36	76412	39
52726	8	71480	33	71588	34	72564	37	74542	35	74767	36	76413	39
52729	8	71490	33	71596	34	72567	37	74543	17	74768	36	76414	39
52732	8	71491	33	71603	38	72573	35	74544	35	74769	36	76510	33
52790	8	71492	33	71604	38	72575	35	74545	17	74950	37	76511	33
52791	8	71493	33	71605	38	72576	35	74546	35	74981	31	76512	33
70107	39	71494	34	71606	38	72577	35	74547	17	74982	31	76513	33
70108	39	71500	34	71607	38	72578	35	74548	35	74985	31	76516	33
70109	39	71501	34	71608	38	72579	35	74549	17	74987	32	76517	33
70110	39	71502	34	71609	38	72580	35	74550	17	75093	28	76553	33
70113	39	71503	34	71610	38	72581	35	74551	35	75703	28	76554	33
70115	39	71504	34	71615	38	73310	36	74552	38	75704	28	76555	33
70117	39	71505	35	71620	38	73311	36	74553	35	75705	28	76556	33
70119	39	71506	35	71625	38	73312	36	74554	38	75706	28	76558	33
70121	39	71507	35	71627	38	73313	36	74555	38	75707	28	76559	33
70123	39	71508	35	71630	38	73314	36	74556	35	75708	28	76810	33
70127	37	71509	35	71631	38	73315	36	74557	38	75709	28	76811	33
70128	37	71510	35	71632	38	73316	36	74558	35	75710	28	76812	33
70129	37	71511	34	71633	38	73317	36	74561	35	75715	28	76813	33
70135	37	71512	34	71634	38	73318	36	74562	38	75720	28	76816	33
70139	37	71513	34	71635	38	73319	36	74564	38	75727	28	76817	33
70142	37	71515	35	71636	38	73320	36	74563	35	75728	28	76853	33
70148	37	71516	34	71637	38	74411	38	74565	35	75729	28	76854	33
70150	37	71517	34	71638	38	74413	38	74567	35	75735	28	76855	33
70151	37	71518	34	71639	38	74415	38	74569	35	75739	28	76856	33
70152	37	71519	34	71640	38	74417	38	74571	35	75742	28	76858	33
70153	37	71520	35	71641	38	74419	38	74573	35	75792	28	76859	33
70154	37	71521	34	71642	38	74421	38	74575	35	75801	28	76895	33
70155	37	71522	34	71643	38	74423	38	74577	35	75985	28	76896	33
70156	37	71523	35	71644	38	74429	38	74579	35	76106	39	77101	40
70157	37	71524	35	71645	38	74431	38	74581	35	76107	39	77103	40
70158	37	71525	35	71648	37	74433	38	74583	35	76109	39	77105	40
70159	37	71527	35	71650	37	74435	38	74586	35	76111	39	77107	40
70160	37	71530	35	71652	37	74460	38	74587	35	76113	39	77109	40
70163	37	71536	36	71654	37	74461	38	74588	35	76117	39	77111	40
70168	37	71537	36	71656	37	74462	38	74589	35	76119	39	77113	40
70190	32	71538	36	71657	37	74463	38	74590	35	76121	39	77115	40
70195	41	71539	36	71658	37	74464	38	74591	35	76123	39	77117	40
70411	34	71540	35	71660	37	74465	38	74601	38	76129	39	77151	40
70413	34	71541	36	71661	39	74466	38	74602	38	76131	39	77152	40
70414	34	71542	36	71662	39	74467	38	74603	38	76191	41	77153	40
70416	34	71543	36	71663	39	74468	38	74604	38	76194	41	77154	40
70417	34	71544	36	71664	39	74469	38	74608	38	76312	39	77156	40
70507	37	71545	36	71665	39	74470	38	74612	38	76314	39	77158	40
70508	37	71546	36	71666	39	74501	36	74616	38	76316	39	77160	40
70509	37	71547	36	71667	39	74502	36	74620	38	76318	39	77162	40
70510	37	71548	35	71668	39	74503	36	74624	38	76322	39	77164	40
70515	37	71549	35	71669	39	74504	36	74628	38	76324	39	77193	40
70520	37	71550	35	71670	39	74505	17	74632	38	76326	39	77195	40
70525	37	71551	35	71671	39	74506	36	74636	38	76328	39	77304	40
70527	37	71552	35	71673	39	74508	36	74659	38	76329	39	77305	40
70530	37	71553	35	71674	39	74510	36	74660	38	76330	39	77306	40
70540	37	71554	35	71675	39	74511	35	74661	38	76331	39	77307	40
70545	37	71555	35	71676	39	74512	35	74662	38	76332	39	77308	40
70550	37	71556	35	71677	39	74513	35	74663	38	76333	39	77310	40
70555	37	71557	35	71678	39	74514	36	74664	38	76334	39	77331	40
70556	37	71558	35	71680	39	74515	36	74665	38	76335	39	77333	40
70557	37	71559	35	71681	39	74516	36	74666	38	76336	39	77335	40
70558	37	71560	35	71690	31	74517	35	74667	38	76337	39	77337	40
70559	37	71561	35	71692	31	74518	36	74668	38	76338	39	77341	40
70560	37	71562	34	71698	41	74519	35	74669	38	76339	39	77343	40
70561	37	71563	34	72525	35	74520	17	74670	38	76340	39	77345	40
70562	37	71564	34	72527	35	74521	35	74711	36	76341	39	77347	40
70563	37	71565	34	72530	35	74522	17	74714	36	76342	39	77349	40
70564	37	71566	34	72531	35	74523	35	74717	36	76346	39	77353	40
70565	37	71567	34	72540	35	74524	17	74721	36	76348	39	77390	40
70566	37	71568	34	72541	35	74526	17	74724	36	76352	39	77391	40
70567	37	71569	34	72542	37	74528	17	74728	36	76354	39	79242	31
70568	37	71570	36	72545	35	74529	35	74732	36	76395	41	79245	31
71130	33	71571	36	72546	35	74531	35	74736	36	76396	41	79247	32
71131	33	71574	34	72547	37	74532	17	74739	36	76397	41	79283	31
71195	30	71576	34	72550	35	74533	35	74742	36	76399	41	79445	31
71470	33	71578	34	72551	35	74534	17	74760	36	76403	39	79447	32
71474	33	71580	34	72552	37	74535	35	74761	36	76404	39	79450	37

(800) 494-6104
 fax: (800) 494-7456
 email: cservice@wihatools.com
www.wihatools.com



Wiha Quality Tools

1348 Dundas Circle
 Monticello, MN 55362
 tel: 763.295.6591
 fax: 763.295.6598

Wiha Tools Canada Ltd.

www.wihatools.ca
 Brampton, ONT L6T 4X4
 tel: 866.494.0096 or 763.295.6591
 fax: 763.295.6598

To:

Catalog Item No. 99914 .wo
 version - 6/1/13

Subject to change
 without notice

©2013 Willi Hahn Corporation

®Torx is a registered trademark of
 Acument Intellectual Properties LLC.




99060.wo - Product Guide



99004.wo - Shop Tools Catalog



99919.wo - Insulated Catalog



99002.wo - Screwdrivers Catalog



99951.wo - Bits Catalog



99001.wo - TorqueControl Catalog



99934.wo - Hex Tools Catalog



99006.wo - Tech Tools Catalog



99945.wo - ESD Catalog



99977.wo - Pliers/Crimpers Catalog

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wiha:](#)

<u>74602</u>	<u>52732</u>	<u>70151</u>	<u>71563</u>	<u>75742</u>	<u>76131</u>	<u>76853</u>	<u>76895</u>	<u>76896</u>	<u>76856</u>	<u>76512</u>	<u>71524</u>	<u>76553</u>	<u>76855</u>	<u>76817</u>
<u>77156</u>	<u>71512</u>	<u>76516</u>	<u>76556</u>	<u>71548</u>	<u>76812</u>	<u>74669</u>	<u>76113</u>	<u>76129</u>	<u>76194</u>	<u>76346</u>	<u>76348</u>	<u>77390</u>	<u>28103</u>	<u>70564</u>
<u>74462</u>	<u>74508</u>	<u>74510</u>	<u>74548</u>	<u>75705</u>	<u>38047</u>	<u>71475</u>	<u>26982</u>	<u>28195</u>	<u>74433</u>	<u>74529</u>	<u>74569</u>	<u>74579</u>	<u>74589</u>	<u>74624</u>
<u>74987</u>	<u>76340</u>	<u>77113</u>	<u>76336</u>	<u>76339</u>	<u>76411</u>	<u>72552</u>	<u>72564</u>	<u>72576</u>	<u>74539</u>	<u>74541</u>	<u>74982</u>	<u>76324</u>	<u>76333</u>	<u>76342</u>
<u>76399</u>	<u>77101</u>	<u>72547</u>	<u>73314</u>	<u>73316</u>	<u>74435</u>	<u>74533</u>	<u>74536</u>	<u>76312</u>	<u>71478</u>	<u>72577</u>	<u>74537</u>	<u>71690</u>	<u>72556</u>	<u>73311</u>
<u>74522</u>	<u>74528</u>	<u>74549</u>	<u>76330</u>	<u>76332</u>	<u>76414</u>	<u>71680</u>	<u>75706</u>	<u>75715</u>	<u>75728</u>	<u>76111</u>	<u>52791</u>	<u>71571</u>	<u>71607</u>	<u>71671</u>
<u>71674</u>	<u>71675</u>	<u>71677</u>	<u>74557</u>	<u>71503</u>	<u>37625</u>	<u>71567</u>	<u>71637</u>	<u>71552</u>	<u>74768</u>					