









REV	DATE	DESCRIPTION	APPD	CHKD
A16	ECR-10-01573		ORLANDO	SR
A17	ECR-14-012603		YUSEP2004	RK MKO
A18	ECR-14-014129		YUSEP2004	RK MKO



Valid only for PN 2-7 and 2-8
 Landing at measure 72.5 (20mm Deep) milled off : bothsides



- NOTES
- MATERIAL-HOUSING ALUMINIUM DIECASTING ALLOY
 - SURFACE-POWDER VARNISH-GREY -VARNISH BLACK
 - VARNISH ON THE INSIDE NOT NECESSARY
 - WITH OUT TE LOGO
 - PACKAGING QUANTITY 5 PIECES IN A BOX

QTY	DESCRIPTION	MATERIAL	SURFACE	COLOR	ITEM NO	NOTES
1	HD-K HOOD	ALUMINIUM		BLACK	46	
1	HD HOOD	ALUMINIUM		GREY	45	
1	HD HOOD	ALUMINIUM			44	WITHOUT LOGODRILLING
1	HD HOOD	ALUMINIUM			43	WITHOUT LOGODRILLING
1	HD HOOD	ALUMINIUM		GREY	42	
1	HD HOOD	ALUMINIUM		UNPAINTED	41	SINGLE PART
1	HD HOOD	ALUMINIUM		GREY	40	3xM20
1	LB-CLIP BOLT	STEEL	ZINC PLATED	BLUE	39	M5
1	HD-K HOOD	ALUMINIUM	ALUMINIUM OXIDE	BLACK	38	
1	HD-K HOOD	ALUMINIUM	ALUMINIUM OXIDE	BLACK	37	
1	HD HOOD	ALUMINIUM		GREY	36	WITH OUT TE-LOGO
1	HD HOOD	ALUMINIUM		GREY	35	WITH OUT TE-LOGO
1	HD HOOD	ALUMINIUM		GREY	34	WITH OUT TE-LOGO
1	HD HOOD	ALUMINIUM		GREY	33	
1	ZB-CLIP POSITIONER	STAINLESS STEEL			32	
1	ZB-CLIP POSITIONER	STEEL	ZINC PLATED	BLUE	31	
1	ZB-LOCKING CLIP	STAINLESS STEEL	BLANK		30	
1	ZB-LOCKING CLIP	STEEL	ZINC PLATED	BLUE	29	
1	LB-SLIDE SPOOL	STEEL	ZINC PLATED	BLUE	28	
1	LB-CLIP BOLT	STAINLESS STEEL	BLANK		27	
1	ZB-CLIP BOLT	STEEL	ZINC PLATED	BLUE	26	
1	VS-CLIP SPRING RIGHT	STAINLESS STEEL	BLANK		25	
1	VS-CLIP SPRING RIGHT	STEEL	ZINC PLATED	BLUE	24	
1	VS-CLIP SPRING LEFT	STAINLESS STEEL	BLANK		23	
1	VS-CLIP SPRING LEFT	STEEL	ZINC PLATED	BLUE	22	
1	VS-CLIP POSITIONER	STAINLESS STEEL	BLANK		21	
1	VS-CLIP POSITIONER	STEEL	ZINC PLATED	BLUE	20	
1	VS-LOCKING CLIP	STAINLESS STEEL	BLANK		19	
1	VS-LOCKING CLIP	STEEL	ZINC PLATED	BLUE	18	
1	VS-CLIP BOLT	STAINLESS STEEL	BLANK		17	
1	VS-CLIP BOLT	STEEL	ZINC PLATED	BLUE	16	
1	HD HOOD	ALUMINIUM		GREY	15	WITH OUT TE-LOGO
1	HD HOOD	ALUMINIUM		GREY	14	WITH OUT TE-LOGO
1	HD HOOD	ALUMINIUM		GREY	13	WITH OUT TE-LOGO
1	HD HOOD	ALUMINIUM		GREY	12	WITH OUT TE-LOGO
1	HD HOOD	ALUMINIUM		GREY	11	
1	HD HOOD	ALUMINIUM		GREY	10	
1	HD-K HOOD	ALUMINIUM	ALUMINIUM OXIDE	BLACK	9	
1	HD-K HOOD	ALUMINIUM	ALUMINIUM OXIDE	BLACK	8	
1	HD-K HOOD	ALUMINIUM	ALUMINIUM OXIDE	BLACK	7	
1	HD-K HOOD	ALUMINIUM	ALUMINIUM OXIDE	BLACK	6	
1	HD-K HOOD	ALUMINIUM	ALUMINIUM OXIDE	BLACK	5	
1	HD HOOD	ALUMINIUM		GREY	4	
1	HD HOOD	ALUMINIUM		GREY	3	
1	HD HOOD	ALUMINIUM		GREY	2	
1	HD HOOD	ALUMINIUM		GREY	1	

ORDERING TEXT

3-63-53-43-33-23-13-02-92-82-72-62-52-41-52-32-22-12-01-91-81-71-61-41-21-11-00-90-80-70-60-50-40-30-20-1

THIS DRAWING IS A CONTROLLED DOCUMENT. DATE: 14.01.2002. DRAWN BY: SCHNEIDER. CHECKED BY: SCHNEIDER.

PRODUCT SPEC: HOOD HD.40.STO/STS.M32/M4.0.G

APPLICATIO SPEC: -

WEIGHT: -

CUSTOMER DRAWING

SCALE: 1:1

SHEET: 1 OF 1

DATE: 14.01.2002

REVISIONS: A16, A17, A18