PRODUCT NUMBER

71600–YXXXLF

- LEAD FREE, SEE NOTE 6
- COLOR OPTION, SEE NOTE 1
- TOTAL NB OF POSITION 04 TO 64 SEE SHEET 2
- OPTIONAL STRAIN RELIEF SEE SHEET 2







NOTES:

1 – HOUSING MATERIAL : GLASS FILLED THERMOPLASTIC. UL94V–0 COLOR: GREY

= STANDARD COLOR GREY
B = OPTION COLOR BLACK

2 – PIN MATERIAL : PHOSPHOR BRONZE

3 – PRODUCT PACKAGED IN TUBES.

4 – TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm

5 – 2x5, 2x6, 2x7 HAVE NO LEFT POLARIZING SLOT.
– 2x2, 2x3 WITH CENTRAL KEY HAVE NO TRIANGLE, NO LEFT AND RIGHT POLARIZING SLOT.
– 2x2 WITHOUT CENTRAL KEY HAS NO LEFT AND RIGHT POLARIZING SLOT.
– 2x3, 2x4 WITHOUT CENTRAL KEY HAVE NO LEFT POLARIZING SLOT
– 2x4 WITH CENTRAL KEY HAVE NO LEFT AND RIGHT POLARIZING SLOT

6 – THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS PER GS–22–008.
PACKAGING SPECIFICATION AS PER GS–14–920.

ltr	ecn no	dr	date
AP	F12–0046	LMU	12.04.25
AR	B–17851	LMU	14.06.05
AS	F–26816	LMU	17.06.06
AL	F06–0270	LMU	06.09.12
AM	F06–0274	LMU	06.09.25
AN	F09–0233	LMU	09.12.15

sheet	revision	AS	AG
index	sheet	1	2

mat'l. code: SEE NOTES

surface: ISO 1302 | tolerance: ISO 406 ISO 1101

tolerances unless otherwise specified

angles	linear	X.X ±0.3
		X.XX ±0.13
		X.XXX ±0.05

dr	D.LE	01.01.24
engr	P.NZ	01.01.24
chr	JF.N	01.01.24
appd	P.NZ	01.01.24

projection | mm | scale 5:1

product family: 2.54MM IDC

title: QUICKIE III FEM
0.76µm Au

dwg no: 71600 | sheet 1 of 2 | size: A3

type: CUSTOMER Drawing

Copyright FCI
FCIconnect.com
form: A3

STRAIN RELIEF OPTION AVAILABILITY	Nbr OF POSITIONS
1/6	04
0/1/2/3/6	06
0/1/2/3/6	08
0/1/2/3/6	10
0/1/2/3/6	14
0/1/2/3/6	16
0/1/2/3/6	18
0/1/2/3/6	20
0/1/3	24
0/1/2/3/6	26
0/1/2/3/6	30
0/1/2/3/6	34
0/1/2/3/6	40
0/1/2/3/6	50
0/1/2/3/6	60
0/1/2/3/6	64

PLATING
0.76µm GOLD ON CONTACT AREA
1.27 µm Ni REMAINDER OF PRODUCT

624
304
204 / 224
004
DASHES NOT AVAILABLE



WITHOUT STRAIN RELIEF



WITH LOW PROFILE STRAIN RELIEF



WITH STANDARD STRAIN RELIEF



WITH LATCHING STRAIN RELIEF



LOW PROFILE STRAIN RELIEF



STANDARD STRAIN RELIEF



LATCHING STRAIN RELIEF FOR SLIM HEADER

PRODUCT NUMBER	WITH	WITHOUT	STANDARD	WITHOUT	LOW PROFILE	LATCHING
	CENTRAL KEY		STRAIN RELIEF			
71600−6YY(B)LF	●					●
71600−3YY(B)LF		●	●			
71600−2YY(B)LF	●				●	
71600−1YY(B)LF	●			●		
71600−0YY(B)LF	●		●			

mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family
ltr	ecn no	dr	date	tolerances unless otherwise specified			QUICKIE
AF	B−17851	LMU	14.06.05	angles	linear		title
AG	F−26816	LMU	17.06.06			mm	IDC RECEPT DR
						scale N/A	
AB	F03019	DLE	03.01.23	dr	D.LE	01.01.24	dwg no 71600
AC	F05−0180	LMU	05.04.22	engr	P.NZ	01.01.24	sheet 2 of −
AD	F06−0270	LMU	06.09.12	chr	JF.N	01.01.24	size A3
AE	F06−0274	LMU	06.09.25	appd	P.NZ	01.01.24	type CUSTOMER Drawing
sheet index	revision sheet						

Copyright FCI
FCIconnect.com

form: A3