



Rating	20A 125VAC 1/3HP 10A 250VAC 3/4HP 20A 14VAC 10A 24VAC	
	10(4)A 250V~	
Contact Resistance	50m ohm Max.	
Insulation Resistance	DC 500V 100M ohm Min.	
Dielectric Strength	AC 1500V 1 minute	
Operation Temp.	- 20 °C ~ 85 ° C	
Function	3P SPDT (ON)-OFF-(ON)	
() = Momentary Function		

Mounting Hole		Circuit Diagram
		
Thickness		
0.75~5mm	X 36.8 ^{+0.2} ₋₀	Y 15.3 ^{+0.2} ₋₀
0.03~0.2inch	1.45 ^{+0.008} ₋₀	.60 ^{+0.008} ₋₀


Material:

Frame: Black, Nylon# 66

Actuator: Black, Nylon#66+33%GF

Printed: None

Water proof and dust proof to fit IP-56



RoHS Compliant

1 Flipped view of circuit diagram & rotated bottom view. 1/17/11.

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 12/08/10

Rev. 1

Unit: mm

Checked By: G.Guld

Title: **ROCKER SWITCH**

CW P/N: **GRB258I01BB**