

Roebuck

CASTOR L/DUTY 50MM



- **CASTOR L/DUTY 50MM**
- **Carrying Capacity:** 50kg
- **Wheel Diameter:** 50mm
- **Bearing Type:** Plain
- **Castor Top Plate Length:** 60mm
- **Castor Top Plate Width:** 60mm
- **Castor Type:** Swivel + Brake
- **Hole Centres (Length):** 48mm
- **Hole Centres (Width):** 48mm
- **Hole Size:** 6mm
- **Hole Spacing - Length:** 38mm
- **Hole Spacing - Width:** 38mm
- **Overall Height:** 68mm
- **Threaded Stem Size (Width):** 19mm
- **Tread Width:** 18mm
-