


7905 Series

D-SUB Straight Type



Material:

Housing: Thermoplastic Polyester Glass Filled UL94V-0.

Contacts: Copper Alloy.

Shell: Metal.

Electrical Characteristics:

Current Rating: 1 A.

Dielectric Withstanding Voltage: AC 1000V.






Insulator Resistance: 1000M Ω min.

Contact Resistance: 30m Ω max.

Operating Temperature: -55°C~+105°C.

Features:

Mates with: 7901, 7907, 7908.



Position	Dimension				
	A	B	C	D	E
9	16.92	24.99	30.81	19.28	16.33
15	25.25	33.32	39.14	27.51	24.66
25	38.96	47.04	53.04	41.30	38.38
37	55.42	63.50	69.32	57.71	54.84

Ordering information

7905- 37 M T
Series Position M: Male T: Tin Shell
F: Female

U C
U: Blue C: Selective Gold
B: Black Plated
W: White G: Gold Plated


00 N1
00: G/F Blank: Standard Type
N1: See Page A167

A
A: Tray
Package

* Please consult factory for details on 50 pin.


Option N1

With NUTS #4-40 Threaded
Riveted On Face Side




Option N1N6

With NUTS #4-40 Threaded
Riveted On Face Side and
Jack Screws Assembled




Option N2

With NUTS #4-40 Threaded
Riveted On Rear Side




Option N2N6

With NUTS #4-40 Threaded
Riveted On Rear Side and
Jack Screws Assembled



Option N3

With #4-40 Threaded Riveted
Brackets (Board Locks)



Option N3N6

With #4-40 Threaded Riveted
Brackets and Jack Screws
Assembled

