

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022173082

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 PC Board Connector, Bottom Entry, 0.38µm Gold (Au) Selective, 8 Circuits

Documents:	
3D Model	Product Specification PS-10-07 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Receptacles
Series	4455
Application	Board-to-Board, Signal
Overview	KK® Interconnect System - Molex
Product Name	KK® 254
UPC	800754204736
Physical	
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Natural (White)
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.960/g
Number of Rows	1
Orientation	Bottom Entry
PC Tail Length	3.35mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to PCB	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	2.5A
Grounding to PCB	No
Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE



EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Contains SVHC(2015

June 15): No

Halogen-Free

Status

Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

4455 Series

Mates With

42153 KK® Wire-to-Board Header, 4094

KK® Wire-to-Board Header, 42376 KK®

Header, 42375 KK® Header, 42377 , 42152

KK® Wire-to-Board Header, 4030 KK®

Wire-to-Board Header, 4380 KK® Header

Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235
Material Info	
Old Part Number	A-4455-BH08D(208)
Reference - Drawing Numbers	
Product Specification	PS-10-07
Sales Drawing	SDA-4455

This document was generated on 09/11/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION