


### Key Top Designed Specially for Projected-plunger-type B3F and B3W Switches

- ROHS compliant.
- Available in a wide range of colors and sizes.



## Ordering Information

### For B3F and B3W Switches


#### New

| Colour     | 6 x 6 mm Switches<br>B3F-1000, B3F-3000,<br>B3W-1000, B3FS) |           |          | 12 x 12 mm Switches<br>(B3F-4000, B3F-5000,<br>B3W-4000) |                    |             |
|------------|-------------------------------------------------------------|-----------|----------|----------------------------------------------------------|--------------------|-------------|
|            | 4 x 4 mm Key Top                                            | 6 mm dia. | D shape  | 9 x 9 mm Key Top                                         | 12 x 12 mm Key Top | 9.5-mm dia. |
| Light Grey | B32-1000                                                    | B32-2000  | B32-2100 | B32-1200                                                 | B32-1300           | B32-1600    |
| Black      | B32-1010                                                    | B32-2010  | B32-2110 | B32-1210                                                 | B32-1310           | B32-1610    |
| Orange     | B32-1020                                                    | -         | -        | B32-1220                                                 | B32-1320           | B32-1620    |
| Yellow     | B32-1030                                                    | -         | -        | B32-1230                                                 | B32-1330           | B32-1630    |
| Blue       | B32-1040                                                    | -         | -        | B32-1240                                                 | B32-1340           | -           |
| Green      | B32-1050                                                    | -         | -        | B32-1250                                                 | B32-1350           | -           |
| White      | B32-1060                                                    | -         | -        | B32-1280                                                 | B32-1380           | -           |
| Red        | B32-1080                                                    | -         | -        | B32-1280                                                 | B32-1380           | -           |


## Dimensions

**Note:** All units are in millimetres unless otherwise indicated. Unless otherwise specified, a tolerance of  $\pm 0.4$  mm applies to all dimensions.


**B32-10□0**




**B32-12□0**




**B32-13□0**




**Panel Cutout**







**Panel Cutout**






**Panel Cutout**




**B32-2000**  
**B32-2010**




**B32-2100**  
**B32-2110**



**Panel Cutout**



**B32-16□0**



**Panel Cutout**

