

Product Data Sheet


Part No. WST-1310S Washable Reflow Type (SMD)

(self drive circuit)



12.8 X 12.8 X 10

DIMENSIONS



UNIT : mm
TOLERANCE : ± 0.3
HOUSING MATERIAL : PPS

Type	Unit	WST-1310S-1	WST-1310S-2	WST-1310S-3
Rated Voltage	(VDC)	1.5	5	12
Operating Voltage	(VDC)	1.4~3	4~7	8~15
Current Consumption	(mA)	< 20	< 30	< 30
Sound Output (Min)	(dB)	> 75	> 85	> 85
Resonant Frequency	(Hz)	2400 $\pm$ 400	2300 $\pm$ 300	2300 $\pm$ 300
Operating Temp	(C)	-20~+70	-20~+70	-20~+70
Storage Temp	(C)	-30~+80	-30~+80	-30~+80
Weight	(g)	2	2	2
Dimension	mm	12.8 x 12.8 x 10	12.8 x 12.8 x 10	12.8 x 12.8 x 10
*Value applying at rated voltage				
*distance for measurement 30cm				

