





CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	2-5 @20°C	0.273 ohms ±10%
D.C. RESISTANCE	5-6 @20°C	0.331 ohms ±10%
INDUCTANCE	2-6 10kHz, 100mVAC, Ls	0.300mH ±10%
URNS RATIO	(2-5):(5-6)	1:1, ±2%

TERM. NO.'s FOR REF. ONLY



Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE	PART NO.
		Method: Tape & Reel			INDUCTOR	750341455
		PKG-0920				
		www.we-online.com/midcom				
6A	3/13	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750341455	SPECIFICATION SHEET 1 OF 1

