




(2,00 mm) .0787"

TSH, TMMS SERIES

SHROUDED HEADERS

Mates with:

CLT, SQT, SQW, ESQT,
TLE, SMM, MMS, PTF

SPECIFICATIONS

For complete specifications and
recommended PCB layouts
see www.samtec.com/TSH**Insulator Material:**
Black Liquid Crystal Polymer**Terminal Material:**

Phosphor Bronze

Plating:

Sn or Au over
50µ" (1,27 µm) Ni**Operating Temp Range:**

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

RoHS Compliant: Yes

Processing:


Lead-Free Solderable: Yes**SMT Lead Coplanarity:**

(0,15 mm) .006" max

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality

FILE NO. E111594

Note: Some lengths, styles
and options are non-standard,
non-returnable.

ALSO AVAILABLE (MOQ Required)

• Other sizes and platings
Contact Samtec.Mates with:
SQT, SQW, ESQT

SPECIFICATIONS

For complete specifications
see www.samtec.com/TMMS**Insulator Material:**

Black LCP

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over
50µ" (1,27 µm) Ni**Operating Temp Range:**

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

RoHS Compliant:


Yes

Lead-Free Solderable: Yes

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality

FILE NO. E111594

Note: Some lengths, styles
and options are non-standard,
non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM