



ETA-USA

HIGH QUALITY SWITCHING POWER SUPPLIES

AC/DC SWITCHING ADAPTOR DESKTOP
SINGLE OUTPUT / UNIVERSAL RANGE INPUT
WITH ACTIVE PFC

80 WATTS



DTC80-xSX-F-W SERIES

3-pole IEC-C14 AC inlet, Class 1
Meets LEVEL V Efficiency requirements
2 year warranty



DIMENSION: L132×W69×H40mm


Input

Input Voltage Range: 90-264VAC (Full Range)
Input Current (rms): 2A @ 90VAC; 1A @ 264VAC MAX.
Frequency: 47 - 63Hz
Power factor: >0.9 (20%~100% Load)
Efficiency: >80% @ full load, 115VAC

Options

N/A

General Description



Features

1. High Reliability
2. 100% BURN-IN Tested
3. 100% Hi-Pot tested
4. Safety Approvals, EMC compliance



ETA USA
16170 Vineyard Blvd. Suite 180, Morgan Hill, CA 95037
Phone: 1-800-ETA-POWER, (408) 778-2793 Fax: (408) 779-2753

Visit us at: www.eta-usa.com
email at: sales@eta-usa.com



ETA-USA

HIGH QUALITY SWITCHING POWER SUPPLIES

Environmental Specification	
Operating Temperature	0°C TO +40°C
Storage Temperature	-10°C +70°C
MTBF	>80'000 Hours at full load and 25°C ambient temp.
Protection	
Over voltage protection, AC recycles; Short circuit protection, Auto recovery.	
Safety	UL 60950 Third Edition CSA C22.2-No.60950 TUV EN60950 CB IEC 60950
EMI STANDARDS	FCC Class B CISPR22 Class B EN 55022 Class B EN 61000-3-2 CE
Dimension	L132×W69×H40mm
AC Input Connector	IEC 320-C14 Inlet

Output Characteristic	Unit	DTC80-09SX-F-W	DTC80-12SX-F-W	DTC80-15SX-F-W	DTC80-18SX-F-W	DTC80-24SX-F-W
Output Voltage	Vdc	9	12	15	18	24
Output Current	A	8	6.67	5.33	4.45	3.34
Output Power	W	72	80	80	80	80
Ripple and Noise	mVp-p	90	120	150	180	240
Output Regulation	%	± 5%				
Hold up time	mS	10ms (typical at full load @ 115VAC)				

Efficiency	%	87% At Full Load@115Vac
-------------------	----------	--------------------------------

Note: 1. Peak to Peak with 20MHz bandwidth with a tantalum 10uF in parallel with a 0.1uF ceramic capacitor.



ETA USA
16170 Vineyard Blvd. Suite 180, Morgan Hill, CA 95037
Phone: 1-800-ETA-POWER, (408) 778-2793 Fax: (408) 779-2753


Visit us at: www.eta-usa.com
email at: sales@eta-usa.com



ETA-USA

HIGH QUALITY SWITCHING POWER SUPPLIES

Dimension Diagram



ETA USA

16170 Vineyard Blvd. Suite 180, Morgan Hill, CA 95037

Phone: 1-800-ETA-POWER, (408) 778-2793 Fax: (408) 779-2753

Visit us at: www.eta-usa.com


email at: sales@eta-usa.com



ETA-USA

HIGH QUALITY SWITCHING POWER SUPPLIES

Derating Curve



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ETA-USA:](#)

[DTC80-18SX-F-W](#) [DTC80-12SX-F-W](#) [DTC80-24SX-F-W](#) [DTC80-15SX-F-W](#)