


# TAJ Series



## Standard and Low Profile Tantalum Capacitors




### FEATURES

- General purpose SMT chip tantalum series
- 17 case sizes available, standard and low profile down to 1mm maximum height
- CV range: 0.10 - 2200µF / 2.5 - 50V
- J-lead construction


### APPLICATIONS

- General low power DC/DC and LDO
- Entertainment / Infotainment systems
- Height restricted design




### MARKING

A, B, C, D, E, F, H, K, S, T, U, V, W, X, Y CASE



### P, R CASE



### HOW TO ORDER

| TAJ  | C                            | 106                                                                                                                                      | M                                 | 035                                                                                                                                                      | R                                                                                                                                                                                                                                   | NJ                                           | —                                                                                                          |
|------|------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------|------------------------------------------------------------------------------------------------------------|
| Type | Case Size<br>See table above | Capacitance Code<br>pF code: 1st two digits represent significant figures<br>3rd digit represents multiplier (number of zeros to follow) | Tolerance<br>K = ±10%<br>M = ±20% | Rated DC Voltage<br>002 = 2.5Vdc<br>004 = 4Vdc<br>006 = 6.3Vdc<br>010 = 10Vdc<br>016 = 16Vdc<br>020 = 20Vdc<br>025 = 25Vdc<br>035 = 35Vdc<br>050 = 50Vdc | Packaging<br>R = Pure Tin 7" Reel<br>S = Pure Tin 13" Reel<br>A = Gold Plating 7" Reel<br>B = Gold Plating 13" Reel<br>H = Tin Lead 7" Reel<br>K = Tin Lead 13" Reel<br>H, K = Non RoHS<br>A, B, H, K = please contact manufacturer | Specification Suffix<br>NJ = Standard Suffix | Additional characters may be added for special requirements<br>V = Dry pack Option (selected ratings only) |

### TECHNICAL SPECIFICATIONS

Technical Data: All technical data relate to an ambient temperature of +25°C

Capacitance Range: 0.10 µF to 2200 µF

Capacitance Tolerance: ±10%; ±20%

|                                    |           |     |     |     |    |    |    |    |    |    |
|------------------------------------|-----------|-----|-----|-----|----|----|----|----|----|----|
| Rated Voltage (V <sub>R</sub> )    | ≤ +85°C:  | 2.5 | 4   | 6.3 | 10 | 16 | 20 | 25 | 35 | 50 |
| Category Voltage (V <sub>C</sub> ) | ≤ +125°C: | 1.7 | 2.7 | 4   | 7  | 10 | 13 | 17 | 23 | 33 |
| Surge Voltage (V <sub>S</sub> )    | ≤ +85°C:  | 3.3 | 5.2 | 8   | 13 | 20 | 26 | 32 | 46 | 65 |
| Surge Voltage (V <sub>S</sub> )    | ≤ +125°C: | 2.2 | 3.4 | 5   | 8  | 13 | 16 | 20 | 28 | 40 |

Temperature Range: -55°C to +125°C

Reliability: 1% per 1000 hours at 85°C, V<sub>R</sub> with 0.1Ω/V series impedance, 60% confidence level

Qualification: CECC 30801 - 005 issue 2 EIA 535BAAC for standard case sizes

Termination Finished: Sn Plating (standard), Gold and SnPb Plating upon request

For AEC-Q200 availability, please contact AVX



## Standard and Low Profile Tantalum Capacitors

STANDARD TANTALUMS CAPACITANCE AND RATED VOLTAGE RANGE  
(LETTER DENOTES CASE SIZE)

| Capacitance          |                   | Rated voltage DC (V <sub>R</sub> ) to 85°C                      |                             |                                         |                                                      |                                         |                                       |                         |                       |                         |
|----------------------|-------------------|-----------------------------------------------------------------|-----------------------------|-----------------------------------------|------------------------------------------------------|-----------------------------------------|---------------------------------------|-------------------------|-----------------------|-------------------------|
| μF                   | Code              | 2.5V (e)                                                        | 4V (G)                      | 6.3V (J)                                | 10V (A)                                              | 16V (C)                                 | 20V (D)                               | 25V (E)                 | 35V (V)               | 50V (T)                 |
| 0.10<br>0.15<br>0.22 | 104<br>154<br>224 |                                                                 |                             |                                         |                                                      |                                         |                                       |                         | A<br>A<br>A           | A<br>A/B<br>A/B         |
| 0.33<br>0.47<br>0.68 | 334<br>474<br>684 |                                                                 |                             |                                         |                                                      |                                         | A                                     | A<br>A                  | A<br>A/B<br>A/B       | A/B<br>A/B/C<br>A/B/C   |
| 1.0<br>1.5<br>2.2    | 105<br>155<br>225 |                                                                 |                             | A                                       | A<br>A                                               | A<br>A/B                                | A<br>A<br>A/B                         | A<br>A/B<br>A/B         | A/B<br>A/B/C<br>A/B/C | A/B/C<br>B/C/D<br>B/C/D |
| 3.3<br>4.7<br>6.8    | 335<br>475<br>685 |                                                                 | A<br>A                      | A<br>A<br>A/B                           | A<br>A/B<br>A/B                                      | A/B<br>A/B<br>A/B/C                     | A/B<br>A/B/C<br>A/B/C                 | A/B/C<br>A/B/C<br>B/C   | B/C<br>B/C/D<br>C/D   | C/D<br>C/D<br>C/D       |
| 10<br>15<br>22       | 106<br>156<br>226 |                                                                 | A<br>A/B<br>A               | A/B<br>A/B<br>A/B/C                     | A/B/C<br>A/B/C<br>A/B/C                              | A/B/C<br>A/B/C<br>B/C/D                 | B/C<br>B/C/D<br>B/C/D                 | B/C/D<br>C/D<br>C/D     | C/D/E<br>C/D<br>D/E   | D/E/V<br>D/E/V<br>V     |
| 33<br>47<br>68       | 336<br>476<br>686 | A<br>A<br>A                                                     | A/B<br>A/B<br>A/B/C         | A/B/C<br>A/B/C/D<br>B/C/D               | A/B/C/D<br>B/C/D<br>B/C/D                            | B/C/D<br>C/D<br>C/D                     | C/D<br>C/D/E<br>C <sup>(M)</sup> /D/E | C/D/E<br>D/E<br>D/E/V   | D/E/V<br>D/E/V<br>V   |                         |
| 100<br>150<br>220    | 107<br>157<br>227 | A/B<br>B<br>B/D                                                 | A/B/C<br>B/C<br>B/C/D       | B/C/D<br>B <sup>(M)</sup> /C/D<br>C/D/E | B/C/D/E<br>C/D/E<br>C/D/E                            | C/D/E<br>D/E/V<br>D <sup>(M)</sup> /E/V | D/E/V<br>E/V                          | E/V<br>V <sup>(M)</sup> |                       |                         |
| 330<br>470<br>680    | 337<br>477<br>687 | D<br>C/D<br>C/D/E                                               | C/D/E<br>C/D/E<br>D/E       | C/D/E<br>D/E/V<br>D/E/V                 | D/E/V<br>E/U/V<br>E <sup>(M)</sup> /V <sup>(M)</sup> | E <sup>(M)</sup>                        |                                       |                         |                       |                         |
| 1000<br>1500<br>2200 | 108<br>158<br>228 | D <sup>(M)</sup> /E<br>D/E/V <sup>(M)</sup><br>V <sup>(M)</sup> | D/E/V<br>E/V <sup>(M)</sup> | E <sup>(M)</sup> /V <sup>(M)</sup>      |                                                      |                                         |                                       |                         |                       |                         |

LOW PROFILE TANTALUMS CAPACITANCE AND RATED VOLTAGE RANGE  
(LETTER DENOTES CASE SIZE)

| Capacitance          |                   | Rated voltage DC (V <sub>R</sub> ) to 85°C |                                         |                                                   |                                           |                                         |                             |                     |                       |                                |
|----------------------|-------------------|--------------------------------------------|-----------------------------------------|---------------------------------------------------|-------------------------------------------|-----------------------------------------|-----------------------------|---------------------|-----------------------|--------------------------------|
| μF                   | Code              | 2.5V (e)                                   | 4V (G)                                  | 6.3V (J)                                          | 10V (A)                                   | 16V (C)                                 | 20V (D)                     | 25V (E)             | 35V (V)               | 50V (T)                        |
| 0.10<br>0.15<br>0.22 | 104<br>154<br>224 |                                            |                                         |                                                   |                                           |                                         | R/S<br>R/S<br>R/S           | R<br>R              | R/S<br>R/S<br>R/S     | S<br>S<br>P/R/S                |
| 0.33<br>0.47<br>0.68 | 334<br>474<br>684 |                                            |                                         |                                                   |                                           |                                         | R/S<br>R/S<br>R/S/T         | R<br>R/S<br>R/S     | R/S<br>R/S/T<br>P/S/T | P/R <sup>(M)</sup> /S/T<br>S/T |
| 1.0<br>1.5<br>2.2    | 105<br>155<br>225 |                                            | R/S                                     | R/S<br>R/S                                        | R/S<br>R/S<br>R/S                         | R/S/T<br>R/S<br>R/S/T                   | R/S/T<br>P/R/S/T<br>P/R/S/T | P/R/S<br>P/S/T<br>T | P/S/T<br>T<br>T       | W<br>W<br>W                    |
| 3.3<br>4.7<br>6.8    | 335<br>475<br>685 | R<br>R                                     | R/S<br>R/S<br>R/S/T                     | R/S<br>R/S/T<br>R/S/T                             | R/S/T<br>R/S/T<br>P/R/S/T                 | R/S/T<br>K/P/S/T<br>S/T                 | T<br>T<br>T                 | T/W<br>T/W<br>W     | W<br>W<br>Y           | Y<br>X/Y<br>Y                  |
| 10<br>15<br>22       | 106<br>156<br>226 | R/S<br>R<br>P/R                            | R/S/T<br>R/S/T<br>K/P/R/S/T             | P/R/S/T<br>K/P/R/S/T<br>K/P <sup>(M)</sup> /S/T/W | K/P/R <sup>(M)</sup> /S/T<br>S/T/W<br>T/W | T/W<br>T <sup>(M)</sup> /W<br>W         | W<br>W<br>W/Y               | W<br>Y<br>F/Y       | X/Y<br>Y<br>Y         |                                |
| 33<br>47<br>68       | 336<br>476<br>686 | K/P/S<br>P <sup>(M)</sup> /S<br>T          | K/P <sup>(M)</sup> /S/T/W<br>T/W<br>T/W | T/W<br>T/W<br>W                                   | W<br>H/W/Y<br>W/Y                         | W/Y<br>W/X/Y<br>F/X/Y                   | X/Y<br>X/Y<br>Y             | Y<br>Y              |                       |                                |
| 100<br>150<br>220    | 107<br>157<br>227 | T/W<br>T <sup>(M)</sup> /W<br>W/Y          | T <sup>(M)</sup> /W<br>W/Y<br>W/X/Y     | W/Y<br>W/X/Y<br>F/X/Y                             | W/X/Y<br>F/X <sup>(M)</sup> /Y<br>Y       | F <sup>(M)</sup> /Y<br>Y <sup>(M)</sup> |                             |                     |                       |                                |
| 330<br>470<br>680    | 337<br>477<br>687 | W <sup>(M)</sup> /Y<br>F/Y<br>Y            | F/X/Y<br>Y<br>Y <sup>(M)</sup>          | Y<br>Y                                            |                                           |                                         |                             |                     |                       |                                |
| 1000                 | 108               | Y <sup>(M)</sup>                           |                                         |                                                   |                                           |                                         |                             |                     |                       |                                |

Not recommended for new designs; higher voltage or smaller case size alternatives are available.

Released ratings <sup>(M tolerance only)</sup>

Note: Voltage ratings are minimum values. AVX reserves the right to supply higher voltage ratings in the same case size, to the same reliability standards.

### RATINGS & PART NUMBER REFERENCE

| AVX<br>Part No. | Case<br>Size | Capacitance<br>(μF) | Rated<br>Voltage<br>(V) | Rated<br>Temperature<br>(°C) | Category<br>Voltage<br>(V) | Category<br>Temperature<br>(°C) | DCL<br>Max.<br>(μA) | DF<br>Max.<br>(%) | ESR<br>Max.<br>@ 100kHz<br>(Ω) | 100kHz RMS Current (mA) |      |       | MSL             |
|-----------------|--------------|---------------------|-------------------------|------------------------------|----------------------------|---------------------------------|---------------------|-------------------|--------------------------------|-------------------------|------|-------|-----------------|
|                 |              |                     |                         |                              |                            |                                 |                     |                   |                                | 25°C                    | 85°C | 125°C |                 |
| 2.5 Volt @ 85°C |              |                     |                         |                              |                            |                                 |                     |                   |                                |                         |      |       |                 |
| TAJR475*002#NJ  | R            | 4.7                 | 2.5                     | 85                           | 1.7                        | 125                             | 0.5                 | 6                 | 20                             | 52                      | 47   | 21    | 1               |
| TAJR685*002#NJ  | R            | 6.8                 | 2.5                     | 85                           | 1.7                        | 125                             | 0.5                 | 6                 | 20                             | 52                      | 47   | 21    | 1               |
| TAJR106*002#NJ  | R            | 10                  | 2.5                     | 85                           | 1.7                        | 125                             | 0.5                 | 8                 | 4.5                            | 111                     | 99   | 44    | 1               |
| TAJS106*002#NJ  | S            | 10                  | 2.5                     | 85                           | 1.7                        | 125                             | 0.5                 | 6                 | 8                              | 90                      | 81   | 36    | 1               |
| TAJR156*002#NJ  | R            | 15                  | 2.5                     | 85                           | 1.7                        | 125                             | 0.5                 | 8                 | 4.1                            | 116                     | 104  | 46    | 1               |
| TAJP226*002#NJ  | P            | 22                  | 2.5                     | 85                           | 1.7                        | 125                             | 0.5                 | 8                 | 3.5                            | 131                     | 118  | 52    | 1               |
| TAJR226*002#NJ  | R            | 22                  | 2.5                     | 85                           | 1.7                        | 125                             | 0.5                 | 8                 | 3.8                            | 120                     | 108  | 48    | 1               |
| TAJA336*002#NJ  | A            | 33                  | 2.5                     | 85                           | 1.7                        | 125                             | 0.8                 | 8                 | 1.7                            | 210                     | 189  | 84    | 1               |
| TAJK336*002#NJ  | K            | 33                  | 2.5                     | 85                           | 1.7                        | 125                             | 0.8                 | 8                 | 1.7                            | 188                     | 169  | 75    | 1               |
| TAJP336*002#NJ  | P            | 33                  | 2.5                     | 85                           | 1.7                        | 125                             | 0.7                 | 8                 | 3.5                            | 131                     | 118  | 52    | 1               |
| TAJS336*002#NJ  | S            | 33                  | 2.5                     | 85                           | 1.7                        | 125                             | 0.7                 | 8                 | 1.5                            | 208                     | 187  | 83    | 1               |
| TAJA476*002#NJ  | A            | 47                  | 2.5                     | 85                           | 1.7                        | 125                             | 0.9                 | 6                 | 3                              | 158                     | 142  | 63    | 1               |
| TAJP476M002#NJ  | P            | 47                  | 2.5                     | 85                           | 1.7                        | 125                             | 1.2                 | 12                | 3.2                            | 137                     | 123  | 55    | 1               |
| TAJS476*002#NJ  | S            | 47                  | 2.5                     | 85                           | 1.7                        | 125                             | 1.2                 | 8                 | 1.6                            | 202                     | 181  | 81    | 1               |
| TAJA686*002#NJ  | A            | 68                  | 2.5                     | 85                           | 1.7                        | 125                             | 1.4                 | 8                 | 1.5                            | 224                     | 201  | 89    | 1               |
| TAJT686*002#NJ  | T            | 68                  | 2.5                     | 85                           | 1.7                        | 125                             | 1.4                 | 8                 | 1.5                            | 231                     | 208  | 92    | 1               |
| TAJA107*002#NJ  | A            | 100                 | 2.5                     | 85                           | 1.7                        | 125                             | 2.5                 | 30                | 1.4                            | 231                     | 208  | 93    | 1               |
| TAJB107*002#NJ  | B            | 100                 | 2.5                     | 85                           | 1.7                        | 125                             | 2.5                 | 8                 | 1.4                            | 246                     | 222  | 99    | 1               |
| TAJT107*002#NJ  | T            | 100                 | 2.5                     | 85                           | 1.7                        | 125                             | 2.5                 | 15                | 1.3                            | 248                     | 223  | 99    | 1               |
| TAJW107*002#NJ  | W            | 100                 | 2.5                     | 85                           | 1.7                        | 125                             | 2.5                 | 8                 | 0.4                            | 474                     | 427  | 190   | 1               |
| TAJB157*002#NJ  | B            | 150                 | 2.5                     | 85                           | 1.7                        | 125                             | 3                   | 10                | 1.6                            | 230                     | 207  | 92    | 1               |
| TAJT157M002#NJ  | T            | 150                 | 2.5                     | 85                           | 1.7                        | 125                             | 3.8                 | 18                | 1.2                            | 258                     | 232  | 103   | 1               |
| TAJW157*002#NJ  | W            | 150                 | 2.5                     | 85                           | 1.7                        | 125                             | 3.8                 | 8                 | 0.3                            | 548                     | 493  | 219   | 1               |
| TAJB227*002#NJ  | B            | 220                 | 2.5                     | 85                           | 1.7                        | 125                             | 4.4                 | 16                | 1.6                            | 230                     | 207  | 92    | 1               |
| TAJD227*002#NJ  | D            | 220                 | 2.5                     | 85                           | 1.7                        | 125                             | 5.5                 | 8                 | 0.3                            | 707                     | 636  | 283   | 1               |
| TAJW227*002#NJ  | W            | 220                 | 2.5                     | 85                           | 1.7                        | 125                             | 5.5                 | 8                 | 0.3                            | 548                     | 493  | 219   | 1               |
| TAJY227*002#NJ  | Y            | 220                 | 2.5                     | 85                           | 1.7                        | 125                             | 5.5                 | 8                 | 0.3                            | 645                     | 581  | 258   | 1 <sup>1)</sup> |
| TAJD337*002#NJ  | D            | 330                 | 2.5                     | 85                           | 1.7                        | 125                             | 8.2                 | 8                 | 0.3                            | 707                     | 636  | 283   | 1               |
| TAJW337M002#NJ  | W            | 330                 | 2.5                     | 85                           | 1.7                        | 125                             | 8.2                 | 12                | 0.3                            | 548                     | 493  | 219   | 1               |
| TAJY337*002#NJ  | Y            | 330                 | 2.5                     | 85                           | 1.7                        | 125                             | 8.2                 | 8                 | 0.3                            | 645                     | 581  | 258   | 1 <sup>1)</sup> |
| TAJC477*002#NJ  | C            | 470                 | 2.5                     | 85                           | 1.7                        | 125                             | 9.4                 | 12                | 0.2                            | 742                     | 667  | 297   | 1               |
| TAJD477*002#NJ  | D            | 470                 | 2.5                     | 85                           | 1.7                        | 125                             | 11.6                | 8                 | 0.2                            | 866                     | 779  | 346   | 1               |
| TAJF477*002#NJ  | F            | 470                 | 2.5                     | 85                           | 1.7                        | 125                             | 11.8                | 12                | 0.3                            | 577                     | 520  | 231   | 1               |
| TAJY477*002#NJ  | Y            | 470                 | 2.5                     | 85                           | 1.7                        | 125                             | 11                  | 12                | 0.2                            | 791                     | 712  | 316   | 1 <sup>1)</sup> |
| TAJC687*002#NJ  | C            | 680                 | 2.5                     | 85                           | 1.7                        | 125                             | 17                  | 18                | 0.2                            | 742                     | 667  | 297   | 1               |
| TAJD687*002#NJ  | D            | 680                 | 2.5                     | 85                           | 1.7                        | 125                             | 17                  | 16                | 0.2                            | 866                     | 779  | 346   | 1               |
| TAJE687*002#NJ  | E            | 680                 | 2.5                     | 85                           | 1.7                        | 125                             | 17                  | 10                | 0.2                            | 908                     | 817  | 363   | 1 <sup>1)</sup> |
| TAJY687*002#NJ  | Y            | 680                 | 2.5                     | 85                           | 1.7                        | 125                             | 17                  | 12                | 0.2                            | 791                     | 712  | 316   | 1 <sup>1)</sup> |
| TAJD108M002#NJ  | D            | 1000                | 2.5                     | 85                           | 1.7                        | 125                             | 25                  | 20                | 0.2                            | 866                     | 779  | 346   | 1               |
| TAJE108*002#NJ  | E            | 1000                | 2.5                     | 85                           | 1.7                        | 125                             | 20                  | 14                | 0.4                            | 642                     | 578  | 257   | 1 <sup>1)</sup> |
| TAJY108M002#NJ  | Y            | 1000                | 2.5                     | 85                           | 1.7                        | 125                             | 25                  | 30                | 0.2                            | 791                     | 712  | 316   | 1 <sup>1)</sup> |
| TAJD158*002#NJ  | D            | 1500                | 2.5                     | 85                           | 1.7                        | 125                             | 37.5                | 60                | 0.2                            | 866                     | 779  | 346   | 1               |
| TAJE158*002#NJ  | E            | 1500                | 2.5                     | 85                           | 1.7                        | 125                             | 37                  | 20                | 0.2                            | 908                     | 817  | 363   | 1 <sup>1)</sup> |
| TAJV158M002#NJ  | V            | 1500                | 2.5                     | 85                           | 1.7                        | 125                             | 30                  | 20                | 0.2                            | 1118                    | 1006 | 447   | 1 <sup>1)</sup> |
| TAJV228M002#NJ  | V            | 2200                | 2.5                     | 85                           | 1.7                        | 125                             | 55                  | 50                | 0.2                            | 1118                    | 1006 | 447   | 1 <sup>1)</sup> |
| 4 Volt @ 85°C   |              |                     |                         |                              |                            |                                 |                     |                   |                                |                         |      |       |                 |
| TAJR225*004#NJ  | R            | 2.2                 | 4                       | 85                           | 2.7                        | 125                             | 0.5                 | 6                 | 25                             | 47                      | 42   | 19    | 1               |
| TAJS225*004#NJ  | S            | 2.2                 | 4                       | 85                           | 2.7                        | 125                             | 0.5                 | 6                 | 25                             | 51                      | 46   | 20    | 1               |
| TAJR335*004#NJ  | R            | 3.3                 | 4                       | 85                           | 2.7                        | 125                             | 0.5                 | 6                 | 20                             | 52                      | 47   | 21    | 1               |
| TAJS335*004#NJ  | S            | 3.3                 | 4                       | 85                           | 2.7                        | 125                             | 0.5                 | 6                 | 18                             | 60                      | 54   | 24    | 1               |
| TAJR475*004#NJ  | R            | 4.7                 | 4                       | 85                           | 2.7                        | 125                             | 0.5                 | 6                 | 12                             | 68                      | 61   | 27    | 1               |
| TAJS475*004#NJ  | S            | 4.7                 | 4                       | 85                           | 2.7                        | 125                             | 0.5                 | 6                 | 10                             | 81                      | 73   | 32    | 1               |
| TAJR685*004#NJ  | R            | 6.8                 | 4                       | 85                           | 2.7                        | 125                             | 0.5                 | 6                 | 5.2                            | 103                     | 93   | 41    | 1               |
| TAJS685*004#NJ  | S            | 6.8                 | 4                       | 85                           | 2.7                        | 125                             | 0.5                 | 6                 | 8                              | 90                      | 81   | 36    | 1               |
| TAJT685*004#NJ  | T            | 6.8                 | 4                       | 85                           | 2.7                        | 125                             | 0.5                 | 6                 | 6                              | 115                     | 104  | 46    | 1               |
| TAJR106*004#NJ  | R            | 10                  | 4                       | 85                           | 2.7                        | 125                             | 0.5                 | 6                 | 7                              | 89                      | 80   | 35    | 1               |
| TAJS106*004#NJ  | S            | 10                  | 4                       | 85                           | 2.7                        | 125                             | 0.5                 | 6                 | 6                              | 104                     | 94   | 42    | 1               |
| TAJT106*004#NJ  | T            | 10                  | 4                       | 85                           | 2.7                        | 125                             | 0.5                 | 6                 | 5                              | 126                     | 114  | 51    | 1               |
| TAJR156*004#NJ  | R            | 15                  | 4                       | 85                           | 2.7                        | 125                             | 0.6                 | 8                 | 4                              | 117                     | 106  | 47    | 1               |
| TAJS156*004#NJ  | S            | 15                  | 4                       | 85                           | 2.7                        | 125                             | 0.6                 | 8                 | 4                              | 127                     | 115  | 51    | 1               |
| TAJT156*004#NJ  | T            | 15                  | 4                       | 85                           | 2.7                        | 125                             | 0.6                 | 6                 | 2                              | 200                     | 180  | 80    | 1               |
| TAJK226*004#NJ  | K            | 22                  | 4                       | 85                           | 2.7                        | 125                             | 0.9                 | 8                 | 1.8                            | 183                     | 164  | 73    | 1               |
| TAJP226*004#NJ  | P            | 22                  | 4                       | 85                           | 2.7                        | 125                             | 0.9                 | 8                 | 4                              | 122                     | 110  | 49    | 1               |
| TAJR226*004#NJ  | R            | 22                  | 4                       | 85                           | 2.7                        | 125                             | 0.9                 | 8                 | 3.8                            | 120                     | 108  | 48    | 1               |
| TAJS226*004#NJ  | S            | 22                  | 4                       | 85                           | 2.7                        | 125                             | 0.9                 | 8                 | 3.5                            | 136                     | 123  | 55    | 1               |
| TAJT226*004#NJ  | T            | 22                  | 4                       | 85                           | 2.7                        | 125                             | 0.9                 | 6                 | 1.9                            | 205                     | 185  | 82    | 1               |
| TAJA336*004#NJ  | A            | 33                  | 4                       | 85                           | 2.7                        | 125                             | 1.3                 | 6                 | 3                              | 158                     | 142  | 63    | 1               |
| TAJK336*004#NJ  | K            | 33                  | 4                       | 85                           | 2.7                        | 125                             | 1.3                 | 10                | 1.7                            | 188                     | 169  | 75    | 1               |
| TAJP336M004#NJ  | P            | 33                  | 4                       | 85                           | 2.7                        | 125                             | 1.3                 | 8                 | 2.8                            | 146                     | 132  | 59    | 1               |
| TAJS336*004#NJ  | S            | 33                  | 4                       | 85                           | 2.7                        | 125                             | 1.3                 | 8                 | 1.7                            | 196                     | 176  | 78    | 1               |

### RATINGS & PART NUMBER REFERENCE

| AVX<br>Part No.        | Case<br>Size | Capacitance<br>(μF) | Rated<br>Voltage<br>(V) | Rated<br>Temperature<br>(°C) | Category<br>Voltage<br>(V) | Category<br>Temperature<br>(°C) | DCL<br>Max.<br>(μA) | DF<br>Max.<br>(%) | ESR<br>Max.<br>@ 100kHz<br>(Ω) | 100kHz RMS Current (mA) |      |       | MSL             |
|------------------------|--------------|---------------------|-------------------------|------------------------------|----------------------------|---------------------------------|---------------------|-------------------|--------------------------------|-------------------------|------|-------|-----------------|
|                        |              |                     |                         |                              |                            |                                 |                     |                   |                                | 25°C                    | 85°C | 125°C |                 |
| TAJT336*004#NJ         | T            | 33                  | 4                       | 85                           | 2.7                        | 125                             | 1.3                 | 6                 | 1.7                            | 217                     | 195  | 87    | 1               |
| TAJW336*004#NJ         | W            | 33                  | 4                       | 85                           | 2.7                        | 125                             | 1.3                 | 6                 | 0.6                            | 387                     | 349  | 155   | 1               |
| TAJA476*004#NJ         | A            | 47                  | 4                       | 85                           | 2.7                        | 125                             | 1.9                 | 8                 | 2.6                            | 170                     | 153  | 68    | 1               |
| TAJT476*004#NJ         | T            | 47                  | 4                       | 85                           | 2.7                        | 125                             | 1.9                 | 10                | 1.6                            | 224                     | 201  | 89    | 1               |
| TAJW476*004#NJ         | W            | 47                  | 4                       | 85                           | 2.7                        | 125                             | 1.9                 | 6                 | 0.5                            | 424                     | 382  | 170   | 1               |
| TAJA686*004#NJ         | A            | 68                  | 4                       | 85                           | 2.7                        | 125                             | 2.7                 | 10                | 1.5                            | 224                     | 201  | 89    | 1               |
| TAJB686*004#NJ         | B            | 68                  | 4                       | 85                           | 2.7                        | 125                             | 2.7                 | 6                 | 1.8                            | 217                     | 196  | 87    | 1               |
| TAJT686*004#NJ         | T            | 68                  | 4                       | 85                           | 2.7                        | 125                             | 2.7                 | 15                | 1.5                            | 231                     | 208  | 92    | 1               |
| TAJW686*004#NJ         | W            | 68                  | 4                       | 85                           | 2.7                        | 125                             | 2.7                 | 6                 | 0.4                            | 474                     | 427  | 190   | 1               |
| TAJA107*004#NJ         | A            | 100                 | 4                       | 85                           | 2.7                        | 125                             | 4                   | 30                | 1.4                            | 231                     | 208  | 93    | 1               |
| TAJB107*004#NJ         | B            | 100                 | 4                       | 85                           | 2.7                        | 125                             | 4                   | 8                 | 0.9                            | 307                     | 277  | 123   | 1               |
| TAJT107M004#NJ         | T            | 100                 | 4                       | 85                           | 2.7                        | 125                             | 4                   | 14                | 1.4                            | 239                     | 215  | 96    | 1               |
| TAJW107*004#NJ         | W            | 100                 | 4                       | 85                           | 2.7                        | 125                             | 4                   | 6                 | 0.4                            | 474                     | 427  | 190   | 1               |
| TAJB157*004#NJ         | B            | 150                 | 4                       | 85                           | 2.7                        | 125                             | 6                   | 10                | 1.5                            | 238                     | 214  | 95    | 1               |
| TAJC157*004#NJ         | C            | 150                 | 4                       | 85                           | 2.7                        | 125                             | 6                   | 6                 | 0.3                            | 606                     | 545  | 242   | 1               |
| TAJW157*004#NJ         | W            | 150                 | 4                       | 85                           | 2.7                        | 125                             | 6                   | 6                 | 0.5                            | 424                     | 382  | 170   | 1               |
| TAJY157*004#NJ         | Y            | 150                 | 4                       | 85                           | 2.7                        | 125                             | 6                   | 6                 | 0.4                            | 559                     | 503  | 224   | 1 <sup>1)</sup> |
| TAJB227*004#NJ         | B            | 220                 | 4                       | 85                           | 2.7                        | 125                             | 8.8                 | 12                | 1.1                            | 278                     | 250  | 111   | 1               |
| TAJC227*004#NJ         | C            | 220                 | 4                       | 85                           | 2.7                        | 125                             | 8.8                 | 8                 | 1.2                            | 303                     | 272  | 121   | 1               |
| TAJD227*004#NJ         | D            | 220                 | 4                       | 85                           | 2.7                        | 125                             | 8.8                 | 8                 | 0.9                            | 408                     | 367  | 163   | 1               |
| TAJW227*004#NJ         | W            | 220                 | 4                       | 85                           | 2.7                        | 125                             | 8.8                 | 8                 | 0.3                            | 548                     | 493  | 219   | 1               |
| TAJX227*004#NJ         | X            | 220                 | 4                       | 85                           | 2.7                        | 125                             | 8.8                 | 8                 | 0.9                            | 577                     | 520  | 231   | 1 <sup>1)</sup> |
| TAJY227*004#NJ         | Y            | 220                 | 4                       | 85                           | 2.7                        | 125                             | 8.8                 | 8                 | 0.3                            | 645                     | 581  | 258   | 1 <sup>1)</sup> |
| TAJC337*004#NJ         | C            | 330                 | 4                       | 85                           | 2.7                        | 125                             | 13.2                | 8                 | 0.3                            | 606                     | 545  | 242   | 1               |
| TAJD337*004#NJ         | D            | 330                 | 4                       | 85                           | 2.7                        | 125                             | 13.2                | 8                 | 0.9                            | 408                     | 367  | 163   | 1               |
| TAJF337*004#NJ         | F            | 330                 | 4                       | 85                           | 2.7                        | 125                             | 13.2                | 10                | 0.3                            | 577                     | 520  | 231   | 1               |
| TAJX337*004#NJ         | X            | 330                 | 4                       | 85                           | 2.7                        | 125                             | 13.2                | 8                 | 0.3                            | 577                     | 520  | 231   | 1 <sup>1)</sup> |
| TAJY337*004#NJ         | Y            | 330                 | 4                       | 85                           | 2.7                        | 125                             | 13.2                | 12                | 0.4                            | 559                     | 503  | 224   | 1 <sup>1)</sup> |
| TAJC477*004#NJ         | C            | 470                 | 4                       | 85                           | 2.7                        | 125                             | 18.8                | 14                | 0.3                            | 606                     | 545  | 242   | 1               |
| TAJD477*004#NJ         | D            | 470                 | 4                       | 85                           | 2.7                        | 125                             | 18.8                | 12                | 0.9                            | 408                     | 367  | 163   | 1               |
| TAJE477*004#NJ         | E            | 470                 | 4                       | 85                           | 2.7                        | 125                             | 18.8                | 10                | 0.5                            | 574                     | 517  | 230   | 1 <sup>1)</sup> |
| TAJY477*004#NJ         | Y            | 470                 | 4                       | 85                           | 2.7                        | 125                             | 18.8                | 14                | 0.4                            | 559                     | 503  | 224   | 1 <sup>1)</sup> |
| TAJD687*004#NJ         | D            | 680                 | 4                       | 85                           | 2.7                        | 125                             | 27.2                | 14                | 0.5                            | 548                     | 493  | 219   | 1               |
| TAJE687*004#NJ         | E            | 680                 | 4                       | 85                           | 2.7                        | 125                             | 27.2                | 14                | 0.9                            | 428                     | 385  | 171   | 1 <sup>1)</sup> |
| TAJY687M004#NJ         | Y            | 680                 | 4                       | 85                           | 2.7                        | 125                             | 27.2                | 25                | 0.2                            | 791                     | 712  | 316   | 1 <sup>1)</sup> |
| TAJD108*004#NJ         | D            | 1000                | 4                       | 85                           | 2.7                        | 125                             | 40                  | 60                | 0.2                            | 866                     | 779  | 346   | 1               |
| TAJE108*004#NJ         | E            | 1000                | 4                       | 85                           | 2.7                        | 125                             | 40                  | 14                | 0.4                            | 642                     | 578  | 257   | 1 <sup>1)</sup> |
| TAJV108*004#NJ         | V            | 1000                | 4                       | 85                           | 2.7                        | 125                             | 40                  | 16                | 0.2                            | 1118                    | 1006 | 447   | 1 <sup>1)</sup> |
| TAJE158*004#NJ         | E            | 1500                | 4                       | 85                           | 2.7                        | 125                             | 60                  | 30                | 0.2                            | 908                     | 817  | 363   | 1 <sup>1)</sup> |
| TAJV158M004#NJ         | V            | 1500                | 4                       | 85                           | 2.7                        | 125                             | 60                  | 30                | 0.2                            | 1118                    | 1006 | 447   | 1 <sup>1)</sup> |
| <b>6.3 Volt @ 85°C</b> |              |                     |                         |                              |                            |                                 |                     |                   |                                |                         |      |       |                 |
| TAJR155*006#NJ         | R            | 1.5                 | 6.3                     | 85                           | 4                          | 125                             | 0.5                 | 6                 | 25                             | 47                      | 42   | 19    | 1               |
| TAJS155*006#NJ         | S            | 1.5                 | 6.3                     | 85                           | 4                          | 125                             | 0.5                 | 6                 | 25                             | 51                      | 46   | 20    | 1               |
| TAJR225*006#NJ         | R            | 2.2                 | 6.3                     | 85                           | 4                          | 125                             | 0.5                 | 6                 | 20                             | 52                      | 47   | 21    | 1               |
| TAJS225*006#NJ         | S            | 2.2                 | 6.3                     | 85                           | 4                          | 125                             | 0.5                 | 6                 | 18                             | 60                      | 54   | 24    | 1               |
| TAJR335*006#NJ         | R            | 3.3                 | 6.3                     | 85                           | 4                          | 125                             | 0.5                 | 6                 | 12                             | 68                      | 61   | 27    | 1               |
| TAJS335*006#NJ         | S            | 3.3                 | 6.3                     | 85                           | 4                          | 125                             | 0.5                 | 6                 | 9                              | 85                      | 76   | 34    | 1               |
| TAJR475*006#NJ         | R            | 4.7                 | 6.3                     | 85                           | 4                          | 125                             | 0.5                 | 6                 | 7                              | 89                      | 80   | 35    | 1               |
| TAJS475*006#NJ         | S            | 4.7                 | 6.3                     | 85                           | 4                          | 125                             | 0.5                 | 6                 | 7.5                            | 93                      | 84   | 37    | 1               |
| TAJT475*006#NJ         | T            | 4.7                 | 6.3                     | 85                           | 4                          | 125                             | 0.5                 | 6                 | 6                              | 115                     | 104  | 46    | 1               |
| TAJR685*006#NJ         | R            | 6.8                 | 6.3                     | 85                           | 4                          | 125                             | 0.5                 | 8                 | 7                              | 89                      | 80   | 35    | 1               |
| TAJS685*006#NJ         | S            | 6.8                 | 6.3                     | 85                           | 4                          | 125                             | 0.5                 | 6                 | 2.6                            | 158                     | 142  | 63    | 1               |
| TAJT685*006#NJ         | T            | 6.8                 | 6.3                     | 85                           | 4                          | 125                             | 0.5                 | 6                 | 5                              | 126                     | 114  | 51    | 1               |
| TAJA106*006#NJ         | A            | 10                  | 6.3                     | 85                           | 4                          | 125                             | 0.6                 | 6                 | 4                              | 137                     | 123  | 55    | 1               |
| TAJP106*006#NJ         | P            | 10                  | 6.3                     | 85                           | 4                          | 125                             | 0.6                 | 8                 | 6                              | 100                     | 90   | 40    | 1               |
| TAJR106*006#NJ         | R            | 10                  | 6.3                     | 85                           | 4                          | 125                             | 0.6                 | 8                 | 6                              | 96                      | 86   | 38    | 1               |
| TAJS106*006#NJ         | S            | 10                  | 6.3                     | 85                           | 4                          | 125                             | 0.6                 | 8                 | 4                              | 127                     | 115  | 51    | 1               |
| TAJT106*006#NJ         | T            | 10                  | 6.3                     | 85                           | 4                          | 125                             | 0.6                 | 6                 | 4                              | 141                     | 127  | 57    | 1               |
| TAJA156*006#NJ         | A            | 15                  | 6.3                     | 85                           | 4                          | 125                             | 0.9                 | 6                 | 3.5                            | 146                     | 132  | 59    | 1               |
| TAJK156*006#NJ         | K            | 15                  | 6.3                     | 85                           | 4                          | 125                             | 0.9                 | 6                 | 2                              | 173                     | 156  | 69    | 1               |
| TAJP156*006#NJ         | P            | 15                  | 6.3                     | 85                           | 4                          | 125                             | 0.9                 | 8                 | 3.5                            | 131                     | 118  | 52    | 1               |
| TAJR156*006#NJ         | R            | 15                  | 6.3                     | 85                           | 4                          | 125                             | 0.9                 | 8                 | 4.1                            | 116                     | 104  | 46    | 1               |
| TAJS156*006#NJ         | S            | 15                  | 6.3                     | 85                           | 4                          | 125                             | 0.9                 | 8                 | 3.5                            | 136                     | 123  | 55    | 1               |
| TAJT156*006#NJ         | T            | 15                  | 6.3                     | 85                           | 4                          | 125                             | 0.9                 | 6                 | 3.5                            | 151                     | 136  | 60    | 1               |
| TAJA226*006#NJ         | A            | 22                  | 6.3                     | 85                           | 4                          | 125                             | 1.4                 | 6                 | 3                              | 158                     | 142  | 63    | 1               |
| TAJK226*006#NJ         | K            | 22                  | 6.3                     | 85                           | 4                          | 125                             | 1.3                 | 10                | 1.8                            | 183                     | 164  | 73    | 1               |
| TAJP226M006#NJ         | P            | 22                  | 6.3                     | 85                           | 4                          | 125                             | 1.3                 | 8                 | 3.3                            | 135                     | 121  | 54    | 1               |
| TAJS226*006#NJ         | S            | 22                  | 6.3                     | 85                           | 4                          | 125                             | 1.3                 | 10                | 1.8                            | 190                     | 171  | 76    | 1               |
| TAJT226*006#NJ         | T            | 22                  | 6.3                     | 85                           | 4                          | 125                             | 1.4                 | 8                 | 2.5                            | 179                     | 161  | 72    | 1               |
| TAJW226*006#NJ         | W            | 22                  | 6.3                     | 85                           | 4                          | 125                             | 1.3                 | 6                 | 0.6                            | 387                     | 349  | 155   | 1               |
| TAJA336*006#NJ         | A            | 33                  | 6.3                     | 85                           | 4                          | 125                             | 2.1                 | 8                 | 2.2                            | 185                     | 166  | 74    | 1               |

### RATINGS & PART NUMBER REFERENCE

| AVX Part No.   | Case Size | Capacitance (μF) | Rated Voltage (V) | Rated Temperature (°C) | Category Voltage (V) | Category Temperature (°C) | DCL Max. (μA) | DF Max. (%) | ESR Max. @ 100kHz (Ω) | 100kHz RMS Current (mA) |      |       | MSL             |
|----------------|-----------|------------------|-------------------|------------------------|----------------------|---------------------------|---------------|-------------|-----------------------|-------------------------|------|-------|-----------------|
|                |           |                  |                   |                        |                      |                           |               |             |                       | 25°C                    | 85°C | 125°C |                 |
| TAJT336*006#NJ | T         | 33               | 6.3               | 85                     | 4                    | 125                       | 2.1           | 10          | 2.5                   | 179                     | 161  | 72    | 1               |
| TAJW336*006#NJ | W         | 33               | 6.3               | 85                     | 4                    | 125                       | 2             | 6           | 0.5                   | 424                     | 382  | 170   | 1               |
| TAJA476*006#NJ | A         | 47               | 6.3               | 85                     | 4                    | 125                       | 2.8           | 10          | 1.6                   | 217                     | 195  | 87    | 1               |
| TAJB476*006#NJ | B         | 47               | 6.3               | 85                     | 4                    | 125                       | 3             | 6           | 2                     | 206                     | 186  | 82    | 1               |
| TAJC476*006#NJ | C         | 47               | 6.3               | 85                     | 4                    | 125                       | 3             | 6           | 1.6                   | 262                     | 236  | 105   | 1               |
| TAJT476*006#NJ | T         | 47               | 6.3               | 85                     | 4                    | 125                       | 2.8           | 10          | 1.6                   | 224                     | 201  | 89    | 1               |
| TAJW476*006#NJ | W         | 47               | 6.3               | 85                     | 4                    | 125                       | 2.8           | 6           | 0.5                   | 424                     | 382  | 170   | 1               |
| TAJB686*006#NJ | B         | 68               | 6.3               | 85                     | 4                    | 125                       | 4             | 8           | 0.9                   | 307                     | 277  | 123   | 1               |
| TAJC686*006#NJ | C         | 68               | 6.3               | 85                     | 4                    | 125                       | 4.3           | 6           | 1.5                   | 271                     | 244  | 108   | 1               |
| TAJW686*006#NJ | W         | 68               | 6.3               | 85                     | 4                    | 125                       | 4.3           | 6           | 1.5                   | 245                     | 220  | 98    | 1               |
| TAJB107*006#NJ | B         | 100              | 6.3               | 85                     | 4                    | 125                       | 6.3           | 10          | 1.7                   | 224                     | 201  | 89    | 1               |
| TAJC107*006#NJ | C         | 100              | 6.3               | 85                     | 4                    | 125                       | 6.3           | 6           | 0.9                   | 350                     | 315  | 140   | 1               |
| TAJW107*006#NJ | W         | 100              | 6.3               | 85                     | 4                    | 125                       | 6.3           | 6           | 0.9                   | 316                     | 285  | 126   | 1               |
| TAJY107*006#NJ | Y         | 100              | 6.3               | 85                     | 4                    | 125                       | 6.3           | 6           | 0.7                   | 423                     | 380  | 169   | 1 <sup>1)</sup> |
| TAJB157M006#NJ | B         | 150              | 6.3               | 85                     | 4                    | 125                       | 9.5           | 10          | 1.2                   | 266                     | 240  | 106   | 1               |
| TAJC157*006#NJ | C         | 150              | 6.3               | 85                     | 4                    | 125                       | 9.5           | 6           | 1.3                   | 291                     | 262  | 116   | 1               |
| TAJD157*006#NJ | D         | 150              | 6.3               | 85                     | 4                    | 125                       | 9.5           | 6           | 0.9                   | 408                     | 367  | 163   | 1               |
| TAJW157*006#NJ | W         | 150              | 6.3               | 85                     | 4                    | 125                       | 9             | 8           | 0.3                   | 548                     | 493  | 219   | 1               |
| TAJX157*006#NJ | X         | 150              | 6.3               | 85                     | 4                    | 125                       | 9             | 6           | 0.4                   | 500                     | 450  | 200   | 1 <sup>1)</sup> |
| TAJY157*006#NJ | Y         | 150              | 6.3               | 85                     | 4                    | 125                       | 9.5           | 6           | 0.4                   | 559                     | 503  | 224   | 1 <sup>1)</sup> |
| TAJC227*006#NJ | C         | 220              | 6.3               | 85                     | 4                    | 125                       | 13.9          | 8           | 1.2                   | 303                     | 272  | 121   | 1               |
| TAJD227*006#NJ | D         | 220              | 6.3               | 85                     | 4                    | 125                       | 13.9          | 8           | 0.4                   | 612                     | 551  | 245   | 1               |
| TAJE227*006#NJ | E         | 220              | 6.3               | 85                     | 4                    | 125                       | 13.9          | 8           | 0.4                   | 642                     | 578  | 257   | 1 <sup>1)</sup> |
| TAJF227*006#NJ | F         | 220              | 6.3               | 85                     | 4                    | 125                       | 13.2          | 10          | 0.3                   | 577                     | 520  | 231   | 1               |
| TAJX227*006#NJ | X         | 220              | 6.3               | 85                     | 4                    | 125                       | 13.2          | 8           | 0.3                   | 577                     | 520  | 231   | 1 <sup>1)</sup> |
| TAJY227*006#NJ | Y         | 220              | 6.3               | 85                     | 4                    | 125                       | 13.9          | 8           | 0.7                   | 423                     | 380  | 169   | 1 <sup>1)</sup> |
| TAJC337*006#NJ | C         | 330              | 6.3               | 85                     | 4                    | 125                       | 19.8          | 12          | 0.5                   | 469                     | 422  | 188   | 1               |
| TAJD337*006#NJ | D         | 330              | 6.3               | 85                     | 4                    | 125                       | 20.8          | 8           | 0.4                   | 612                     | 551  | 245   | 1               |
| TAJE337*006#NJ | E         | 330              | 6.3               | 85                     | 4                    | 125                       | 20.8          | 8           | 0.4                   | 642                     | 578  | 257   | 1 <sup>1)</sup> |
| TAJY337*006#NJ | Y         | 330              | 6.3               | 85                     | 4                    | 125                       | 20.8          | 12          | 0.4                   | 559                     | 503  | 224   | 1 <sup>1)</sup> |
| TAJD477*006#NJ | D         | 470              | 6.3               | 85                     | 4                    | 125                       | 28            | 12          | 0.4                   | 612                     | 551  | 245   | 1               |
| TAJE477*006#NJ | E         | 470              | 6.3               | 85                     | 4                    | 125                       | 28            | 10          | 0.4                   | 642                     | 578  | 257   | 1 <sup>1)</sup> |
| TAJV477*006#NJ | V         | 470              | 6.3               | 85                     | 4                    | 125                       | 28            | 10          | 0.4                   | 791                     | 712  | 316   | 1 <sup>1)</sup> |
| TAJY477*006#NJ | Y         | 470              | 6.3               | 85                     | 4                    | 125                       | 28.2          | 20          | 0.2                   | 791                     | 712  | 316   | 1 <sup>1)</sup> |
| TAJD687*006#NJ | D         | 680              | 6.3               | 85                     | 4                    | 125                       | 40.8          | 20          | 0.5                   | 548                     | 493  | 219   | 3               |
| TAJE687*006#NJ | E         | 680              | 6.3               | 85                     | 4                    | 125                       | 42.8          | 10          | 0.5                   | 574                     | 517  | 230   | 1 <sup>1)</sup> |
| TAJV687*006#NJ | V         | 680              | 6.3               | 85                     | 4                    | 125                       | 42.8          | 10          | 0.5                   | 707                     | 636  | 283   | 1 <sup>1)</sup> |
| TAJE108M006#NJ | E         | 1000             | 6.3               | 85                     | 4                    | 125                       | 60            | 20          | 0.2                   | 908                     | 817  | 363   | 1 <sup>1)</sup> |
| TAJV108M006#NJ | V         | 1000             | 6.3               | 85                     | 4                    | 125                       | 60            | 16          | 0.2                   | 1118                    | 1006 | 447   | 1 <sup>1)</sup> |
| 10 Volt @ 85°C |           |                  |                   |                        |                      |                           |               |             |                       |                         |      |       |                 |
| TAJR105*010#NJ | R         | 1                | 10                | 85                     | 7                    | 125                       | 0.5           | 4           | 25                    | 47                      | 42   | 19    | 1               |
| TAJS105*010#NJ | S         | 1                | 10                | 85                     | 7                    | 125                       | 0.5           | 4           | 25                    | 51                      | 46   | 20    | 1               |
| TAJR155*010#NJ | R         | 1.5              | 10                | 85                     | 7                    | 125                       | 0.5           | 6           | 20                    | 52                      | 47   | 21    | 1               |
| TAJS155*010#NJ | S         | 1.5              | 10                | 85                     | 7                    | 125                       | 0.5           | 6           | 20                    | 57                      | 51   | 23    | 1               |
| TAJR225*010#NJ | R         | 2.2              | 10                | 85                     | 7                    | 125                       | 0.5           | 6           | 15                    | 61                      | 54   | 24    | 1               |
| TAJS225*010#NJ | S         | 2.2              | 10                | 85                     | 7                    | 125                       | 0.5           | 6           | 12                    | 74                      | 66   | 29    | 1               |
| TAJR335*010#NJ | R         | 3.3              | 10                | 85                     | 7                    | 125                       | 0.5           | 6           | 8                     | 83                      | 75   | 33    | 1               |
| TAJS335*010#NJ | S         | 3.3              | 10                | 85                     | 7                    | 125                       | 0.5           | 6           | 8                     | 90                      | 81   | 36    | 1               |
| TAJT335*010#NJ | T         | 3.3              | 10                | 85                     | 7                    | 125                       | 0.5           | 6           | 6                     | 115                     | 104  | 46    | 1               |
| TAJA475*010#NJ | A         | 4.7              | 10                | 85                     | 7                    | 125                       | 0.5           | 6           | 5                     | 122                     | 110  | 49    | 1               |
| TAJR475*010#NJ | R         | 4.7              | 10                | 85                     | 7                    | 125                       | 0.5           | 6           | 9                     | 78                      | 70   | 31    | 1               |
| TAJS475*010#NJ | S         | 4.7              | 10                | 85                     | 7                    | 125                       | 0.5           | 6           | 5                     | 114                     | 103  | 46    | 1               |
| TAJT475*010#NJ | T         | 4.7              | 10                | 85                     | 7                    | 125                       | 0.5           | 6           | 5                     | 126                     | 114  | 51    | 1               |
| TAJA685*010#NJ | A         | 6.8              | 10                | 85                     | 7                    | 125                       | 0.7           | 6           | 4                     | 137                     | 123  | 55    | 1               |
| TAJP685*010#NJ | P         | 6.8              | 10                | 85                     | 7                    | 125                       | 0.6           | 6           | 5                     | 110                     | 99   | 44    | 1               |
| TAJR685*010#NJ | R         | 6.8              | 10                | 85                     | 7                    | 125                       | 0.7           | 6           | 5.2                   | 103                     | 93   | 41    | 1               |
| TAJS685*010#NJ | S         | 6.8              | 10                | 85                     | 7                    | 125                       | 0.7           | 6           | 4                     | 127                     | 115  | 51    | 1               |
| TAJT685*010#NJ | T         | 6.8              | 10                | 85                     | 7                    | 125                       | 0.7           | 6           | 4                     | 141                     | 127  | 57    | 1               |
| TAJA106*010#NJ | A         | 10               | 10                | 85                     | 7                    | 125                       | 1             | 6           | 3                     | 158                     | 142  | 63    | 1               |
| TAJK106*010#NJ | K         | 10               | 10                | 85                     | 7                    | 125                       | 1             | 6           | 2.2                   | 165                     | 149  | 66    | 1               |
| TAJP106*010#NJ | P         | 10               | 10                | 85                     | 7                    | 125                       | 1             | 8           | 6                     | 100                     | 90   | 40    | 1               |
| TAJR106M010#NJ | R         | 10               | 10                | 85                     | 7                    | 125                       | 1             | 20          | 6                     | 96                      | 86   | 38    | 1               |
| TAJS106*010#NJ | S         | 10               | 10                | 85                     | 7                    | 125                       | 1             | 8           | 3                     | 147                     | 132  | 59    | 1               |
| TAJT106*010#NJ | T         | 10               | 10                | 85                     | 7                    | 125                       | 1             | 6           | 3                     | 163                     | 147  | 65    | 1               |
| TAJA156*010#NJ | A         | 15               | 10                | 85                     | 7                    | 125                       | 1.5           | 6           | 3.2                   | 153                     | 138  | 61    | 1               |
| TAJB156*010#NJ | B         | 15               | 10                | 85                     | 7                    | 125                       | 1.5           | 6           | 2.8                   | 174                     | 157  | 70    | 1               |
| TAJS156*010#NJ | S         | 15               | 10                | 85                     | 7                    | 125                       | 1.5           | 6           | 2                     | 180                     | 162  | 72    | 1               |
| TAJT156*010#NJ | T         | 15               | 10                | 85                     | 7                    | 125                       | 1.5           | 8           | 2.8                   | 169                     | 152  | 68    | 1               |
| TAJW156*010#NJ | W         | 15               | 10                | 85                     | 7                    | 125                       | 1.5           | 6           | 0.7                   | 359                     | 323  | 143   | 1               |
| TAJA226*010#NJ | A         | 22               | 10                | 85                     | 7                    | 125                       | 2.2           | 8           | 3                     | 158                     | 142  | 63    | 1               |
| TAJB226*010#NJ | B         | 22               | 10                | 85                     | 7                    | 125                       | 2.2           | 6           | 2.4                   | 188                     | 169  | 75    | 1               |

## RATINGS &amp; PART NUMBER REFERENCE

| AVX<br>Part No. | Case<br>Size | Capacitance<br>(μF) | Rated<br>Voltage<br>(V) | Rated<br>Temperature<br>(°C) | Category<br>Voltage<br>(V) | Category<br>Temperature<br>(°C) | DCL<br>Max.<br>(μA) | DF<br>Max.<br>(%) | ESR<br>Max.<br>@ 100kHz<br>(Ω) | 100kHz RMS Current (mA) |      |       | MSL             |
|-----------------|--------------|---------------------|-------------------------|------------------------------|----------------------------|---------------------------------|---------------------|-------------------|--------------------------------|-------------------------|------|-------|-----------------|
|                 |              |                     |                         |                              |                            |                                 |                     |                   |                                | 25°C                    | 85°C | 125°C |                 |
| TAJT226*010#NJ  | T            | 22                  | 10                      | 85                           | 7                          | 125                             | 2.2                 | 8                 | 2.2                            | 191                     | 172  | 76    | 1               |
| TAJW226*010#NJ  | W            | 22                  | 10                      | 85                           | 7                          | 125                             | 2.2                 | 6                 | 0.6                            | 387                     | 349  | 155   | 1               |
| TAJA336*010#NJ  | A            | 33                  | 10                      | 85                           | 7                          | 125                             | 3.3                 | 8                 | 1.7                            | 210                     | 189  | 84    | 1               |
| TAJB336*010#NJ  | B            | 33                  | 10                      | 85                           | 7                          | 125                             | 3.3                 | 6                 | 1.8                            | 217                     | 196  | 87    | 1               |
| TAJC336*010#NJ  | C            | 33                  | 10                      | 85                           | 7                          | 125                             | 3.3                 | 6                 | 1.6                            | 262                     | 236  | 105   | 1               |
| TAJW336*010#NJ  | W            | 33                  | 10                      | 85                           | 7                          | 125                             | 3.3                 | 6                 | 1.6                            | 237                     | 213  | 95    | 1               |
| TAJB476*010#NJ  | B            | 47                  | 10                      | 85                           | 7                          | 125                             | 4.7                 | 8                 | 1                              | 292                     | 262  | 117   | 1               |
| TAJC476*010#NJ  | C            | 47                  | 10                      | 85                           | 7                          | 125                             | 4.7                 | 6                 | 1.2                            | 303                     | 272  | 121   | 1               |
| TAJH476*006#NJ  | H            | 47                  | 10                      | 85                           | 7                          | 125                             | 4.7                 | 8                 | 1.0                            | 283                     | 255  | 113   | 1               |
| TAJW476*010#NJ  | W            | 47                  | 10                      | 85                           | 7                          | 125                             | 4.7                 | 6                 | 1.4                            | 254                     | 228  | 101   | 1               |
| TAJY476*010#NJ  | Y            | 47                  | 10                      | 85                           | 7                          | 125                             | 4.7                 | 6                 | 0.5                            | 500                     | 450  | 200   | 1 <sup>1)</sup> |
| TAJB686*010#NJ  | B            | 68                  | 10                      | 85                           | 7                          | 125                             | 6.8                 | 6                 | 1.4                            | 246                     | 222  | 99    | 1               |
| TAJC686*010#NJ  | C            | 68                  | 10                      | 85                           | 7                          | 125                             | 6.8                 | 6                 | 1.3                            | 291                     | 262  | 116   | 1               |
| TAJW686*010#NJ  | W            | 68                  | 10                      | 85                           | 7                          | 125                             | 6.8                 | 6                 | 1.2                            | 274                     | 246  | 110   | 1               |
| TAJY686*010#NJ  | Y            | 68                  | 10                      | 85                           | 7                          | 125                             | 6.8                 | 6                 | 0.9                            | 373                     | 335  | 149   | 1 <sup>1)</sup> |
| TAJB107*010#NJ  | B            | 100                 | 10                      | 85                           | 7                          | 125                             | 10                  | 8                 | 1.4                            | 246                     | 222  | 99    | 1               |
| TAJC107*010#NJ  | C            | 100                 | 10                      | 85                           | 7                          | 125                             | 10                  | 8                 | 1.2                            | 303                     | 272  | 121   | 1               |
| TAJD107*010#NJ  | D            | 100                 | 10                      | 85                           | 7                          | 125                             | 10                  | 6                 | 0.9                            | 408                     | 367  | 163   | 1               |
| TAJW107*010#NJ  | W            | 100                 | 10                      | 85                           | 7                          | 125                             | 10                  | 6                 | 0.4                            | 474                     | 427  | 190   | 1               |
| TAJX107*010#NJ  | X            | 100                 | 10                      | 85                           | 7                          | 125                             | 10                  | 8                 | 0.9                            | 333                     | 300  | 133   | 1 <sup>1)</sup> |
| TAJY107*010#NJ  | Y            | 100                 | 10                      | 85                           | 7                          | 125                             | 10                  | 6                 | 0.9                            | 373                     | 335  | 149   | 1 <sup>1)</sup> |
| TAJC157*010#NJ  | C            | 150                 | 10                      | 85                           | 7                          | 125                             | 15                  | 8                 | 0.9                            | 350                     | 315  | 140   | 1               |
| TAJD157*010#NJ  | D            | 150                 | 10                      | 85                           | 7                          | 125                             | 15                  | 8                 | 0.9                            | 408                     | 367  | 163   | 1               |
| TAJE157*010#NJ  | E            | 150                 | 10                      | 85                           | 7                          | 125                             | 15                  | 8                 | 0.9                            | 428                     | 385  | 171   | 1 <sup>1)</sup> |
| TAJF157*010#NJ  | F            | 150                 | 10                      | 85                           | 7                          | 125                             | 15                  | 10                | 0.3                            | 577                     | 520  | 231   | 1               |
| TAJX157M010#NJ  | X            | 150                 | 10                      | 85                           | 7                          | 125                             | 15                  | 6                 | 0.3                            | 577                     | 520  | 231   | 1 <sup>1)</sup> |
| TAJY157*010#NJ  | Y            | 150                 | 10                      | 85                           | 7                          | 125                             | 15                  | 6                 | 1.2                            | 323                     | 290  | 129   | 1 <sup>1)</sup> |
| TAJC227*010#NJ  | C            | 220                 | 10                      | 85                           | 7                          | 125                             | 22                  | 16                | 0.5                            | 469                     | 422  | 188   | 1               |
| TAJD227*010#NJ  | D            | 220                 | 10                      | 85                           | 7                          | 125                             | 22                  | 8                 | 0.5                            | 548                     | 493  | 219   | 1               |
| TAJE227*010#NJ  | E            | 220                 | 10                      | 85                           | 7                          | 125                             | 22                  | 8                 | 0.5                            | 574                     | 517  | 230   | 1 <sup>1)</sup> |
| TAJY227*010#NJ  | Y            | 220                 | 10                      | 85                           | 7                          | 125                             | 22                  | 10                | 0.5                            | 500                     | 450  | 200   | 1 <sup>1)</sup> |
| TAJD337*010#NJ  | D            | 330                 | 10                      | 85                           | 7                          | 125                             | 33                  | 8                 | 0.9                            | 408                     | 367  | 163   | 1               |
| TAJE337*010#NJ  | E            | 330                 | 10                      | 85                           | 7                          | 125                             | 33                  | 8                 | 0.9                            | 428                     | 385  | 171   | 1 <sup>1)</sup> |
| TAJV337*010#NJ  | V            | 330                 | 10                      | 85                           | 7                          | 125                             | 33                  | 10                | 0.9                            | 572                     | 474  | 211   | 1 <sup>1)</sup> |
| TAJE477*010#NJ  | E            | 470                 | 10                      | 85                           | 7                          | 125                             | 47                  | 10                | 0.5                            | 574                     | 517  | 230   | 1 <sup>1)</sup> |
| TAJU477*010RNJ  | U            | 470                 | 10                      | 85                           | 7                          | 125                             | 47                  | 12                | 0.5                            | 574                     | 517  | 230   | 1 <sup>1)</sup> |
| TAJV477*010#NJ  | V            | 470                 | 10                      | 85                           | 7                          | 125                             | 47                  | 10                | 0.5                            | 707                     | 636  | 283   | 1 <sup>1)</sup> |
| TAJE687M010#NJV | E            | 680                 | 10                      | 85                           | 7                          | 125                             | 68                  | 18                | 0.4                            | 642                     | 578  | 257   | 3               |
| TAJV687M010#NJV | V            | 680                 | 10                      | 85                           | 7                          | 125                             | 68                  | 18                | 0.4                            | 791                     | 712  | 316   | 3               |
| 16 Volt @ 85°C  |              |                     |                         |                              |                            |                                 |                     |                   |                                |                         |      |       |                 |
| TAJR684*016#NJ  | R            | 0.68                | 16                      | 85                           | 10                         | 125                             | 0.5                 | 4                 | 25                             | 47                      | 42   | 19    | 1               |
| TAJS684*016#NJ  | S            | 0.68                | 16                      | 85                           | 10                         | 125                             | 0.5                 | 4                 | 25                             | 51                      | 46   | 20    | 1               |
| TAJR105*016#NJ  | R            | 1                   | 16                      | 85                           | 10                         | 125                             | 0.5                 | 4                 | 20                             | 52                      | 47   | 21    | 1               |
| TAJS105*016#NJ  | S            | 1                   | 16                      | 85                           | 10                         | 125                             | 0.5                 | 4                 | 15                             | 66                      | 59   | 26    | 1               |
| TAJT105*016#NJ  | T            | 1                   | 16                      | 85                           | 10                         | 125                             | 0.5                 | 4                 | 5                              | 126                     | 114  | 51    | 1               |
| TAJR155*016#NJ  | R            | 1.5                 | 16                      | 85                           | 10                         | 125                             | 0.5                 | 6                 | 10                             | 74                      | 67   | 30    | 1               |
| TAJS155*016#NJ  | S            | 1.5                 | 16                      | 85                           | 10                         | 125                             | 0.5                 | 6                 | 12                             | 74                      | 66   | 29    | 1               |
| TAJA225*016#NJ  | A            | 2.2                 | 16                      | 85                           | 10                         | 125                             | 0.5                 | 6                 | 6.5                            | 107                     | 97   | 43    | 1               |
| TAJR225*016#NJ  | R            | 2.2                 | 16                      | 85                           | 10                         | 125                             | 0.5                 | 6                 | 6.5                            | 92                      | 83   | 37    | 1               |
| TAJS225*016#NJ  | S            | 2.2                 | 16                      | 85                           | 10                         | 125                             | 0.5                 | 6                 | 6                              | 104                     | 94   | 42    | 1               |
| TAJT225*016#NJ  | T            | 2.2                 | 16                      | 85                           | 10                         | 125                             | 0.5                 | 6                 | 6.5                            | 111                     | 100  | 44    | 1               |
| TAJA335*016#NJ  | A            | 3.3                 | 16                      | 85                           | 10                         | 125                             | 0.5                 | 6                 | 5                              | 122                     | 110  | 49    | 1               |
| TAJB335*016#NJ  | B            | 3.3                 | 16                      | 85                           | 10                         | 125                             | 0.5                 | 6                 | 4.5                            | 137                     | 124  | 55    | 1               |
| TAJR335*016#NJ  | R            | 3.3                 | 16                      | 85                           | 10                         | 125                             | 0.5                 | 8                 | 5                              | 105                     | 94   | 42    | 1               |
| TAJS335*016#NJ  | S            | 3.3                 | 16                      | 85                           | 10                         | 125                             | 0.5                 | 6                 | 5                              | 114                     | 103  | 46    | 1               |
| TAJT335*016#NJ  | T            | 3.3                 | 16                      | 85                           | 10                         | 125                             | 0.5                 | 6                 | 5                              | 126                     | 114  | 51    | 1               |
| TAJA475*016#NJ  | A            | 4.7                 | 16                      | 85                           | 10                         | 125                             | 0.8                 | 6                 | 4                              | 137                     | 123  | 55    | 1               |
| TAJB475*016#NJ  | B            | 4.7                 | 16                      | 85                           | 10                         | 125                             | 0.8                 | 6                 | 3.5                            | 156                     | 140  | 62    | 1               |
| TAJK475*016#NJ  | K            | 4.7                 | 16                      | 85                           | 10                         | 125                             | 0.8                 | 6                 | 3.1                            | 139                     | 125  | 56    | 1               |
| TAJP475*016#NJ  | P            | 4.7                 | 16                      | 85                           | 10                         | 125                             | 0.8                 | 8                 | 5                              | 110                     | 99   | 44    | 1               |
| TAJS475*016#NJ  | S            | 4.7                 | 16                      | 85                           | 10                         | 125                             | 0.8                 | 8                 | 4                              | 127                     | 115  | 51    | 1               |
| TAJT475*016#NJ  | T            | 4.7                 | 16                      | 85                           | 10                         | 125                             | 0.8                 | 6                 | 3.1                            | 161                     | 145  | 64    | 1               |
| TAJA685*016#NJ  | A            | 6.8                 | 16                      | 85                           | 10                         | 125                             | 1.1                 | 6                 | 3.5                            | 146                     | 132  | 59    | 1               |
| TAJB685*016#NJ  | B            | 6.8                 | 16                      | 85                           | 10                         | 125                             | 1.1                 | 6                 | 2.5                            | 184                     | 166  | 74    | 1               |
| TAJS685*016#NJ  | S            | 6.8                 | 16                      | 85                           | 10                         | 125                             | 1.1                 | 8                 | 2.4                            | 165                     | 148  | 66    | 1               |
| TAJT685*016#NJ  | T            | 6.8                 | 16                      | 85                           | 10                         | 125                             | 1.1                 | 6                 | 3.5                            | 151                     | 136  | 60    | 1               |
| TAJA106*016#NJ  | A            | 10                  | 16                      | 85                           | 10                         | 125                             | 1.6                 | 6                 | 3                              | 158                     | 142  | 63    | 1               |
| TAJB106*016#NJ  | B            | 10                  | 16                      | 85                           | 10                         | 125                             | 1.6                 | 6                 | 2.8                            | 174                     | 157  | 70    | 1               |
| TAJC106*016#NJ  | C            | 10                  | 16                      | 85                           | 10                         | 125                             | 1.6                 | 6                 | 2                              | 235                     | 211  | 94    | 1               |
| TAJT106*016#NJ  | T            | 10                  | 16                      | 85                           | 10                         | 125                             | 1.6                 | 8                 | 2.2                            | 191                     | 172  | 76    | 1               |
| TAJW106*016#NJ  | W            | 10                  | 16                      | 85                           | 10                         | 125                             | 1.6                 | 6                 | 2                              | 212                     | 191  | 85    | 1               |

### RATINGS & PART NUMBER REFERENCE

| AVX Part No.   | Case Size | Capacitance (µF) | Rated Voltage (V) | Rated Temperature (°C) | Category Voltage (V) | Category Temperature (°C) | DCL Max. (µA) | DF Max. (%) | ESR Max. @ 100kHz (Ω) | 100kHz RMS Current (mA) |      |       | MSL             |
|----------------|-----------|------------------|-------------------|------------------------|----------------------|---------------------------|---------------|-------------|-----------------------|-------------------------|------|-------|-----------------|
|                |           |                  |                   |                        |                      |                           |               |             |                       | 25°C                    | 85°C | 125°C |                 |
| TAJA156*016#NJ | A         | 15               | 16                | 85                     | 10                   | 125                       | 2.4           | 6           | 2                     | 194                     | 174  | 77    | 1               |
| TAJB156*016#NJ | B         | 15               | 16                | 85                     | 10                   | 125                       | 2.4           | 6           | 2.5                   | 184                     | 166  | 74    | 1               |
| TAJC156*016#NJ | C         | 15               | 16                | 85                     | 10                   | 125                       | 2.4           | 6           | 1.8                   | 247                     | 222  | 99    | 1               |
| TAJT156M016#NJ | T         | 15               | 16                | 85                     | 10                   | 125                       | 2.4           | 6           | 2                     | 200                     | 180  | 80    | 1               |
| TAJW156*016#NJ | W         | 15               | 16                | 85                     | 10                   | 125                       | 2.4           | 6           | 0.7                   | 359                     | 323  | 143   | 1               |
| TAJB226*016#NJ | B         | 22               | 16                | 85                     | 10                   | 125                       | 3.5           | 6           | 2.3                   | 192                     | 173  | 77    | 1               |
| TAJC226*016#NJ | C         | 22               | 16                | 85                     | 10                   | 125                       | 3.5           | 6           | 1                     | 332                     | 298  | 133   | 1               |
| TAJD226*016#NJ | D         | 22               | 16                | 85                     | 10                   | 125                       | 3.5           | 6           | 1.1                   | 369                     | 332  | 148   | 1               |
| TAJW226*016#NJ | W         | 22               | 16                | 85                     | 10                   | 125                       | 3.5           | 6           | 1.6                   | 237                     | 213  | 95    | 1               |
| TAJB336*016#NJ | B         | 33               | 16                | 85                     | 10                   | 125                       | 5.3           | 8           | 2.1                   | 201                     | 181  | 80    | 1               |
| TAJC336*016#NJ | C         | 33               | 16                | 85                     | 10                   | 125                       | 5.3           | 6           | 1.5                   | 271                     | 244  | 108   | 1               |
| TAJD336*016#NJ | D         | 33               | 16                | 85                     | 10                   | 125                       | 5.3           | 6           | 0.9                   | 408                     | 367  | 163   | 1               |
| TAJW336*016#NJ | W         | 33               | 16                | 85                     | 10                   | 125                       | 5.3           | 6           | 1.5                   | 245                     | 220  | 98    | 1               |
| TAJY336*016#NJ | Y         | 33               | 16                | 85                     | 10                   | 125                       | 5.3           | 6           | 0.9                   | 373                     | 335  | 149   | 1 <sup>1)</sup> |
| TAJC476*016#NJ | C         | 47               | 16                | 85                     | 10                   | 125                       | 7.5           | 6           | 0.5                   | 469                     | 422  | 188   | 1               |
| TAJD476*016#NJ | D         | 47               | 16                | 85                     | 10                   | 125                       | 7.5           | 6           | 0.9                   | 408                     | 367  | 163   | 1               |
| TAJW476*016#NJ | W         | 47               | 16                | 85                     | 10                   | 125                       | 7.5           | 6           | 0.4                   | 474                     | 427  | 190   | 1               |
| TAJX476*016#NJ | X         | 47               | 16                | 85                     | 10                   | 125                       | 7.5           | 6           | 0.75                  | 365                     | 329  | 146   | 1 <sup>1)</sup> |
| TAJY476*016#NJ | Y         | 47               | 16                | 85                     | 10                   | 125                       | 7.5           | 6           | 0.7                   | 423                     | 380  | 169   | 1 <sup>1)</sup> |
| TAJC686*016#NJ | C         | 68               | 16                | 85                     | 10                   | 125                       | 10.9          | 6           | 1.3                   | 291                     | 262  | 116   | 1               |
| TAJD686*016#NJ | D         | 68               | 16                | 85                     | 10                   | 125                       | 10.9          | 6           | 0.9                   | 408                     | 367  | 163   | 1               |
| TAJF686*016#NJ | F         | 68               | 16                | 85                     | 10                   | 125                       | 10.9          | 10          | 0.4                   | 500                     | 450  | 200   | 1               |
| TAJX686*016#NJ | X         | 68               | 16                | 85                     | 10                   | 125                       | 10.9          | 8           | 0.6                   | 408                     | 367  | 163   | 1 <sup>1)</sup> |
| TAJY686*016#NJ | Y         | 68               | 16                | 85                     | 10                   | 125                       | 10.9          | 6           | 0.9                   | 373                     | 335  | 149   | 1 <sup>1)</sup> |
| TAJC107*016#NJ | C         | 100              | 16                | 85                     | 10                   | 125                       | 16            | 8           | 1                     | 332                     | 298  | 133   | 1               |
| TAJD107*016#NJ | D         | 100              | 16                | 85                     | 10                   | 125                       | 16            | 6           | 0.6                   | 500                     | 450  | 200   | 1               |
| TAJE107*016#NJ | E         | 100              | 16                | 85                     | 10                   | 125                       | 16            | 6           | 0.9                   | 428                     | 385  | 171   | 1 <sup>1)</sup> |
| TAJF107M016#NJ | F         | 100              | 16                | 85                     | 10                   | 125                       | 16            | 10          | 0.4                   | 500                     | 450  | 200   | 1               |
| TAJY107*016#NJ | Y         | 100              | 16                | 85                     | 10                   | 125                       | 16            | 8           | 0.9                   | 373                     | 335  | 149   | 1 <sup>1)</sup> |
| TAJD157*016#NJ | D         | 150              | 16                | 85                     | 10                   | 125                       | 24            | 6           | 0.9                   | 408                     | 367  | 163   | 1               |
| TAJE157*016#NJ | E         | 150              | 16                | 85                     | 10                   | 125                       | 23            | 8           | 0.3                   | 742                     | 667  | 297   | 1 <sup>1)</sup> |
| TAJV157*016#NJ | V         | 150              | 16                | 85                     | 10                   | 125                       | 24            | 8           | 0.5                   | 707                     | 636  | 283   | 1 <sup>1)</sup> |
| TAJY157M016#NJ | Y         | 150              | 16                | 85                     | 10                   | 125                       | 24            | 15          | 0.3                   | 645                     | 581  | 258   | 1 <sup>1)</sup> |
| TAJD227M016#NJ | D         | 220              | 16                | 85                     | 10                   | 125                       | 35.2          | 10          | 0.5                   | 548                     | 493  | 219   | 3               |
| TAJE227*016#NJ | E         | 220              | 16                | 85                     | 10                   | 125                       | 35.2          | 10          | 0.5                   | 574                     | 517  | 230   | 1 <sup>1)</sup> |
| TAJV227*016#NJ | V         | 220              | 16                | 85                     | 10                   | 125                       | 35.2          | 8           | 0.9                   | 527                     | 474  | 211   | 1 <sup>1)</sup> |
| TAJE337M016#NJ | E         | 330              | 16                | 85                     | 10                   | 125                       | 52.8          | 30          | 0.4                   | 642                     | 578  | 257   | 1 <sup>1)</sup> |
| 20 Volt @ 85°C |           |                  |                   |                        |                      |                           |               |             |                       |                         |      |       |                 |
| TAJR104*020#NJ | R         | 0.1              | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 25                    | 47                      | 42   | 19    | 1               |
| TAJS104*020#NJ | S         | 0.1              | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 25                    | 51                      | 46   | 20    | 1               |
| TAJR154*020#NJ | R         | 0.15             | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 25                    | 47                      | 42   | 19    | 1               |
| TAJS154*020#NJ | S         | 0.15             | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 25                    | 51                      | 46   | 20    | 1               |
| TAJR224*020#NJ | R         | 0.22             | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 25                    | 47                      | 42   | 19    | 1               |
| TAJS224*020#NJ | S         | 0.22             | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 25                    | 51                      | 46   | 20    | 1               |
| TAJR334*020#NJ | R         | 0.33             | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 25                    | 47                      | 42   | 19    | 1               |
| TAJS334*020#NJ | S         | 0.33             | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 25                    | 51                      | 46   | 20    | 1               |
| TAJR474*020#NJ | R         | 0.47             | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 25                    | 47                      | 42   | 19    | 1               |
| TAJS474*020#NJ | S         | 0.47             | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 25                    | 51                      | 46   | 20    | 1               |
| TAJR684*020#NJ | R         | 0.68             | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 20                    | 52                      | 47   | 21    | 1               |
| TAJS684*020#NJ | S         | 0.68             | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 25                    | 51                      | 46   | 20    | 1               |
| TAJT684*020#NJ | T         | 0.68             | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 15                    | 73                      | 66   | 29    | 1               |
| TAJA105*020#NJ | A         | 1                | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 9                     | 91                      | 82   | 37    | 1               |
| TAJR105*020#NJ | R         | 1                | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 20                    | 52                      | 47   | 21    | 1               |
| TAJS105*020#NJ | S         | 1                | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 12                    | 74                      | 66   | 29    | 1               |
| TAJT105*020#NJ | T         | 1                | 20                | 85                     | 13                   | 125                       | 0.5           | 4           | 9                     | 94                      | 85   | 38    | 1               |
| TAJA155*020#NJ | A         | 1.5              | 20                | 85                     | 13                   | 125                       | 0.5           | 6           | 6.5                   | 107                     | 97   | 43    | 1               |
| TAJP155*020#NJ | P         | 1.5              | 20                | 85                     | 13                   | 125                       | 0.5           | 6           | 9.6                   | 79                      | 71   | 32    | 1               |
| TAJR155*020#NJ | R         | 1.5              | 20                | 85                     | 13                   | 125                       | 0.5           | 6           | 9.6                   | 76                      | 68   | 30    | 1               |
| TAJS155*020#NJ | S         | 1.5              | 20                | 85                     | 13                   | 125                       | 0.5           | 6           | 5.4                   | 110                     | 99   | 44    | 1               |
| TAJT155*020#NJ | T         | 1.5              | 20                | 85                     | 13                   | 125                       | 0.5           | 6           | 6.5                   | 111                     | 100  | 44    | 1               |
| TAJA225*020#NJ | A         | 2.2              | 20                | 85                     | 13                   | 125                       | 0.5           | 6           | 5.3                   | 119                     | 107  | 48    | 1               |
| TAJB225*020#NJ | B         | 2.2              | 20                | 85                     | 13                   | 125                       | 0.5           | 6           | 3.5                   | 156                     | 140  | 62    | 1               |
| TAJP225*020#NJ | P         | 2.2              | 20                | 85                     | 13                   | 125                       | 0.5           | 6           | 8.3                   | 85                      | 77   | 34    | 1               |
| TAJR225*020#NJ | R         | 2.2              | 20                | 85                     | 13                   | 125                       | 0.5           | 6           | 6                     | 96                      | 86   | 38    | 1               |
| TAJS225*020#NJ | S         | 2.2              | 20                | 85                     | 13                   | 125                       | 0.5           | 6           | 4.5                   | 120                     | 108  | 48    | 1               |
| TAJT225*020#NJ | T         | 2.2              | 20                | 85                     | 13                   | 125                       | 0.5           | 6           | 6                     | 115                     | 104  | 46    | 1               |
| TAJA335*020#NJ | A         | 3.3              | 20                | 85                     | 13                   | 125                       | 0.7           | 6           | 4.5                   | 129                     | 116  | 52    | 1               |
| TAJB335*020#NJ | B         | 3.3              | 20                | 85                     | 13                   | 125                       | 0.7           | 6           | 3                     | 168                     | 151  | 67    | 1               |
| TAJT335*020#NJ | T         | 3.3              | 20                | 85                     | 13                   | 125                       | 0.7           | 6           | 3                     | 163                     | 147  | 65    | 1               |
| TAJA475*020#NJ | A         | 4.7              | 20                | 85                     | 13                   | 125                       | 0.9           | 6           | 4                     | 137                     | 123  | 55    | 1               |
| TAJB475*020#NJ | B         | 4.7              | 20                | 85                     | 13                   | 125                       | 0.9           | 6           | 3                     | 168                     | 151  | 67    | 1               |
| TAJT475*020#NJ | T         | 4.7              | 20                | 85                     | 13                   | 125                       | 0.9           | 6           | 3.1                   | 161                     | 145  | 64    | 1               |

### RATINGS & PART NUMBER REFERENCE

| AVX<br>Part No. | Case<br>Size | Capacitance<br>(μF) | Rated<br>Voltage<br>(V) | Rated<br>Temperature<br>(°C) | Category<br>Voltage<br>(V) | Category<br>Temperature<br>(°C) | DCL<br>Max.<br>(μA) | DF<br>Max.<br>(%) | ESR<br>Max.<br>@ 100kHz<br>(Ω) | 100kHz RMS Current (mA) |      |       | MSL             |
|-----------------|--------------|---------------------|-------------------------|------------------------------|----------------------------|---------------------------------|---------------------|-------------------|--------------------------------|-------------------------|------|-------|-----------------|
|                 |              |                     |                         |                              |                            |                                 |                     |                   |                                | 25°C                    | 85°C | 125°C |                 |
| TAJA685*020#NJ  | A            | 6.8                 | 20                      | 85                           | 13                         | 125                             | 1.4                 | 6                 | 2.4                            | 177                     | 159  | 71    | 1               |
| TAJB685*020#NJ  | B            | 6.8                 | 20                      | 85                           | 13                         | 125                             | 1.4                 | 6                 | 2.5                            | 184                     | 166  | 74    | 1               |
| TAJC685*020#NJ  | C            | 6.8                 | 20                      | 85                           | 13                         | 125                             | 1.4                 | 6                 | 2                              | 235                     | 211  | 94    | 1               |
| TAJT685*020#NJ  | T            | 6.8                 | 20                      | 85                           | 13                         | 125                             | 1.4                 | 6                 | 2.6                            | 175                     | 158  | 70    | 1               |
| TAJB106*020#NJ  | B            | 10                  | 20                      | 85                           | 13                         | 125                             | 2                   | 6                 | 2.1                            | 201                     | 181  | 80    | 1               |
| TAJC106*020#NJ  | C            | 10                  | 20                      | 85                           | 13                         | 125                             | 2                   | 6                 | 1.2                            | 303                     | 272  | 121   | 1               |
| TAJW106*020#NJ  | W            | 10                  | 20                      | 85                           | 13                         | 125                             | 2                   | 6                 | 1.9                            | 218                     | 196  | 87    | 1               |
| TAJB156*020#NJ  | B            | 15                  | 20                      | 85                           | 13                         | 125                             | 3                   | 6                 | 2                              | 206                     | 186  | 82    | 1               |
| TAJC156*020#NJ  | C            | 15                  | 20                      | 85                           | 13                         | 125                             | 3                   | 6                 | 1.7                            | 254                     | 229  | 102   | 1               |
| TAJW156*020#NJ  | W            | 15                  | 20                      | 85                           | 13                         | 125                             | 3                   | 6                 | 1.7                            | 230                     | 207  | 92    | 1               |
| TAJB226*020#NJ  | B            | 22                  | 20                      | 85                           | 13                         | 125                             | 4.4                 | 6                 | 1.8                            | 217                     | 196  | 87    | 1               |
| TAJC226*020#NJ  | C            | 22                  | 20                      | 85                           | 13                         | 125                             | 4.4                 | 6                 | 1.6                            | 262                     | 236  | 105   | 1               |
| TAJD226*020#NJ  | D            | 22                  | 20                      | 85                           | 13                         | 125                             | 4.4                 | 6                 | 0.9                            | 408                     | 367  | 163   | 1               |
| TAJW226*020#NJ  | W            | 22                  | 20                      | 85                           | 13                         | 125                             | 4.4                 | 6                 | 1.6                            | 237                     | 213  | 95    | 1               |
| TAJY226*020#NJ  | Y            | 22                  | 20                      | 85                           | 13                         | 125                             | 4.4                 | 6                 | 0.9                            | 373                     | 335  | 149   | 1 <sup>1)</sup> |
| TAJC336*020#NJ  | C            | 33                  | 20                      | 85                           | 13                         | 125                             | 6.6                 | 6                 | 1.5                            | 271                     | 244  | 108   | 1               |
| TAJD336*020#NJ  | D            | 33                  | 20                      | 85                           | 13                         | 125                             | 6.6                 | 6                 | 0.9                            | 408                     | 367  | 163   | 1               |
| TAJX336*020#NJ  | X            | 33                  | 20                      | 85                           | 13                         | 125                             | 6.6                 | 6                 | 0.5                            | 447                     | 402  | 179   | 1 <sup>1)</sup> |
| TAJY336*020#NJ  | Y            | 33                  | 20                      | 85                           | 13                         | 125                             | 6.6                 | 6                 | 0.6                            | 456                     | 411  | 183   | 1 <sup>1)</sup> |
| TAJC476*020#NJ  | C            | 47                  | 20                      | 85                           | 13                         | 125                             | 9.4                 | 6                 | 0.5                            | 469                     | 422  | 188   | 1               |
| TAJD476*020#NJ  | D            | 47                  | 20                      | 85                           | 13                         | 125                             | 9.4                 | 6                 | 0.9                            | 408                     | 367  | 163   | 1               |
| TAJE476*020#NJ  | E            | 47                  | 20                      | 85                           | 13                         | 125                             | 9.4                 | 6                 | 0.9                            | 428                     | 385  | 171   | 1 <sup>1)</sup> |
| TAJX476*020#NJ  | X            | 47                  | 20                      | 85                           | 13                         | 125                             | 9.4                 | 6                 | 0.4                            | 500                     | 450  | 200   | 1 <sup>1)</sup> |
| TAJY476*020#NJ  | Y            | 47                  | 20                      | 85                           | 13                         | 125                             | 9.4                 | 6                 | 0.9                            | 373                     | 335  | 149   | 1 <sup>1)</sup> |
| TAJC686M020#NJ  | C            | 68                  | 20                      | 85                           | 13                         | 125                             | 13.6                | 8                 | 0.5                            | 469                     | 422  | 188   | 1               |
| TAJD686*020#NJ  | D            | 68                  | 20                      | 85                           | 13                         | 125                             | 13.6                | 6                 | 0.4                            | 612                     | 551  | 245   | 1               |
| TAJE686*020#NJ  | E            | 68                  | 20                      | 85                           | 13                         | 125                             | 13.6                | 6                 | 0.9                            | 428                     | 385  | 171   | 1 <sup>1)</sup> |
| TAJY686*020#NJ  | Y            | 68                  | 20                      | 85                           | 13                         | 125                             | 13.6                | 6                 | 0.9                            | 373                     | 335  | 149   | 1 <sup>1)</sup> |
| TAJD107*020#NJ  | D            | 100                 | 20                      | 85                           | 13                         | 125                             | 20                  | 6                 | 0.5                            | 548                     | 493  | 219   | 1               |
| TAJE107*020#NJ  | E            | 100                 | 20                      | 85                           | 13                         | 125                             | 20                  | 6                 | 0.4                            | 642                     | 578  | 257   | 1 <sup>1)</sup> |
| TAJV107*020#NJ  | V            | 100                 | 20                      | 85                           | 13                         | 125                             | 20                  | 8                 | 0.9                            | 527                     | 474  | 211   | 1 <sup>1)</sup> |
| TAJE157*020#NJ  | E            | 150                 | 20                      | 85                           | 13                         | 125                             | 30                  | 8                 | 0.3                            | 742                     | 667  | 297   | 1 <sup>1)</sup> |
| TAJV157*020#NJ  | V            | 150                 | 20                      | 85                           | 13                         | 125                             | 30                  | 8                 | 0.3                            | 913                     | 822  | 365   | 1 <sup>1)</sup> |
| 25 Volt @ 85°C  |              |                     |                         |                              |                            |                                 |                     |                   |                                |                         |      |       |                 |
| TAJR154*025#NJ  | R            | 0.15                | 25                      | 85                           | 17                         | 125                             | 0.5                 | 4                 | 24                             | 48                      | 43   | 19    | 1               |
| TAJR224*025#NJ  | R            | 0.15                | 25                      | 85                           | 17                         | 125                             | 0.5                 | 4                 | 21                             | 51                      | 46   | 20    | 1               |
| TAJR334*025#NJ  | R            | 0.15                | 25                      | 85                           | 17                         | 125                             | 0.5                 | 4                 | 17                             | 57                      | 51   | 23    | 1               |
| TAJA474*025#NJ  | A            | 0.47                | 25                      | 85                           | 17                         | 125                             | 0.5                 | 4                 | 14                             | 73                      | 66   | 29    | 1               |
| TAJR474*025#NJ  | R            | 0.47                | 25                      | 85                           | 17                         | 125                             | 0.5                 | 4                 | 15                             | 61                      | 54   | 24    | 1               |
| TAJS474*025#NJ  | S            | 0.47                | 25                      | 85                           | 17                         | 125                             | 0.5                 | 4                 | 9                              | 85                      | 76   | 34    | 1               |
| TAJA684*025#NJ  | A            | 0.68                | 25                      | 85                           | 17                         | 125                             | 0.5                 | 4                 | 10                             | 87                      | 78   | 35    | 1               |
| TAJR684*025#NJ  | R            | 0.68                | 25                      | 85                           | 17                         | 125                             | 0.5                 | 4                 | 13                             | 65                      | 59   | 26    | 1               |
| TAJS684*025#NJ  | S            | 0.68                | 25                      | 85                           | 17                         | 125                             | 0.5                 | 4                 | 8                              | 90                      | 81   | 36    | 1               |
| TAJA105*025#NJ  | A            | 1                   | 25                      | 85                           | 17                         | 125                             | 0.5                 | 4                 | 8                              | 97                      | 87   | 39    | 1               |
| TAJP105*025#NJ  | P            | 1                   | 25                      | 85                           | 17                         | 125                             | 0.5                 | 4                 | 11                             | 74                      | 66   | 30    | 1               |
| TAJR105*025#NJ  | R            | 1                   | 25                      | 85                           | 17                         | 125                             | 0.5                 | 4                 | 8                              | 83                      | 75   | 33    | 1               |
| TAJS105*025#NJ  | S            | 1                   | 25                      | 85                           | 17                         | 125                             | 0.5                 | 4                 | 8                              | 90                      | 81   | 36    | 1               |
| TAJA155*025#NJ  | A            | 1.5                 | 25                      | 85                           | 17                         | 125                             | 0.5                 | 6                 | 7.5                            | 100                     | 90   | 40    | 1               |
| TAJB155*025#NJ  | B            | 1.5                 | 25                      | 85                           | 17                         | 125                             | 0.5                 | 6                 | 5                              | 130                     | 117  | 52    | 1               |
| TAJP155*025#NJ  | P            | 1.5                 | 25                      | 85                           | 17                         | 125                             | 0.5                 | 6                 | 9.6                            | 79                      | 71   | 32    | 1               |
| TAJS155*025#NJ  | S            | 1.5                 | 25                      | 85                           | 17                         | 125                             | 0.5                 | 6                 | 5.4                            | 110                     | 99   | 44    | 1               |
| TAJT155*025#NJ  | T            | 1.5                 | 25                      | 85                           | 17                         | 125                             | 0.5                 | 6                 | 5                              | 126                     | 114  | 51    | 1               |
| TAJA225*025#NJ  | A            | 2.2                 | 25                      | 85                           | 17                         | 125                             | 0.6                 | 6                 | 7                              | 104                     | 93   | 41    | 1               |
| TAJB225*025#NJ  | B            | 2.2                 | 25                      | 85                           | 17                         | 125                             | 0.6                 | 6                 | 4.5                            | 137                     | 124  | 55    | 1               |
| TAJT225*025#NJ  | T            | 2.2                 | 25                      | 85                           | 17                         | 125                             | 0.6                 | 6                 | 4.5                            | 133                     | 120  | 53    | 1               |
| TAJA335*025#NJ  | A            | 3.3                 | 25                      | 85                           | 17                         | 125                             | 0.8                 | 6                 | 3.7                            | 142                     | 128  | 57    | 1               |
| TAJB335*025#NJ  | B            | 3.3                 | 25                      | 85                           | 17                         | 125                             | 0.8                 | 6                 | 3.5                            | 156                     | 140  | 62    | 1               |
| TAJT335*025#NJ  | T            | 3.3                 | 25                      | 85                           | 17                         | 125                             | 0.8                 | 6                 | 3.5                            | 151                     | 136  | 60    | 1               |
| TAJW335*025#NJ  | W            | 3.3                 | 25                      | 85                           | 17                         | 125                             | 0.8                 | 6                 | 1.6                            | 237                     | 213  | 95    | 1               |
| TAJA475*025#NJ  | A            | 4.7                 | 25                      | 85                           | 17                         | 125                             | 1.2                 | 6                 | 3.1                            | 156                     | 140  | 62    | 1               |
| TAJB475*025#NJ  | B            | 4.7                 | 25                      | 85                           | 17                         | 125                             | 1.2                 | 6                 | 1.5                            | 238                     | 214  | 95    | 1               |
| TAJT475*025#NJ  | T            | 4.7                 | 25                      | 85                           | 17                         | 125                             | 1.2                 | 6                 | 3.1                            | 161                     | 145  | 64    | 1               |
| TAJW475*025#NJ  | W            | 4.7                 | 25                      | 85                           | 17                         | 125                             | 1.2                 | 6                 | 1.2                            | 274                     | 246  | 110   | 1               |
| TAJB685*025#NJ  | B            | 6.8                 | 25                      | 85                           | 17                         | 125                             | 1.7                 | 6                 | 2.8                            | 174                     | 157  | 70    | 1               |
| TAJC685*025#NJ  | C            | 6.8                 | 25                      | 85                           | 17                         | 125                             | 1.7                 | 6                 | 2                              | 235                     | 211  | 94    | 1               |
| TAJW685*025#NJ  | W            | 6.8                 | 25                      | 85                           | 17                         | 125                             | 1.7                 | 6                 | 2                              | 212                     | 191  | 85    | 1               |
| TAJB106*025#NJ  | B            | 10                  | 25                      | 85                           | 17                         | 125                             | 2.5                 | 6                 | 2.5                            | 184                     | 166  | 74    | 1               |
| TAJC106*025#NJ  | C            | 10                  | 25                      | 85                           | 17                         | 125                             | 2.5                 | 6                 | 1.8                            | 247                     | 222  | 99    | 1               |
| TAJD106*025#NJ  | D            | 10                  | 25                      | 85                           | 17                         | 125                             | 2.5                 | 6                 | 1.2                            | 354                     | 318  | 141   | 1               |
| TAJW106*025#NJ  | W            | 10                  | 25                      | 85                           | 17                         | 125                             | 2.5                 | 6                 | 1.8                            | 224                     | 201  | 89    | 1               |
| TAJC156*025#NJ  | C            | 15                  | 25                      | 85                           | 17                         | 125                             | 3.8                 | 6                 | 1.6                            | 262                     | 236  | 105   | 1               |

### RATINGS & PART NUMBER REFERENCE

| AVX Part No.          | Case Size | Capacitance (μF) | Rated Voltage (V) | Rated Temperature (°C) | Category Voltage (V) | Category Temperature (°C) | DCL Max. (μA) | DF Max. (%) | ESR Max. @ 100kHz (Ω) | 100kHz RMS Current (mA) |      |       | MSL             |
|-----------------------|-----------|------------------|-------------------|------------------------|----------------------|---------------------------|---------------|-------------|-----------------------|-------------------------|------|-------|-----------------|
|                       |           |                  |                   |                        |                      |                           |               |             |                       | 25°C                    | 85°C | 125°C |                 |
| TAJD156*025#NJ        | D         | 15               | 25                | 85                     | 17                   | 125                       | 3.8           | 6           | 1                     | 387                     | 349  | 155   | 1               |
| TAJY156*025#NJ        | Y         | 15               | 25                | 85                     | 17                   | 125                       | 3.8           | 6           | 1                     | 354                     | 318  | 141   | 1 <sup>1)</sup> |
| TAJC226*025#NJ        | C         | 22               | 25                | 85                     | 17                   | 125                       | 5.5           | 6           | 1.4                   | 280                     | 252  | 112   | 1               |
| TAJD226*025#NJ        | D         | 22               | 25                | 85                     | 17                   | 125                       | 5.5           | 6           | 0.9                   | 408                     | 367  | 163   | 1               |
| TAJF226*025#NJ        | F         | 22               | 25                | 85                     | 17                   | 125                       | 5.5           | 6           | 1                     | 316                     | 285  | 126   | 1               |
| TAJY226*025#NJ        | Y         | 22               | 25                | 85                     | 17                   | 125                       | 5.5           | 6           | 0.8                   | 395                     | 356  | 158   | 1 <sup>1)</sup> |
| TAJC336*025#NJ        | C         | 33               | 25                | 85                     | 17                   | 125                       | 8.3           | 6           | 0.9                   | 350                     | 315  | 140   | 1               |
| TAJD336*025#NJ        | D         | 33               | 25                | 85                     | 17                   | 125                       | 8.3           | 6           | 0.9                   | 408                     | 367  | 163   | 1               |
| TAJE336*025#NJ        | E         | 33               | 25                | 85                     | 17                   | 125                       | 8.3           | 6           | 0.9                   | 428                     | 385  | 171   | 1 <sup>1)</sup> |
| TAJY336*025#NJ        | Y         | 33               | 25                | 85                     | 17                   | 125                       | 8.3           | 6           | 0.5                   | 500                     | 450  | 200   | 1 <sup>1)</sup> |
| TAJD476*025#NJ        | D         | 47               | 25                | 85                     | 17                   | 125                       | 11.8          | 6           | 0.9                   | 408                     | 367  | 163   | 1               |
| TAJE476*025#NJ        | E         | 47               | 25                | 85                     | 17                   | 125                       | 11.8          | 6           | 0.9                   | 428                     | 385  | 171   | 1 <sup>1)</sup> |
| TAJY476*025#NJ        | Y         | 47               | 25                | 85                     | 17                   | 125                       | 11.8          | 6           | 0.9                   | 373                     | 335  | 149   | 1 <sup>1)</sup> |
| TAJD686*025#NJ        | D         | 68               | 25                | 85                     | 17                   | 125                       | 17            | 6           | 0.9                   | 408                     | 367  | 163   | 1               |
| TAJE686*025#NJ        | E         | 68               | 25                | 85                     | 17                   | 125                       | 17            | 6           | 0.9                   | 428                     | 385  | 171   | 1 <sup>1)</sup> |
| TAJV686*025#NJ        | V         | 68               | 25                | 85                     | 17                   | 125                       | 17            | 6           | 0.9                   | 527                     | 474  | 211   | 1 <sup>1)</sup> |
| TAJE107*025#NJ        | E         | 100              | 25                | 85                     | 17                   | 125                       | 25            | 10          | 0.3                   | 742                     | 667  | 297   | 1 <sup>1)</sup> |
| TAJV107*025#NJ        | V         | 100              | 25                | 85                     | 17                   | 125                       | 25            | 8           | 0.4                   | 791                     | 712  | 316   | 1 <sup>1)</sup> |
| TAJV157M025#NJ        | V         | 150              | 25                | 85                     | 17                   | 125                       | 37.5          | 10          | 0.4                   | 791                     | 712  | 316   | 1 <sup>1)</sup> |
| <b>35 Volt @ 85°C</b> |           |                  |                   |                        |                      |                           |               |             |                       |                         |      |       |                 |
| TAJA104*035#NJ        | A         | 0.1              | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 24                    | 56                      | 50   | 22    | 1               |
| TAJR104*035#NJ        | R         | 0.1              | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 29                    | 44                      | 39   | 17    | 1               |
| TAJS104*035#NJ        | S         | 0.1              | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 24                    | 52                      | 47   | 21    | 1               |
| TAJA154*035#NJ        | A         | 0.15             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 21                    | 60                      | 54   | 24    | 1               |
| TAJR154*035#NJ        | R         | 0.15             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 24                    | 48                      | 43   | 19    | 1               |
| TAJS154*035#NJ        | S         | 0.15             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 21                    | 56                      | 50   | 22    | 1               |
| TAJA224*035#NJ        | A         | 0.22             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 18                    | 65                      | 58   | 26    | 1               |
| TAJR224*035#NJ        | R         | 0.22             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 21                    | 51                      | 46   | 20    | 1               |
| TAJS224*035#NJ        | S         | 0.22             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 18                    | 60                      | 54   | 24    | 1               |
| TAJA334*035#NJ        | A         | 0.33             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 15                    | 71                      | 64   | 28    | 1               |
| TAJR334*035#NJ        | R         | 0.33             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 17                    | 57                      | 51   | 23    | 1               |
| TAJS334*035#NJ        | S         | 0.33             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 15                    | 66                      | 59   | 26    | 1               |
| TAJA474*035#NJ        | A         | 0.47             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 12                    | 79                      | 71   | 32    | 1               |
| TAJB474*035#NJ        | B         | 0.47             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 10                    | 92                      | 83   | 37    | 1               |
| TAJR474*035#NJ        | R         | 0.47             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 15                    | 61                      | 54   | 24    | 1               |
| TAJS474*035#NJ        | S         | 0.47             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 12                    | 74                      | 66   | 29    | 1               |
| TAJT474*035#NJ        | T         | 0.47             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 10                    | 89                      | 80   | 36    | 1               |
| TAJA684*035#NJ        | A         | 0.68             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 8                     | 97                      | 87   | 39    | 1               |
| TAJB684*035#NJ        | B         | 0.68             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 8                     | 103                     | 93   | 41    | 1               |
| TAJP684*035#NJ        | P         | 0.68             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 13                    | 68                      | 61   | 27    | 1               |
| TAJS684*035#NJ        | S         | 0.68             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 8                     | 90                      | 81   | 36    | 1               |
| TAJT684*035#NJ        | T         | 0.68             | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 8                     | 100                     | 90   | 40    | 1               |
| TAJA105*035#NJ        | A         | 1                | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 7.5                   | 100                     | 90   | 40    | 1               |
| TAJB105*035#NJ        | B         | 1                | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 6.5                   | 114                     | 103  | 46    | 1               |
| TAJP105*035#NJ        | P         | 1                | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 11                    | 74                      | 66   | 30    | 1               |
| TAJS105*035#NJ        | S         | 1                | 35                | 85                     | 23                   | 125                       | 0.5           | 4           | 7.5                   | 93                      | 84   | 37    | 1               |
| TAJT105*035#NJ        | T         | 1                | 35                | 85                     | 23                   | 125                       | 5             | 4           | 6.5                   | 111                     | 100  | 44    | 1               |
| TAJA155*035#NJ        | A         | 1.5              | 35                | 85                     | 23                   | 125                       | 0.5           | 6           | 7.5                   | 100                     | 90   | 40    | 1               |
| TAJB155*035#NJ        | B         | 1.5              | 35                | 85                     | 23                   | 125                       | 0.5           | 6           | 5.2                   | 128                     | 115  | 51    | 1               |
| TAJC155*035#NJ        | C         | 1.5              | 35                | 85                     | 23                   | 125                       | 0.5           | 6           | 4.5                   | 156                     | 141  | 63    | 1               |
| TAJT155*035#NJ        | T         | 1.5              | 35                | 85                     | 23                   | 125                       | 0.5           | 6           | 5.2                   | 124                     | 112  | 50    | 1               |
| TAJA225*035#NJ        | A         | 2.2              | 35                | 85                     | 23                   | 125                       | 0.8           | 6           | 4.5                   | 129                     | 116  | 52    | 1               |
| TAJB225*035#NJ        | B         | 2.2              | 35                | 85                     | 23                   | 125                       | 0.8           | 6           | 4.2                   | 142                     | 128  | 57    | 1               |
| TAJC225*035#NJ        | C         | 2.2              | 35                | 85                     | 23                   | 125                       | 0.8           | 6           | 3.5                   | 177                     | 160  | 71    | 1               |
| TAJT225*035#NJ        | T         | 2.2              | 35                | 85                     | 23                   | 125                       | 0.8           | 6           | 4.2                   | 138                     | 124  | 55    | 1               |
| TAJB335*035#NJ        | B         | 3.3              | 35                | 85                     | 23                   | 125                       | 1.2           | 6           | 3.5                   | 156                     | 140  | 62    | 1               |
| TAJC335*035#NJ        | C         | 3.3              | 35                | 85                     | 23                   | 125                       | 1.2           | 6           | 2.5                   | 210                     | 189  | 84    | 1               |
| TAJW335*035#NJ        | W         | 3.3              | 35                | 85                     | 23                   | 125                       | 1.2           | 6           | 1.6                   | 237                     | 213  | 95    | 1               |
| TAJB475*035#NJ        | B         | 4.7              | 35                | 85                     | 23                   | 125                       | 1.6           | 6           | 3.1                   | 166                     | 149  | 66    | 1               |
| TAJC475*035#NJ        | C         | 4.7              | 35                | 85                     | 23                   | 125                       | 1.6           | 6           | 2.2                   | 224                     | 201  | 89    | 1               |
| TAJD475*035#NJ        | D         | 4.7              | 35                | 85                     | 23                   | 125                       | 1.6           | 6           | 1.5                   | 316                     | 285  | 126   | 1               |
| TAJW475*035#NJ        | W         | 4.7              | 35                | 85                     | 23                   | 125                       | 1.6           | 6           | 2.2                   | 202                     | 182  | 81    | 1               |
| TAJC685*035#NJ        | C         | 6.8              | 35                | 85                     | 23                   | 125                       | 2.4           | 6           | 1.8                   | 247                     | 222  | 99    | 1               |
| TAJD685*035#NJ        | D         | 6.8              | 35                | 85                     | 23                   | 125                       | 2.4           | 6           | 1.3                   | 340                     | 306  | 136   | 1               |
| TAJY685*035#NJ        | Y         | 6.8              | 35                | 85                     | 23                   | 125                       | 2.3           | 6           | 0.9                   | 373                     | 335  | 149   | 1 <sup>1)</sup> |
| TAJC106*035#NJ        | C         | 10               | 35                | 85                     | 23                   | 125                       | 3.5           | 6           | 1.6                   | 262                     | 236  | 105   | 1               |
| TAJD106*035#NJ        | D         | 10               | 35                | 85                     | 23                   | 125                       | 3.5           | 6           | 1                     | 387                     | 349  | 155   | 1               |
| TAJE106*035#NJ        | E         | 10               | 35                | 85                     | 23                   | 125                       | 3.5           | 6           | 0.9                   | 428                     | 385  | 171   | 1 <sup>1)</sup> |
| TAJX106*035#NJ        | X         | 10               | 35                | 85                     | 23                   | 125                       | 3.5           | 6           | 0.7                   | 378                     | 340  | 151   | 1 <sup>1)</sup> |
| TAJY106*035#NJ        | Y         | 10               | 35                | 85                     | 23                   | 125                       | 3.5           | 6           | 1                     | 354                     | 318  | 141   | 1 <sup>1)</sup> |
| TAJC156*035#NJ        | C         | 15               | 35                | 85                     | 23                   | 125                       | 5.3           | 6           | 1.4                   | 280                     | 252  | 112   | 1               |

## RATINGS &amp; PART NUMBER REFERENCE

| AVX Part No.   | Case Size | Capacitance (μF) | Rated Voltage (V) | Rated Temperature (°C) | Category Voltage (V) | Category Temperature (°C) | DCL Max. (μA) | DF Max. (%) | ESR Max. @ 100kHz (Ω) | 100kHz RMS Current (mA) |      |       | MSL             |
|----------------|-----------|------------------|-------------------|------------------------|----------------------|---------------------------|---------------|-------------|-----------------------|-------------------------|------|-------|-----------------|
|                |           |                  |                   |                        |                      |                           |               |             |                       | 25°C                    | 85°C | 125°C |                 |
| TAJD156*035#NJ | D         | 15               | 35                | 85                     | 23                   | 125                       | 5.3           | 6           | 0.9                   | 408                     | 367  | 163   | 1               |
| TAJY156*035#NJ | Y         | 15               | 35                | 85                     | 23                   | 125                       | 5.3           | 6           | 0.6                   | 456                     | 411  | 183   | 1 <sup>1)</sup> |
| TAJD226*035#NJ | D         | 22               | 35                | 85                     | 23                   | 125                       | 7.7           | 6           | 0.9                   | 408                     | 367  | 163   | 1               |
| TAJE226*035#NJ | E         | 22               | 35                | 85                     | 23                   | 125                       | 7.7           | 6           | 0.5                   | 574                     | 517  | 230   | 1 <sup>1)</sup> |
| TAJY226*035#NJ | Y         | 22               | 35                | 85                     | 23                   | 125                       | 7.7           | 6           | 0.5                   | 500                     | 450  | 200   | 1 <sup>1)</sup> |
| TAJD336*035#NJ | D         | 33               | 35                | 85                     | 23                   | 125                       | 11.6          | 6           | 0.9                   | 408                     | 367  | 163   | 1               |
| TAJE336*035#NJ | E         | 33               | 35                | 85                     | 23                   | 125                       | 11.6          | 6           | 0.9                   | 428                     | 385  | 171   | 1 <sup>1)</sup> |
| TAJV336*035#NJ | V         | 33               | 35                | 85                     | 23                   | 125                       | 11.6          | 6           | 0.5                   | 707                     | 636  | 283   | 1 <sup>1)</sup> |
| TAJD476*035#NJ | D         | 47               | 35                | 85                     | 23                   | 125                       | 16.5          | 6           | 0.9                   | 408                     | 367  | 163   | 3               |
| TAJE476*035#NJ | E         | 47               | 35                | 85                     | 23                   | 125                       | 16.5          | 6           | 0.9                   | 428                     | 385  | 171   | 1 <sup>1)</sup> |
| TAJV476*035#NJ | V         | 47               | 35                | 85                     | 23                   | 125                       | 16.5          | 6           | 0.4                   | 791                     | 712  | 316   | 1 <sup>1)</sup> |
| TAJV686*035#NJ | V         | 68               | 35                | 85                     | 23                   | 125                       | 23.8          | 6           | 0.5                   | 707                     | 363  | 283   | 1 <sup>1)</sup> |
| 50 Volt @ 85°C |           |                  |                   |                        |                      |                           |               |             |                       |                         |      |       |                 |
| TAJA104*050#NJ | A         | 0.1              | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 22                    | 58                      | 53   | 23    | 1               |
| TAJS104*050#NJ | S         | 0.1              | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 19                    | 58                      | 53   | 23    | 1               |
| TAJA154*050#NJ | A         | 0.15             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 15                    | 71                      | 64   | 28    | 1               |
| TAJB154*050#NJ | B         | 0.15             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 17                    | 71                      | 64   | 28    | 1               |
| TAJS154*050#NJ | S         | 0.15             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 16                    | 64                      | 57   | 25    | 1               |
| TAJA224*050#NJ | A         | 0.22             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 18                    | 65                      | 58   | 26    | 1               |
| TAJB224*050#NJ | B         | 0.22             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 14                    | 78                      | 70   | 31    | 1               |
| TAJP224*050#NJ | P         | 0.22             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 17                    | 59                      | 53   | 24    | 1               |
| TAJR224*050#NJ | R         | 0.22             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 17                    | 57                      | 51   | 23    | 1               |
| TAJS224*050#NJ | S         | 0.22             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 13                    | 71                      | 64   | 28    | 1               |
| TAJA334*050#NJ | A         | 0.33             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 17                    | 66                      | 60   | 27    | 1               |
| TAJB334*050#NJ | B         | 0.33             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 12                    | 84                      | 76   | 34    | 1               |
| TAJP334*050#NJ | P         | 0.33             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 17                    | 59                      | 53   | 24    | 1               |
| TAJR334M050#NJ | R         | 0.33             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 17                    | 57                      | 51   | 23    | 1               |
| TAJS334*050#NJ | S         | 0.33             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 11                    | 77                      | 69   | 31    | 1               |
| TAJT334*050#NJ | T         | 0.33             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 11                    | 85                      | 77   | 34    | 1               |
| TAJA474*050#NJ | A         | 0.47             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 9.5                   | 89                      | 80   | 36    | 1               |
| TAJB474*050#NJ | B         | 0.47             | 50                | 85                     | 33                   | 125                       | 0.7           | 4           | 9.5                   | 95                      | 85   | 38    | 1               |
| TAJC474*050#NJ | C         | 0.47             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 8                     | 117                     | 106  | 47    | 1               |
| TAJS474*050#NJ | S         | 0.47             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 9.5                   | 83                      | 74   | 33    | 1               |
| TAJT474*050#NJ | T         | 0.47             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 9.5                   | 92                      | 83   | 37    | 1               |
| TAJA684*050#NJ | A         | 0.68             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 7.9                   | 97                      | 88   | 39    | 1               |
| TAJB684*050#NJ | B         | 0.68             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 8                     | 103                     | 93   | 41    | 1               |
| TAJC684*050#NJ | C         | 0.68             | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 7                     | 125                     | 113  | 50    | 1               |
| TAJA105*050#NJ | A         | 1                | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 6.6                   | 107                     | 96   | 43    | 1               |
| TAJB105*050#NJ | B         | 1                | 50                | 85                     | 33                   | 125                       | 0.5           | 6           | 7                     | 110                     | 99   | 44    | 1               |
| TAJC105*050#NJ | C         | 1                | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 5.5                   | 141                     | 127  | 57    | 1               |
| TAJW105*050#NJ | W         | 1                | 50                | 85                     | 33                   | 125                       | 0.5           | 6           | 4.4                   | 143                     | 129  | 57    | 1               |
| TAJB155*050#NJ | B         | 1.5              | 50                | 85                     | 33                   | 125                       | 0.8           | 8           | 5.4                   | 125                     | 113  | 50    | 1               |
| TAJC155*050#NJ | C         | 1.5              | 50                | 85                     | 33                   | 125                       | 0.8           | 6           | 4.5                   | 156                     | 141  | 63    | 1               |
| TAJD155*050#NJ | D         | 1.5              | 50                | 85                     | 33                   | 125                       | 0.8           | 6           | 4                     | 194                     | 174  | 77    | 1               |
| TAJW155*050#NJ | W         | 1.5              | 50                | 85                     | 33                   | 125                       | 0.8           | 6           | 3.1                   | 170                     | 153  | 68    | 1               |
| TAJB225*050#NJ | B         | 2.2              | 50                | 85                     | 33                   | 125                       | 1.1           | 8           | 4.5                   | 137                     | 124  | 55    | 1               |
| TAJC225*050#NJ | C         | 2.2              | 50                | 85                     | 33                   | 125                       | 1.1           | 8           | 2.5                   | 210                     | 189  | 84    | 1               |
| TAJD225*050#NJ | D         | 2.2              | 50                | 85                     | 33                   | 125                       | 1.1           | 6           | 2.5                   | 245                     | 220  | 98    | 1               |
| TAJW225*050#NJ | W         | 2.2              | 50                | 85                     | 33                   | 125                       | 1.1           | 8           | 2.5                   | 190                     | 171  | 76    | 1               |
| TAJC335*050#NJ | C         | 3.3              | 50                | 85                     | 33                   | 125                       | 1.6           | 6           | 2.5                   | 210                     | 189  | 84    | 1               |
| TAJD335*050#NJ | D         | 3.3              | 50                | 85                     | 33                   | 125                       | 1.7           | 6           | 2                     | 274                     | 246  | 110   | 1               |
| TAJY335*050#NJ | Y         | 3.3              | 50                | 85                     | 33                   | 125                       | 1.7           | 4           | 1.5                   | 289                     | 260  | 115   | 1 <sup>1)</sup> |
| TAJC475*050#NJ | C         | 4.7              | 50                | 85                     | 33                   | 125                       | 0.5           | 4           | 1.4                   | 280                     | 252  | 112   | 1               |
| TAJD475*050#NJ | D         | 4.7              | 50                | 85                     | 33                   | 125                       | 2.4           | 6           | 1.4                   | 327                     | 295  | 131   | 1               |
| TAJX475*050#NJ | X         | 4.7              | 50                | 85                     | 33                   | 125                       | 2.4           | 6           | 1.0                   | 316                     | 285  | 126   | 3               |
| TAJY475*050#NJ | Y         | 4.7              | 50                | 85                     | 33                   | 125                       | 2.4           | 6           | 1.2                   | 323                     | 290  | 129   | 1 <sup>1)</sup> |
| TAJC685*050#NJ | C         | 6.8              | 50                | 85                     | 33                   | 125                       | 3.4           | 6           | 1                     | 332                     | 298  | 133   | 1               |
| TAJD685*050#NJ | D         | 6.8              | 50                | 85                     | 33                   | 125                       | 3.4           | 6           | 1                     | 387                     | 349  | 155   | 1               |
| TAJY685*050#NJ | Y         | 6.8              | 50                | 85                     | 33                   | 125                       | 3.4           | 6           | 0.9                   | 373                     | 335  | 149   | 1 <sup>1)</sup> |
| TAJD106*050#NJ | D         | 10               | 50                | 85                     | 33                   | 125                       | 5             | 6           | 0.8                   | 433                     | 390  | 173   | 1               |
| TAJE106*050#NJ | E         | 10               | 50                | 85                     | 33                   | 125                       | 5             | 6           | 1                     | 406                     | 366  | 162   | 1 <sup>1)</sup> |
| TAJV106*050#NJ | V         | 10               | 50                | 85                     | 33                   | 125                       | 5             | 6           | 0.65                  | 620                     | 558  | 248   | 1 <sup>1)</sup> |
| TAJD156*050#NJ | D         | 15               | 50                | 85                     | 33                   | 125                       | 7.5           | 6           | 0.6                   | 500                     | 450  | 200   | 1               |
| TAJE156*050#NJ | E         | 15               | 50                | 85                     | 33                   | 125                       | 7.5           | 6           | 0.6                   | 524                     | 472  | 210   | 1 <sup>1)</sup> |
| TAJV156*050#NJ | V         | 15               | 50                | 85                     | 33                   | 125                       | 7.5           | 6           | 0.6                   | 645                     | 581  | 258   | 1 <sup>1)</sup> |
| TAJV226*050#NJ | V         | 22               | 50                | 85                     | 33                   | 125                       | 11            | 8           | 0.6                   | 645                     | 581  | 258   | 1 <sup>1)</sup> |

1<sup>1)</sup> – Dry pack option (see How to order) is recommended for reduction of stress during soldering. Dry pack parts should be treated as MSL 3.

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5V RMS with a maximum DC bias of 2.2 volts. DCL is measured at rated voltage after 5 minutes.

For typical weight and composition see page 273.


**NOTE: AVX reserves the right to supply higher voltage ratings or tighter tolerance part in the same case size, to the same reliability standards.**

### QUALIFICATION TABLE


| TEST                         | TAJ series (Temperature range -55°C to +125°C)                                                                                                                                                            |               |               |                    |                                    |           |           |           |            |           |
|------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------|---------------|--------------------|------------------------------------|-----------|-----------|-----------|------------|-----------|
|                              | Condition                                                                                                                                                                                                 |               |               | Characteristics    |                                    |           |           |           |            |           |
| <b>Endurance</b>             | Apply rated voltage (Ur) at 85°C and / or category voltage (Uc) at 125°C for 2000 hours through a circuit impedance of $\leq 0.1\Omega/V$ . Stabilize at room temperature for 1-2 hours before measuring. |               |               | Visual examination | no visible damage                  |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | DCL                | 1.25 x initial limit               |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | $\Delta C/C$       | within $\pm 10\%$ of initial value |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | DF                 | initial limit                      |           |           |           |            |           |
| <b>Humidity</b>              | Store at 65°C and 95% relative humidity for 500 hours, with no applied voltage. Stabilize at room temperature and humidity for 1-2 hours before measuring.                                                |               |               | Visual examination | no visible damage                  |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | DCL                | 1.5 x initial limit                |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | $\Delta C/C$       | within $\pm 10\%$ of initial value |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | DF                 | 1.2 x initial limit                |           |           |           |            |           |
| <b>Temperature Stability</b> | Step                                                                                                                                                                                                      | Temperature°C | Duration(min) |                    | +20°C                              | -55°C     | +20°C     | +85°C     | +125°C     | +20°C     |
|                              | 1                                                                                                                                                                                                         | +20           | 15            | DCL                | IL*                                | n/a       | IL*       | 10 x IL*  | 12.5 x IL* | IL*       |
|                              | 2                                                                                                                                                                                                         | -55           | 15            |                    |                                    |           |           |           |            |           |
|                              | 3                                                                                                                                                                                                         | +20           | 15            | $\Delta C/C$       | n/a                                | +0/-10%   | $\pm 5\%$ | +10/-0%   | +12/-0%    | $\pm 5\%$ |
|                              | 4                                                                                                                                                                                                         | +85           | 15            |                    |                                    |           |           |           |            |           |
|                              | 5                                                                                                                                                                                                         | +125          | 15            | DF                 | IL*                                | 1.5 x IL* | IL*       | 1.5 x IL* | 2 x IL*    | IL*       |
|                              | 6                                                                                                                                                                                                         | +20           | 15            |                    |                                    |           |           |           |            |           |
| <b>Surge Voltage</b>         | Apply 1.3x category voltage (Uc) at 125°C for 1000 cycles of duration 6 min (30 sec charge, 5 min 30 sec discharge) through a charge / discharge resistance of 1000 $\Omega$                              |               |               | Visual examination | no visible damage                  |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | DCL                | initial limit                      |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | $\Delta C/C$       | within $\pm 5\%$ of initial value  |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | DF                 | initial limit                      |           |           |           |            |           |
| <b>Mechanical Shock</b>      | MIL-STD-202, Method 213, Condition C                                                                                                                                                                      |               |               | Visual examination | no visible damage                  |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | DCL                | initial limit                      |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | $\Delta C/C$       | within $\pm 5\%$ of initial value  |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | DF                 | initial limit                      |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | ESR                | initial limit                      |           |           |           |            |           |
| <b>Vibration</b>             | MIL-STD-202, Method 204, Condition D                                                                                                                                                                      |               |               | Visual examination | no visible damage                  |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | DCL                | initial limit                      |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | $\Delta C/C$       | within $\pm 5\%$ of initial value  |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | DF                 | initial limit                      |           |           |           |            |           |
|                              |                                                                                                                                                                                                           |               |               | ESR                | initial limit                      |           |           |           |            |           |

\*Initial Limit

### AVX SOLID ELECTROLYTE CAPACITOR ROADMAP



### Five Capacitor Construction Styles



### SERIES LINE UP: CONVENTIONAL SMD MnO<sub>2</sub>

