


PLCC Socket 1,27 mm

Series

081



Rated current	1,0 A
Rated voltage	100 V _{RMS} / V _{DC}
Withstand voltage	600 V _{RMS} for 1 minute
Material contact	Phosphor bronze
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +85°C
Max. processing temper.	260°C for 10 seconds

pitch
1,27

termination



max.
pincount
084


All dimensions in mm.

Variation



Removal Tool

086

PCB Layout



1



086-1-00

no. of contacts	see figure left	see figure left	see figure left	see figure left	see figure left
n	A	B	C	D	E
020	15,56	15,56	5,08	5,08	18,20
028	18,10	18,10	7,62	7,62	21,70
032	18,10	20,64	7,62	10,16	23,65
044	23,18	23,18	12,70	12,70	28,80
052	25,72	25,72	15,24	15,24	32,50
068	30,80	30,80	20,32	20,32	40,00
084	35,88	35,88	25,40	25,40	47,15

Colour:
0 = Black
7 = Brown

Packaging:
T = Tube

Variation

No. of contacts

Colour

Packaging



www.mpe-connector.de

Order code:

081-1-??-?-X-T0