


THIS IS OUR EXCLUSIVE PROPERTY. IT IS NOT TO BE COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY, NOR USED FOR MANUFACTURING WITHOUT OUR WRITTEN CONSENT, AND HAS TO BE RETURNED TO US IN CASE OF NO USAGE

DIT IS ONZE EIGENDOM EN MAG NOCH NAGEMAAKT, HERDRUKT, OVERGEMAAKT AAN DERDEN, NOCH VOOR FABRIKATIE GEBRUIKT WORDEN, ZONDER ONZE SCHRIFTELIJKE TOELATING. BIJ NIET GEBRUIK IS DE TERUGZENDING VERPLICHT.

REV.	DATE	DESCRIPTION	BY	C'K'D'



MATING FACE MATERIAL

- BODY : GLASS-FILLED POLYESTER. COLOUR: BLACK
- BAYONET RING : HIGH STRENGTH CuZn ALLOY, NICKEL PLATED
- COUPLING SPRING : SPRING STEEL
- O-RING: BLACK NEOPRENE.

PERFORMANCE CHARACTERISTICS


- OPERATING TEMPERATURE : -55 °C TO +125 °C.
- INSULATION RESISTANCE : 5000 MOhm MIN.
- TEST POTENTIAL : POWER CONTACTS: 4000 V AC EFF.
SIGNAL CONTACTS: 2000 V AC EFF.
- VOLTAGE: PER VDE 0110 : CLASS II - POLLUTION DEGREE 2

POWER CONTACTS: OVERVOLTAGE : 600 V AC eff. Phase to Ground
CREEP VOLTAGE: 630 V AC eff. Phase to phase

SIGNAL CONTACTS: OVERVOLTAGE : 300 V AC eff. Phase to Ground
CREEP VOLTAGE: 400 V AC eff. Phase to phase

NOTES

- 1.CONNECTOR ACCEPTS: Ø 2.4 MM MACHINED PIN CONTACTS IN POS. 1, 2, 3, AND GROUNDING.
Ø 1.6 MM MACHINED PIN CONTACTS IN POS. A, B, C, AND D.
- 2.CONTACTS ARE NOT INCLUDED AND HAVE TO BE ORDERED SEPARATELY.
- 3.MATING PART : UTG0148P(H)

GEN. ST.	01	02	03	04	05	06	07	08	0D	50	60	70	80	90																				
INT. ST.	10	11	12	13	14	18	20	31	32	33	34	38	39	40	42	43	44	45	46	48	56	70	72	73	75	76	81	82	83	84	88			
1DEC ±0,2 1DEC 2DEC ±0,1 2DEC ANGLES ±1° HOEKEN			APPR.		DATE		SIGN.		8 POS. METALOK BANTAM FEMALE PLUG																									
			DRAFT		28/09/07		ROUILLARD		CAT. No. UTG6148SN																									
WE RESERVE THE RIGHT TO CHANGE DIMENSIONS OR REQUIREMENTS WITHOUT PRIOR NOTICE.			CHECKED						 SOURIAU Connection Technology												SOURIAU				Route Nationale 23				72470 CHAMPAGNE				SCALE	
			PROD. MGR.																										2 / 1					
			PR.ENG.MGR.																															
ALL DIMENSIONS IN MM 			PR.MGT.MGR.						 SOURIAU Connection Technology												BS,A , 203017,002										NOT EXPORT CONTROLLED			
ALLE AFMETINGEN IN MM			REFERENCES / REFERENTIES							DRAWING NR. CUSTOMER DRAWING REVISION																								