


Dimensions: mm (In.)



POS. 1	POS. 2	POS. 3
		
ON	OFF	MOM
2-3	OPEN	2-1
		

Electrical Specifications:

- Rating: 2 A/250 VAC
5A/120 VAC or 28VDC
- Contact Resistance: 10m Ω max. initial @ 2-4VDC 100mA
- Insulation Resistance: 1,000M Ω min.
- Dielectric Strength: 1,000 V RMS@ sea level

Mechanical Specifications:

- Mechanical Life: 50,000 make-and-break cycles.
- Operating Temperature: -30°C to 85°C

Note:

- RoHS Compliant by Exemption

Materials:

- Case: dially phthalate (DAP)
- Actuator: nylon, black std.
- Bushing: brass, nickel plated
- Housing: stainless steel
- Switch Support: brass, tin plated
- Terminals / Contact: brass, silver or gold plated

Miniature Paddle Switch

Mountain Switch

Available from Mouser Electronics

www.mouser.com

1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[103-7011-EVX](#)