





ARRANGEMENT OF CONTACTS									
PARTS	B3098-3P	B3098-4P	B3098-5P	B3098-5A	B3098-5B	B3098-6P	B3098-7P	B3098-8P	B3098-8A
ANGLE	180°	216°	180°	240°	360°	240°	270°	270°	262°
POSITION OF VIEWS									

SPECIFICATIONS	
Dielectric strength	1,000V AC/1 Minute
Contact resistance	20M Ω Max.
Insulation resistance	100M Ω Min. at 500V DC
Rating	100V AC 2A



7	GROUNDING PIECE	1	BSR-H (0.2t)	[C5191R-H]	NICKEL	3-5U"
6	SCREW	1	2AAR1050	[A4510]	NICKEL	3-5U"
5	PLASTIC TRAIL	1	PVC		BLACK	UL
4	MAIN BODY	1	DIECAST		NICKEL	3-5U"
3	CLIP PLATE	1	SPCC SB (0.95t)		NICKEL	3-5U"
2	CONTACT TERMINAL	4	BSR-H (0.7t)	[C2680R]	SILVER PLATED	3-5U"
1	PLASTIC CORE	1	ABS	[777D]	BLACK	HB
P/N	PART NAME	Q'TY	MATERIAL		PLATING	REMARKS



DRAWN	KIDD	APP'D	UNIT	MM	TOLERANCE X ±0.20 XX ±0.10 XXX ±0.05 XXXX ±0.03 ANGULAR ±1°			TITLE	B3098-4P DIN CIRCULAR JACK		SHEET A
CHK'D								PART NO.	B3098-4P	DWG NO.	DIN JACK