



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.



REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
A	APPROVED FOR PRODUCTION	05/04/01	MCCORMICK
B	REVISED PICTORALLY ONLY	11/26/01	MCCORMICK
C	REVISED TOLERANCES (ECN 1489)	08/08/03	MCCORMICK
D	ECN 3124: UPDATE DWG FORMAT	12/19/07	D.GRIFFIN



BNC PLUG



2X BNC JACK



CIRCUIT DIAGRAM

SPECIFICATIONS;


MATERIALS;
SHELL: BRASS
CONTACTS: BRASS
INSULATOR: DELRIN

FINISH;
SHELL: NICKEL
CONTACT: GOLD

ELECTRICAL;
CHARACTERISTIC IMPEDANCE: 50 OHMS

RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm]
TOLERANCES TO BE:
.X ±.1 [2.5] ANGLES ±2°
.XX ±.01 [.25]
.XXX ±.005 [.13]
OVERALL CABLE LENGTH TOL:
≤ 60 [1524] +3 [76.2] / - 0
> 60 [1524] +5% / -0%



APPROVALS	DATE
DRAWN BY C.MCCORMICK	05/04/2001
CHECKED BY D.PARHAM	05/04/2001
APPROVED BY R.CARRICK	05/04/2001

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

L-com CONNECTIVITY PRODUCTS		45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
CATEGORY		COAXIAL	
PRODUCT DESCRIPTION		TEE ADAPTOR BNC M/F/F	
SIZE A	FSCM NO. 43321	DWG. NO. BA250	REV. D
SCALE: NONE		CAD FILE: BA250.SLDDRW	
		SHEET 1 OF 1	