

Flexible, Flame Retarded General Purpose Heat Shrinkable Polyolefin Tubing

Specification Values

PROPERTY	TEST METHOD	VALUES
Tensile Strength	ISO 37	10 MPa minimum
Ultimate Elongation	ISO 37	250% minimum
Specific Gravity	ISO 1183	1.35 maximum
Heat Shock	ASTM D2671 (4hrs at 250°C)	no dripping, cracking or flowing
Heat Ageing	ISO 188 (168hrs at 175°C)	
Ultimate Elongation	ISO 37	150% minimum
Low Temperature Flexibility	ASTM D2671 (4hrs at -55°C)	no cracking
Flammability (except Clear)	ASTM D876	pass
Electric Strength	IEC 243	20KV/mm minimum
Corrosion (Copper Contact and Copper Mirror)	ASTM D2671	no corrosion
Water Absorption	ISO 62	0.5 % maximum
Fluid Resistance	ISO 1817	
Gasoline		
Hydraulic Fluid		
Lubricating Oil		
Tensile Strength	ISO 37	7 MPa minimum
Ultimate Elongation		200% minimum
Fungus Resistance	ISO 846	
Tensile Strength	ISO 37	10 MPa minimum
Ultimate Elongation		250% minimum

Specification References/Approvals

TYPE	SHRINKTEK	MILITARY	UNDERWRITERS LAB	CSA
SP	ST6002	MIL-DTL 23053/5 DEF STAN 59-97 VG 95343 Pt5	UL 224 VW1 600V, 125°C FILE NO. E196685	600V, 125°C (OFT)

- Shrink Ratio 2:1
- Operating Temperature Range -55°C to 135°C
- Shrink Temperature 100°C
- Suitable for general use on high quality equipment requiring military/UL approvals



Ordering Data

ORDERING SIZE		MINIMUM EXPANSION		MAXIMUM RECOVERED		NOMINAL RECOVERED WALL		STANDARD REEL LENGTH
ins	mm	ins	mm	ins	mm	ins	mm	
$\frac{3}{64}$	1.2	0.046	1.2	0.023	0.6	0.018	0.45	150
$\frac{1}{16}$	1.6	0.063	1.6	0.031	0.8	0.018	0.45	150
$\frac{3}{32}$	2.4	0.093	2.4	0.046	1.2	0.019	0.50	150
$\frac{1}{8}$	3.2	0.125	3.2	0.062	1.6	0.019	0.50	150
$\frac{3}{16}$	4.8	0.187	4.8	0.093	2.4	0.019	0.50	150
$\frac{1}{4}$	6.4	0.250	6.4	0.125	3.2	0.026	0.65	75
$\frac{3}{8}$	9.5	0.375	9.5	0.187	4.8	0.026	0.65	75
$\frac{1}{2}$	12.7	0.500	12.7	0.250	6.4	0.026	0.65	75
$\frac{3}{4}$	19.0	0.750	19.1	0.375	9.5	0.029	0.75	60
1	25.4	1.000	25.4	0.500	12.7	0.035	0.90	60
$1\frac{1}{2}$	38.1	1.500	38.1	0.750	19.1	0.039	1.00	30
2	50.8	2.000	50.8	1.000	25.4	0.045	1.15	30
3	76.2	3.000	76.2	1.500	38.1	0.049	1.25	30
4	102.0	4.000	101.6	2.000	50.8	0.055	1.40	30

Standard Colours: black, clear, red, yellow, blue, white, green/yellow (other colours available to order)

Standard Packaging: on reels (see table for lengths). Also in 1.2m lengths

To order: specify product part number, size and colour (e.g. SP 4.8 black)

