



Common mode choke

Order code	TCK-086
Inductance	Pin 1-2: 156 μ H $\pm$ 35% (at 100 kHz / 100 mV) Pin 3-4: 156 μ H $\pm$ 35% (at 100 kHz / 100 mV)
Rated current	25 A max.
DCR	Pin 1-2: 2.5 m Ω Pin 3-4: 2.5 m Ω
Rated voltage	500 VDC
Operating temperature	-40 to +105°C

Impedance curve



Dimensions [mm]

A	16.6 $\pm$ 0.4
B	16.4 $\pm$ 0.4
C	12.5 max.
D	5.0 $\pm$ 1.0
E	14.1 $\pm$ 0.5
F	6.1 $\pm$ 0.5
G	$\varnothing$ 1.8 max.