


Secondary PRT with calibration options

Technical Data



- 5608: -200 °C to 500 °C (80 mm minimum immersion)
- 5609: -200 °C to 670 °C (100 mm minimum immersion)
- ± 0.01 short-term stability
- Calibration not included, NVLAP-accredited calibration optional, lab code 200348-0
- Dry-well reference with 90 ° bend

If you want a very stable thermometer from -200 °C to 670 °C and are particular about the calibration, then look no further than our 5609 Secondary Reference PRT. Its short-term stability at the triple point of water is only ± 10 mK and its one-quarter inch (6.35 mm) diameter lets you get accurate measurements in only 100 mm of immersion. The 5608 is also a ± 10 mK probe at the triple point of water, but its one-eighth inch (3.18 mm) diameter gets you accurate measurements from -200 °C to 500 °C with only 80 mm (3.1 in) of immersion. With multiple sheath length options on both of these probes, and an optional 90 ° bend at nine inches from the tip for dry-well applications, you can find the dimensions that are just right for your specific application.

The 5608 comes with a one-eighth inch (3.18 mm) diameter sheath in lengths of 9 inches or 12 inches. The 5609 comes with a one-quarter inch (6.35 mm) diameter sheath in lengths of 12 inches, 15 inches, and 20 inches; or with a 6 mm diameter in lengths of 300 mm, 400 mm, or 500 mm.

When looking for improved response time and reduced stem effect in shallow immersion, look for small diameter probes, because the measurement error called stem effect is caused by the diameter of the stem rather than the length of the stem.

Both of these probes have Inconel™ sheaths and are made using a special manufacturing process, giving them great precision over a wide temperature range. The sensors for these

probes are reference-grade platinum and feature four-wire connections with less noisy measurements than two-wire counterparts.

As standard, each probe includes its resistance value at the triple point of water. If calibration is desired, you can order a NVLAP-accredited calibration from our laboratory; lab code 200348-0. On the report of calibration, you'll get the test data and the ITS-90 calibration coefficients that you can easily input into any Fluke Calibration thermometer. If you order your probe with an INFO-CON connector, we'll program the coefficients directly into your connector, which loads the coefficients for you when you plug it into our 1522 Handheld Thermometer.

Call today for your free quote.

Specifications

Temperature range	5608: -200 °C to 500 °C 5609: -200 °C to 670 °C
Nominal resistance at 0.01 °C	100 Ω ± 0.5 Ω
Temperature coefficient	0.0039250 Ω/Ω/°C
Accuracy^[1]	See footnote
Short-term repeatability^[2]	± 0.01 °C at 0.010 °C ± 0.02 °C at max temp
Drift^[3]	± 0.01 °C at 0.010 °C ± 0.02 °C at max temp
Hysteresis	± 0.01 °C maximum
Sensor length	30 mm ± 5 mm (1.2 in ± 0.2 in)
Sensor location	3 mm ± 1 mm from tip (0.1 in ± 0.1 in)
Sheath material	Inconel™ 600
Minimum insulation resistance	5608: 500 MΩ at 23 °C, 20 MΩ at 500 °C 5609: 500 MΩ at 23 °C, 10 MΩ at 670 °C
Transition junction dimensions	71 mm x 12.5 mm (2.8 in x 0.49 in)
Minimum immersion length^[4] (<5 mK error)	5608: 80 mm (3.1 in) 5609: 100 mm (3.9 in)
Maximum immersion length	305 mm (12 in)
Response time^[5]	5608: 9 seconds typical 5609: 12 seconds typical
Self heating (in 0 °C bath)	5608: 75 mW/°C 5609: 50 mW/°C
Lead-wire cable type	Teflon,™ 24 AWG
Lead-wire length	1.8 m (6 ft)
Lead-wire temperature range	-50 °C to 250 °C
Calibration	Calibration not included; NVLAP-accredited calibration optional, lab code 200348-0. Please see calibration uncertainty table and its explanation of changeable uncertainties.
^[1] "Accuracy" is a difficult term when used to describe a resistance thermometer. The simplest way to derive basic "accuracy" is to combine the probe drift specification and calibration uncertainty with readout accuracy at a given temperature.	
^[2] Three thermal cycles from min to max temp, includes hysteresis, 99.9 % confidence	
^[3] After 100 hours at max temp, 99.9 % confidence	
^[4] Per ASTM E 644	

Calibration uncertainty for optional calibrations

	1922	1923	1924
-197 °C	0.010 °C	0.025 °C	0.025 °C
-38 °C	0.009 °C	0.025 °C	0.025 °C
0 °C	0.009 °C	0.025 °C	0.025 °C
157 °C	0.014 °C	0.030 °C	0.045 °C
232 °C	0.016 °C	0.030 °C	0.045 °C
420 °C	0.025 °C [†]	0.035 °C	0.045 °C
660 °C	n/a	0.050 °C	0.050 °C

Note: Uncertainties depend on lab practices, available information and equipment. A selection of calibrations are available to meet customer needs. 1930 calibrations are for complete thermometer systems. 1923 and 1924 calibrations are for PRTs only. As of 2008, model 1923 and 1930 calibrations are accredited. 1924 calibrations have not yet been accredited. Lab code 200348-0.

[†]1922-4-R uncertainties are ± 0.025 °C at 500 °C.

Ordering information

5608-9-X Secondary Reference PRT, 9 in x 1/8 in, -200 to 500 °C

5608-12-X Secondary Reference PRT, 12 in x 1/8 in, -200 to 500 °C

5609-12-X Secondary Reference PRT, 12 in x 1/4 in, -200 to 670 °C

5609-15-X Secondary Reference PRT, 15 in x 1/4 in, -200 to 670 °C

5609-20-X Secondary Reference PRT, 20 in x 1/4 in, -200 to 670 °C

5609-300-X Secondary Reference PRT, 300 mm x 6 mm, -200 to 670 °C

5609-400-X Secondary Reference PRT, 400 mm x 6 mm, -200 to 670 °C

5609-500-X Secondary Reference PRT, 500 mm x 6 mm, -200 to 670 °C

5609-9BND Secondary Reference PRT, 15 in x 1/4 in, 9 in bend, -200 °C to 670 °C, (optional calibration: 1924-4-7 only)

1922-4-R PRT Calibration, -200 °C to 500 °C, NVLAP Accredited

1923-4-7 PRT Calibration, -200 °C to 660 °C, NVLAP Accredited

1924-4-7 PRT Calibration, -200 °C to 660 °C, NIST-traceable

1930 Precision Digital Thermometer System Calibration by Comparison, NVLAP-accredited, lab code 200348-0

2601 Plastic PRT Case, for models ending -9, -12, and -300

2609 Plastic PRT Case, for models ending -15, -20, -400, and -500

X = termination. Specify "B" (bare wire), "D" (5-pin DIN for Tweener Thermometers), "G" (gold pins), "I" (INFO-CON for 1521 or 1522 Handheld Thermometers), "J" (banana plugs), "L" (mini spade lugs), "M" (mini banana plugs), or "S" (spade lugs).

Fluke Calibration. Precision, performance, confidence.™

Electrical	RF	Temperature	Pressure	Flow	Software
------------	----	-------------	----------	------	----------

Fluke Calibration
PO Box 9090,
Everett, WA 98206 U.S.A.

Fluke Europe B.V.
PO Box 1186, 5602 BD
Eindhoven, The Netherlands

For more information call:

In the U.S.A. (877) 355-3225 or Fax (425) 446-5116
In Europe/M-East/Africa +31 (0) 40 2675 200 or Fax +31 (0) 40 2675 222
In Canada (800)-36-FLUKE or Fax (905) 890-6866
From other countries +1 (425) 446-5500 or Fax +1 (425) 446-5116
Web access: <http://www.flukecal.com>

©2008-2015 Fluke Calibration. Specifications subject to change without notice.
Printed in U.S.A. 8/2015 3025877C_EN
Pub_ID: 11224-eng

Modification of this document is not permitted without written permission from Fluke Calibration.