




ISO: 5745, DIN: 5745

**Material:** Chrome-Vanadium. With Ergo handles in two-material combination.

**Cutting capacity:** Hard steel wire.

**IP** = Industrial pack



|  | <br>731415+ |  | A<br>mm | B<br>mm | C<br>mm | D<br>mm | E<br>mm | F<br>mm | G<br>mm |  |
|-----------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|---------|---------|---------|---------|---------|---------|---------|-------------------------------------------------------------------------------------|
| 2430 G-140                                                                        | 0102563                                                                                      | 5                                                                                 | 140     | 39      | 15      | 8       | 2.5     | 2.0     | 12      | 1.25 120                                                                            |
| 2430 G-160                                                                        | 0024070                                                                                      | 5                                                                                 | 160     | 49      | 16      | 8       | 3.0     | 2.5     | 12      | 1.5 160                                                                             |
| 2430 G-200                                                                        | 0100422                                                                                      | 5                                                                                 | 200     | 72      | 17      | 9       | 4.0     | 2.5     | 12      | 1.5 170                                                                             |
| 2430 G-140 IP                                                                     | 0102143                                                                                      | 5                                                                                 | 140     | 39      | 15      | 8       | 2.5     | 2.0     | 12      | 1.25 120                                                                            |
| 2430 G-160 IP                                                                     | 0100811                                                                                      | 5                                                                                 | 160     | 49      | 16      | 8       | 3.0     | 2.5     | 12      | 1.5 160                                                                             |
| 2430 G-200 IP                                                                     | 0100835                                                                                      | 5                                                                                 | 200     | 72      | 17      | 9       | 4.0     | 2.5     | 12      | 1.5 170                                                                             |