


## USB 2.0 All-in-One Keystone/Panel Mount Coupler Cable (F/F), Angled Connector, White, 1 ft.

MODEL NUMBER: **U060-001-KPA-WH**



1 ft. cable with angled connector adds a USB-A female port to a fixed location, such as a keystone wall plate or panel. Optional panel mount adapter included for installation in a motherboard, podium or kiosk.

### Description

The U060-001-KPA-WH USB 2.0 All-in-One Keystone/Panel Mount Coupler Cable (F/F) allows you to terminate a USB-A connection in a universal keystone wall plate or panel. Or you can use the included panel mount adapter to convert the female keystone jack for installation in a motherboard, podium or kiosk. One angled connector makes the cable easier to install in tight spaces.

This one-foot cable is recommended for completing an in-wall USB cable run, connecting two USB devices or extending the length of an existing USB application. It also can give your conference room, classroom, home theater room or retail establishment a professional, tidy look by hiding components out of sight in a closet or another room to eliminate cable clutter.

Molded nickel-plated connectors with corrosion-resistant gold-plated contacts provide maximum conductivity and minimize data loss. Premium foil and braid shielding delivers reliable, error-free signal quality and protection from EMI/RFI line noise that can distort or destroy data. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking. A rugged PVC jacket protects twisted 28 AWG data lines and 24 AWG power lines.

### Features

#### Mounts a USB 2.0 Female Port in a Fixed Location

- USB-A female keystone jack snaps easily into wall plate or panel
- Optional panel mount adapter allows installation in motherboard, podium or kiosk
- Hides components out of sight to eliminate cable clutter
- Angled female connector permits more flexible installation in tight spaces

### Highlights

- Angled female connector allows more flexible installation in tight spaces
- Gold-plated contacts for max conductivity and minimum data loss
- Optional panel mount adapter secures to podium or kiosk
- Keystone design snaps easily into standard wall plate or panel
- White in color to match most common wall plates

### Package Includes

- U060-001-KPA-WH USB 2.0 All-in-One Keystone/Panel Mount Coupler Cable (F/F), White, 1 ft.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

- White in color to match most common wall plates

#### Premium Construction for Superior Signal Transfer

- Premium foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded connectors with gold-plated contacts provide maximum conductivity and minimize data loss
- Integral strain relief helps cable and connectors move freely without stress or cracking
- Rugged PVC jacket protects twisted 28/24 AWG data/power lines
- Heavy-duty plastic housings designed for durability and long life

## Specifications

OVERVIEW	
UPC Code	037332209917
Technology	USB (all versions); USB 2.0 (High Speed)
INPUT	
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
Cable Length (cm)	30.48
PHYSICAL	
Wire Gauge (AWG)	28/24
Shipping Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.0700
Shipping Weight (kg)	0.03
Material of Construction	PVC, ABS
Color	White
Cable Outer Diameter (OD)	0.15mm
ENVIRONMENTAL	
Operating Temperature Range	32 to 104 F (0 to 40 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Relative Humidity	10% to 90% RH, Non-Condensing
CONNECTIONS	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Side A - Connector 1	USB A (FEMALE)
Side B - Connector 1	USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 2.0 (up to 480 Mbps)
<b>CERTIFICATIONS</b>	
Certifications	ROHS Compliant, CE
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2018 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>