

D

C

B

A




TYPT-1 / 类型-1

TYPT-2 / 类型-2


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	16DEC2015	DL	CW
	B	ECR-15-013292	24SEP2015	DL	CW
	B1	ECR-16-011552	11AUG2016	QY	CW
	B2	ECR-17-004602	01APR2017	CH	CW

- NOTES:
- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250 V
RATED CURRENT: 10 A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4 KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14-2.5 mm² (26-14 AWG)
CONTACT TYPE: CRIMP CONTACT
 - CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING:T20200X20XX000)

- 注释:
- 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4 KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14-2.5 mm² (26-14 AWG)
接线类型: 冷压接
 - 端子需要单独订购.
(订货号参考图面: T20200X20XX000)



DETAIL B
SCALE 5:1



DETAIL A
SCALE 5:1

T2020252201-Z00	HD-025-F/Z	HD-025 FEMALE INSERT(Z) HD-025母插(Z)	TYPE-2 类型-2
T2020252201-000	HD-025-F	HD-025 FEMALE INSERT HD-025母插	TYPE-1 类型-1
PART NUMBER 料号	PART DESCRIPTION 描述		

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 16JUL2015 DAVID LI	TE Connectivity			
DIMENSIONS: mm		CHK 16JUL2015 CHRIS WANG				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 16JUL2015 XU XIANG	NAME HD-025-F			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH		PRODUCT SPEC 108-137042 APPLICATION SPEC 114-137042 WEIGHT -	SIZE A2		CAGE CODE -	DRAWING NO T2020252201000
MATERIAL -		CUSTOMER DRAWING		RESTRICTED TO -	SCALE 3:2	SHEET 1 OF 1
				REV B2		