



PART NO.	DIM "A" ±.015 (±0.4)
DLCBST-1-01	1/16 (1.6)
DLCBST-2-01	1/8 (3.2)
DLCBST-3-01	3/16 (4.8)
DLCBST-4-01	1/4 (6.4)
DLCBST-5-01	5/16 (7.9)
DLCBST-6-01	3/8 (9.5)
DLCBST-7-01	7/16 (11.1)
DLCBST-8-01	1/2 (12.7)
DLCBST-9-01	9/16 (14.3)
DLCBST-10-01	5/8 (15.9)



TO SNAP-LOCK IN A .100±.002
(2.54±0.05) DIA. HOLE, IN A
.064 (1.63) MAX. THK. BD. (BOTH ENDS)



NOTES:

1. MATERIAL: NYLON 6/6 (RMS-01).
FLAME RETARDANT, NYLON (RMS-19),
AVIALABLE BY SPECIAL ORDER ONLY.
2. COLOR: NATURAL.

			TITLE: DUAL LOCKING CKT. BD. SUPPORT, TEARDROP					DWG IN IN (MM)	
			TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=1/64 ANG=1°	FILE # DLCBST	DWN: P.B.	APP:	FINAL		
C	CHANGED FILE NO. AND TITLE BLOCK	SM 04.27.01	MAT'L: SEE NOTES			DT: 03-07-95	DT:	PART #	
B	MAT'L RMS-19 ADDED	J.L. 12.29.97	RE: RICHCO, INC.			RICHCO INC.		SEE TABLE	
A	CONVERTED TO ACAD	PB 03.07.95				PO BOX 804238, CHICAGO, 60680			
REV	DESCRIPTION	ENGR DATE				(773) 539-4060		PRINT TYPE CA	