




PANEL CUT OUT
PANEL THK: .125 MAX. W/GASKET
.187 MAX. W/OUT GASKET
.062 MIN.

- NOTES:
- 1) MATERIAL: SEE TABLE
 - 2) FINISHES: SEE TABLE
 - 3) LABEL IS MARKED WITH P/N, BAR CODE, DESCRIPTION
 - 4) MATES WITH: RJ45 CORDSET
 - 5) ELECTRICAL DATA:
FIELD WIRING TO PCB: 8 THRU HOLES, PLUS SHIELD
MAX. VOLTAGE: 125V DC
MAX. CURRENT 1.5A
PROTECTION IP67
TEMPERATURE RANGE: -20°C TO 80°C
CSA & UL
CATEGORY RATING: CAT5e
 - 6) PACKAGING:
ASSEMBLIES ARE BAGGED SEPERATELY
IN POLY BAGS WITH BAR CODE LABEL ATTACHED
TO OUTSIDE OF BAG.
 - 7) ASSEMBLY IS RoHS COMPLIANT.

1	WHT/BLU
2	BLU/WHT
3	WHT/ORG
4	
5	
6	ORG/WHT
7	
8	
GND	DRAIN WIRE

WIRING DIAGRAM

SALES DRAWING

5	1	HEX NUT	LNP	BLACK
4	1	BULKHEAD GASKET	NITRILE	BLACK
3	1	O RING	VITON	BROWN
2	1	HOUSING	ABS	BLACK
1	1	RJ45 W/PCB SUB ASSY.	---	---
ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH

MODIFIED CUTOUT EC NO: IPG2013-0733 DRAWN: BWOODMAN CHKD: JPMURPHY APPR: JPMURPHY 2012/11/19 2012/12/04	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY BRUPERT	DATE 04/16/09	TITLE PC BOARD TO CABLE RECPT.				
			4 PLACES	± ---	± ---	CHECKED BY BWOODMAN	DATE 04/16/09					
			3 PLACES	± ---	± ---	APPROVED BY JPMURPHY	DATE 04/16/09	MOLEX MOLEX INCORPORATED				
			2 PLACES	± ---	± ---	MATERIAL NO. 1300550016	DOCUMENT NO. SD-130055-016					
			1 PLACE	± ---	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						
			ANGULAR ±1/2°									
REV			SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									