

**Input**

Rated input voltage	100 V ~ 240 V ac
Input voltage range	90 V ~ 264 V ac
Rated frequency	50~60 Hz
Frequency range	47~63 Hz
Rated input current	300 mA RMS max.
Inrush current	15 A max. at 115 / 30 A max. at 230 V ac cool start

Output

Output voltage	6 V dc at 2 A
Output min. current	0 A
Line regulation	± 1%
Load regulation	± 5%
Over voltage protection	7.1 ~ 7.9 V dc max. (output shut down)
Short circuit protection	output shut down and auto restart
Ripple voltage	150 mV (p-p) (100~240 V ac at full load)
Efficiency	60% min.

Safety and EMI

HI-POT	input to output	3000 V ac at 10 mA for 1 min.
Insulation resistance	input to output	> 100 M Ohm at 500 V dc
Safety approvals	UL/cUL	
EMI standard	meets EN55022 B	
RoHS compliant	yes	
Leakage current	0.25 mA	

Environmental

Storage temperature	-10°C ~ +70° C
Operating temperature	0°C ~ +40° C
Storage humidity	10~90%
Operating humidity	20~80%



CUI INC

Part No: DPS060200UPS-P5P-SZ


Description: switching power supply

Date: 4/05/2006

Unit: mm

Page No: 2 of 6

Label



**CUI INC**

Part No: DPS060200UPS-P5P-SZ

Description: switching power supply

Date: 4/05/2006


Unit: mm

Page No: 3 of 6

Mechanical Drawing

Tolerance: ± 1

Input plug	Direct plug-in UL type
Weight	114.5 g
Case size	60 L x 44 W x 25 H mm





Description: switching power supply

Page No: 4 of 6



CUI INC

Part No: DPS060200UPS-P5P-SZ

Description: switching power supply


Date: 4/05/2006

Unit: mm


Page No: 5 of 6

Individual Packaging

Tolerance: ± 1



product



"RoHS Compliant"



CUI INC

Part No: DPS060200UPS-P5P-SZ

Description: switching power supply

Date: 4/05/2006

Unit: mm

Page No: 6 of 6

Packaging

Tolerance: +7/-0

CARTON SIZE: 375*368*225mm

QTY: 80PCS(20*4)

"RoHS Compliant"

