



CONNECTION ELEMENTS

ISO-KF Small Flange Components


CLAMPING RING		DN ... ISO-KF	Part No.	A	B	C
Clamping ring half:	Aluminum 380.0/3.2162	10 – 16	211-001	45	61	16
Bolt & nut:	Steel nickel plated	20 – 25	211-002	55	72	16
		32 – 40	211-003	70	90	18
		50	211-004	95	123	25




RAPID FASTENING CLAMP		DN ... ISO-KF	Part No.	A	B	C
Spring:	Steel	10 – 16	211-005	52	70	16
Clamping ring half:	Aluminum 380.0/3.2162	20 – 25	211-006	61	81	16
Lever:	Polyamide	32 – 40	211-007	75	98	18




HOSE CLIP CLAMPING RING		DN ... ISO-KF	Part No.	A	B	C
Clamping ring half:	Aluminum 380.0/3.2162	10 – 16	211-016	42	54	16
Band:	Stainless steel 430/1.4016	20 – 25	211-017	52	64	16
Bolt & nutthread:	Steel zinc plated	32 – 40	211-018	67	79	16




CLAMPING ELEMENT		DN ... ISO-KF	Part No.	A	C
Clamping Element:	Aluminum 380.0/3.2162	10 – 16	211-008	52	18
Bolt:	Stainless steel	20 – 25	211-009	75	20
Nut:	Steel zinc plated	32 – 40	211-010	90	23
		50	211-011	115	28



CHAIN CLAMP		DN ... ISO-KF	Part No.	A	B	C
Chain link:	Aluminum 6081/3.2215	10 – 16	211-021	71	52.5	18
Screw & nut & bolts:	Stainless steel	20 – 25	211-022	82	65	18
		32 – 40	211-023	98	79	18
		50	211-024	117	97.5	20



CLAW GRIP		DN ... ISO-KF	Part No.	A	B	C	D	E	Set of
Claw:	Aluminum 6082/3.2215	10 – 50	211-015	19.5	11.5	12.5	20	14	4 pcs.
Screw & washer:	Stainless steel								



GLOBAL HEADQUARTERS:

Two Technology Place, East Syracuse, NY 13057 USA
Tel: +1.315.434.1100 Fax: +1.315.437.3803 E-mail: reachus@inficon.com

UNITED STATES FRANCE GERMANY LIECHTENSTEIN SWITZERLAND UNITED KINGDOM CHINA JAPAN KOREA SINGAPORE TAIWAN

Visit our website for contact information and other sales offices worldwide. www.inficon.com
Due to our continuing program of product improvements, specifications are subject to change without notice.
qiba01e1-b (2007-02) ©2007 INFICON Inc.