


OMNIMATE Signal - series LM

LM 3.50/06/90 3.2SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
www.weidmueller.com



Small, compact PCB terminal or -tier PCB terminal with proven clamping yoke connection and 3.5 mm pitch. Suitable for conductor cross-sections up to 1.5 mm².

- 0.20 - 1.50 mm² (IEC) / 28 - 14 AWG (UL)
- 320 V (IEC) / 300 V (UL)
- 16 A (IEC) / 10 A (UL)

General ordering data

Type	LM 3.50/06/90 3.2SN OR BX
Order No.	1845050000
Version	PCB terminal, 3.50 mm, No. of poles: 6, 90°, Solder pin length (l): 3.2 mm, tinned, Orange, Clamping yoke connection, Clamping range, rated connection, max.: 2.08 mm², Box
GTIN (EAN)	4032248357857
Qty.	50 pc(s).
Product data	IEC: 320 V / 16 A / 0.5 - 1.5 mm² UL: 300 V / 10 A / AWG 28 - AWG 14
Packaging	Box

OMNIMATE Signal - series LM
LM 3.50/06/90 3.2SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	3.82 g
------------	--------

System characteristics

Product family	OMNIMATE Signal - series LM	Wire connection method	Clamping yoke connection
Mounting onto the PCB	Solder connection	Conductor outlet direction	90°
Pitch in mm (P)	3.5 mm	Pitch in inches (P)	0.138 inch
No. of poles	6	Fitted by customer	Yes
Max. adjacent poles per row	24	Solder pin length (l)	3.2 mm
Solder pin dimensions	1.0 x 0.6 mm	Solder eyelet hole diameter (D)	1.3 mm
Solder eyelet hole diameter tolerance (D)+ 0,1 mm		Number of solder pins per pole	1
Screwdriver blade	0.4 x 2.5	Screwdriver blade standard	DIN 5264
Tightening torque, min.	0.2 Nm	Tightening torque, max.	0.25 Nm
Clamping screw	M 2	Stripping length	5 mm
L1 in mm	17.5 mm	L1 in inches	0.689 inch
Touch-safe protection acc. to DIN VDE 0470	IP 20	Touch-safe protection acc. to DIN VDE 57 106	Safe from finger touch
Volume resistance	3.60 mΩ		

Material data

Moisture Level (MSL)	3	Insulating material	PA
Colour	Orange	UL 94 flammability rating	V-2
CTI	≥ 600	Coating	1-3 µm Ni, 4-6 µm SN
Contact material	Cu-Leg	Contact surface	tinned
Operating temperature, min.	-50 °C	Operating temperature, max.	100 °C
Temperature range, installation, min.	-25 °C	Temperature range, installation, max.	100 °C

Connectable conductors

Clamping range, rated connection, min.	0.08 mm ²	Clamping range, rated connection, max.	2.08 mm ²
Wire connection cross section AWG, min.	AWG 28	Wire connection cross section AWG, max.	AWG 14
Solid, min. H05(07) V-U	0.5 mm ²	Solid, max. H05(07) V-U	1.5 mm ²
Flexible, min. H05(07) V-K	0.5 mm ²	Flexible, max. H05(07) V-K	1.5 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, min.	0.5 mm ²	w. plastic collar ferrule, DIN 46228 pt 4, max.	0.75 mm ²
Plug gauge acc. to EN 60999 a x b; Ø	2.4 mm x 1.5 mm		

CSA rating data

Institute (CSA)		Certificate No. (CSA)	154685-1202192
Rated voltage (Use group B)	300 V	Rated current (use group B)	10 A
Rated voltage (use group D)	300 V	Rated current (use group D)	10 A
Wire cross-section, AWG, min.	AWG 28	Wire cross-section, AWG, max.	AWG 14

OMNIMATE Signal - series LM
LM 3.50/06/90 3.2SN OR BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data**UL 1059 rating data**

Institute (UR)



Certificate No. (UR)

E60693

Rated voltage (use group B)	300 V
Rated voltage (use group D)	300 V
Wire cross-section, AWG, min.	AWG 28

Rated current (use group B)	10 A
Rated current (use group D)	10 A
Wire cross-section, AWG, max.	AWG 14

Rating data acc. to IEC 60664-1 / IEC 61984

Rated current, min. no. of poles (Tu=20°C)	16 A
Rated current, number of poles (Tu=40°C), min	14 A
Rated voltage for surge voltage class / pollution degree II/2	320 V
Rated voltage for surge voltage class / pollution degree III/3	160 V
Rated impulse voltage for surge voltage class/ pollution degree III/2	2.5 kV
Short-time withstand current resistance	3 x 1s with 72 A

Rated current, max. no. of poles (Tu=20°C)	12 A
Rated current, number of poles (Tu=40°C), max.	10 A
Rated voltage for surge voltage class / pollution degree III/2	160 V
Rated impulse voltage for surge voltage class/ pollution degree II/2	2.5 kV
Rated impulse voltage for surge voltage class/ contamination degree III/3	2.5 kV

Classifications

ETIM 3.0	EC001284	ETIM 4.0	EC002643
ETIM 5.0	EC002643	ETIM 6.0	EC002643
UNSPSC	30-21-18-01	eClass 6.2	27-26-11-01
eClass 7.1	27-44-04-01		

Notes

Notes

- Additional colours on request
- Rated current related to rated cross-section & min. No. of poles.
- Max. outer diameter of the conductor: 2.9 mm
- Wire end ferrule with plastic collar to DIN 46228/4
- P on drawing = pitch
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.

IPC conformity

The products are developed, manufactured and delivered according to the internationally recognised IPC-A-610 standard, category "permissible". More extensive demands on the products can be evaluated on request.

Approvals

Approvals



ROHS

Conform

OMNIMATE Signal - series LM LM 3.50/06/90 3.2SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data



Downloads

CAD Library (P-CAD Format - ASCII)	LM.zip
CAD Library (P-CAD Format - Standard)	LM.zip

OMNIMATE Signal - series LM LM 3.50/06/90 3.2SN OR BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings



Recommended wave soldering profiles

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Single Wave:



Double Wave:



Wave soldering profiles

Wired connection elements should be processed in accordance with the DIN EN 61760-1 standard. We have included two recommendations for practical wave soldering profiles, with which Weidmüller PCB terminals and connectors are qualified.

When choosing a suitable profile for your application, the following factors also need to be considered:

- PCB thickness
- Proportion of Cu in the layers
- Single/double-sided assembly
- Product range
- Heating and cooling rates

The single and double wave profiles each indicate the recommended operating range, including the maximum soldering temperature of 260°C. In practice, the maximum soldering temperature is quite often well below the above maximum profile.

We reserve the right to make technical changes.

Adressen weltweit

Let's connect.

AE	Vereinigte Arabische Emirate Weidmüller Middle East FZE Warehouse Q3-79 SAIF-Zone P.O. BOX 8591 Sharjah Telefonnummer +971 65572723 Faxnummer +971 65572724 wme.info@weidmuller.com	BH	Bahrain Khayber Trading Company P.O. Box 1976 Manama Telefonnummer +973 720747 Faxnummer +973 720331 khayber@batelco.com.bh	CO	Kolumbien Automatización Avanzada S. A. Carrera 97 No., 24 c - 23 Bodega 4 110911 Bogotá-D.C. Telefonnummer +57 (1) 547-8510 Faxnummer +57 (1) 422-3044 comercial@automatizacionavanzada.com www.automatizacionavanzada.com	ES	Spanien Weidmüller, S. A. Narcis Monturiol 11-13, Pol. Ind. Sudoeste 8960 Sant Just Desvern - Barcelona Telefonnummer +34 934 803 386 Faxnummer +34 933 718 055 weidmuller@weidmuller.es www.weidmuller.es	HU	Ungarn Weidmüller Kereskedelmi Kft. Budapest Gubacsi út 6. 1097 Telefonnummer +36 1 382 7700 Faxnummer +36 1 382 7701 info@weidmuller.hu www.weidmuller.hu
AO	Angola Bitte kontaktieren Sie Phambili Interface Südafrika	BR	Brasilien Weidmüller Conexel do Brasil Conexões Elétricas Ltda. Av. Presidente Juscelino, 642 - Piraporinha Diadema, São Paulo 09950-370 Telefonnummer +55 (11) 4366-9600 Faxnummer +55 (11) 4362-1677 vendas@weidmuller.com.br www.weidmuller.com.br	CR	Costa Rica ELVATRON S. A. la Uruca 400 Norte Banco Costa Rica San Jose Costa Rica Telefonnummer +506 2961-060 Faxnummer +506 5200-609 dirk.haase@elvatron.com www.elvatron.com	FI	Finnland Weidmüller Suomi, Weidmüller Aktiebolagetin siviliike Koy Plaza Vivace Äyritie 8C FI 1510 Vantaa Telefonnummer +358 20 7351300 Faxnummer +358 800 114 667 asiakaspalvelu@weidmuller.fi www.weidmuller.fi	ID	Indonesien PT. Nego Electrindo Ruko Mega Grosir Cempaka Mas Blok I No. 20 - 22 Jakarta 10640 Telefonnummer +62 21 42882255 Faxnummer +62 21 42882266 sales@negoelectrindo.co.id
AR	Argentinien CPI SA Bauness 2660 C1431DOF Buenos Aires Telefonnummer +54 11 4523 8008 Faxnummer +54 11 4522 0546 info@cpi.com.ar www.cpi.com.ar	BW	Botswana Bitte kontaktieren Sie Phambili Interface Südafrika	CZ	Tschechische Republik Weidmüller s.r.o. Lomnického 5/1705 140 00 Praha 4 Telefonnummer +420 244 001 400 Faxnummer +420 244 001 499 office@weidmuller.cz www.weidmuller.cz	FR	Frankreich Weidmüller E. U. R. L. 12, Chaussée Jules César BP 263 Osny 95523 Cergy-Pontoise Cedex Telefonnummer +33 1 34 24 55 00 Faxnummer +33 1 34 24 55 01 mail@weidmuller.fr	IE	Irland Bitte kontaktieren Sie Weidmüller Ltd. Großbritannien
AT	Österreich Weidmüller GmbH IZ NOE Süd Straße 2b, Obj M 59 2355 Wiener Neudorf Telefonnummer +43 2236 67080 Faxnummer +43 2236 6708-899 office.at@weidmuller.com www.weidmuller.com	BY	Weißrussland TECHNIKON Ltd. Nezavisimosti pr. 177-9 220125 Minsk Telefonnummer +375 17 393-11-77 Faxnummer +375 17 3930080 wm@technikon.by	DE	Deutschland Weidmüller GmbH & Co. KG Ohmstraße 9 32758 Detmold Postfach 30 54 32720 Detmold Telefonnummer +49 5231 1428-0 Faxnummer +49 5231 14-292083 weidmuller@weidmuller.de www.weidmuller.de	GB	Großbritannien Weidmüller Ltd. Klippon House Centurion Court Office Park, Meridian East, Meridian Business Park Leicester LE19 1TP Telefonnummer +44 116 282 3470 Faxnummer +44 116 289 3582 marketing@weidmuller.co.uk www.weidmuller.co.uk	IL	Israel A. U. Shay Ltd. 23/25, Embarr Street 49222 Petach-Tikva P.O. Box 1 00 49 49222 Petach-Tikva Telefonnummer +972 3-923-3601 Faxnummer +972 3-923-4601 shay@uriel-shay.com www.uriel-shay.com
AU	Australien Weidmüller Pty. Ltd. PO BOX 6944 Huntingwood 2148 Huntingwood Drive 43 Huntingwood NSW 2148 Telefonnummer +61 2 9671 9999 Faxnummer +61 2 9671 9911 info@weidmuller.com.au www.weidmuller.com.au	CA	Kanada W Interconnections Canada Inc. 10 Spy Court Markham Ontario L3R 5H6 Telefonnummer +1 (905) 475-1507 Ext. 9836 Faxnummer +1 (905) 475-2798 support@weidmuller.ca www.weidmuller.ca	DK	Dänemark Weidmüller Danmark Vallensbækvej 18A 2605 Brøndby Telefonnummer +45 27747800 kundeservice@weidmuller.dk www.weidmuller.dk	GE	Georgien Bitte kontaktieren Sie unser Representative Office Rashad Mahmudov Aserbaidschan.	IN	Indien Repräsentanz Büro Weidmüller Electronics India Pvt. Ltd. 12th Lane North Avenue, Opp Joggers Park, Kalyani Nagar, Pune 411 006 Telefonnummer +91 20-41290090 wmi.pune@weidmuller.in www.weidmuller.com
AZ	Aserbaidschan Repräsentanz Büro Rashad Mahmudov Demirchi Tower, 4th floor 37, Khojali ave. AZ 1025 Baku Telefonnummer +994 12 488 80 36 Faxnummer +994 12 488 80 37 rashad.mahmudov@weidmuller.com	CG	Kongo Bitte kontaktieren Sie Phambili Interface Südafrika	DZ	Algerien SARL INTER ELECTRIC 1a Angles des Rues Okba Ibn Nafaa et Hassi Beida 2300 Annaba Telefonnummer Faxnummer contact@inter-electric.com	GH	Ghana Bitte kontaktieren Sie Weidmüller Interface GmbH & Co. KG Südafrika	IS	Island Samey Automation Center Lýgass 13 210 Garoabær Telefonnummer +354 510 5200 Faxnummer +354 510 5201 Samey@samey.is www.samey.is
BA	Bosnien und Herzegowina Bitte kontaktieren Sie unser Representative Office Weidmüller Interface GmbH & Co. KG Serbien oder BIG electric d.o.o Mladena Stojanovića 117A 78000 Banja Luka Telefonnummer +387 51926277 Faxnummer +387 51926277 bigelectric@blic.net www.bigelectric.ba	CH	Schweiz Weidmüller Schweiz AG Rundbuckstraße 2 8212 Neuhausen am Rheinfall SH Telefonnummer +41 52 674 07 07 Faxnummer +41 52 674 07 08 info@weidmuller.ch www.weidmuller.ch	EC	Ecuador Elsystec S. A., Electricidad Sistemas y Tecnología Vasco de Contreras N35-251 y Mañosa Quito - Pichincha Telefonnummer +593 22456510 Faxnummer +593 22456755 Elsystec@uio.satnet.net	GR	Griechenland G.A. Solutions Ippokratous 11 Metamorfosi 144 52 Athen Telefonnummer +30 210 2823233 Faxnummer +30 210 2823233 info@weidmuller.gr www.weidmuller.gr	IT	Italien Weidmüller S. r.l. Via Albert Einstein 4 20092 Cinisello Balsamo Milano Telefonnummer +39 02 660681 Faxnummer +39 02 6124945 weidmuller@weidmuller.it www.weidmuller.it
BE	Belgien Weidmüller Benelux B. V. Mechelsesteenweg 519 bus 6 en 7 1930 Nossegem Telefonnummer +32 2 752 40 70 Faxnummer +32 2 751 36 06 info@weidmuller.be www.weidmuller.be	CL	Chile ATS - INTECH Maria Luisa Santander 0475 Santiago Providencia 7500859 Telefonnummer +56 2 341 1271 Faxnummer +56 2 341 1275 felipe@atsintech.com www.atsintech.com CPI CHILE LTDA Av. Presidente Frei Montalva 6001, 47 complejo el cortijo Santiago - Conchalí Telefonnummer +562 963 8440 Faxnummer +562 963 8440 cpi@cpichile.cl www.cpichile.cl	EE	Estland Bitte kontaktieren Sie unser Representative Office Weidmüller Interface GmbH & Co. KG Lettland oder Soots Interface OÜ Pärnu mnt 142 11317 Tallinn Telefonnummer +372 609 6933 Faxnummer info@sootsinterface.ee www.sootsinterface.ee	GT	Guatemala Prestelectro, Prestegard Electro, S.A. Avenida Petapa 44-22, Zona 12 Guatemala City Telefonnummer +502 2442-3346 Faxnummer +502 2476-8945 ventas@prestelectro.com	JM	Jamaika Bitte kontaktieren Sie W Interconnections Inc. USA
BG	Bulgarien Weid-Bul EOOD Bul. "Kliment Ohridski" 13 1756 Sofia Telefonnummer +359 2 963 2560 Faxnummer +359 2 963 1098 sofia@weidbul.com www.weidbul.com	CN	China Weidmüller Interface (Shanghai) Co. Ltd. 100 Yutong Road 25 F, BM Intercontinental Business Center 200070 Shanghai Telefonnummer +86 21-22195008 Faxnummer +86 512-68417505 customer.hotline@weidmuller.com.cn www.cnweidmuller.com	EG	Ägypten Standard Electric (OMEGA) 1, Abdelhamid Badawy Street Heliopolis Cairo Telefonnummer +202 21805111 Faxnummer +202 21805600 stdelec@rite.com	HK	Hong Kong Weidmüller (Hong Kong) Limited Co. Ltd. Unit 1617, Metropolis Tower No. 10 Metropolis Drive, Hunghom, Kowloon Telefonnummer +852 3154 8088 Faxnummer +852 31548099 Info-hk@weidmuller.com.hk	JO	Jordanien Trans Jordan for Electro PO Box 33 06 07 Amman Telefonnummer +962 6 533 2020 Faxnummer +962 6 533 5800 transjordan@batelco.jo
						HR	Kroatien ElektroPARTNER d.o.o. Slavonska avenija 24/6 HR-10000 Zagreb Telefonnummer +385 (1) 6184 793 Faxnummer +385 (1) 6184 795 elektropartner@zg.t-com.hr www.elektropartner.hr		



Let's connect.

Alle Weidmüller Adressen sowie Ihren lokalen Ansprechpartner finden Sie im Internet unter:
www.weidmueller.com/countries

Vertriebsgesellschaft

Auslandsvertretung

ohne Auslandsvertretung

JP Japan
Nihon Weidmüller Co. Ltd.
Sphere Tower Tennoz 2-2-8
Higashi-Shinagawa,
Shinagawa-ku
Tokyo
140-0002
Telefonnummer +81 3 6711
5300
Faxnummer +81 3 6711
5333
weidmullerjapan@weidmuller.co.jp
www.weidmuller.co.jp

KE Kenia
Bitte kontaktieren Sie
Phambili Interface
Südafrika

KR Korea
Weidmüller Korea Co. Ltd.
9th floor, Wonbang B/D
Samseong 2-Dong, Gangnam-
Gu
Seoul 143-42
5333
Faxnummer +82 2-516-0090
info@weidmuller.co.kr
www.weidmuller.co.kr

KW Kuwait
Kana Controls General Trading
& Contracting Co. W. L. L.
Al Rai Industrial Area, Plot
28-30, St. 31
13016 Safat
B.P. 25593
Telefonnummer +965
4741373
Faxnummer +965 4741537
info@kanacontrols.com

KZ Kasachstan
Bitte kontaktieren Sie
OOO Weidmüller
Russland

LB Libanon
Progress Engineering &
Trading Enterprises
Al Nahr Street
Beirut 11-1111
Telefonnummer +961 1
444 664
Faxnummer +961 1 561 880
progress@inco.com.lb

LT Litauen
Bitte kontaktieren Sie
unser Representative Office
Weidmüller Interface GmbH
& Co. KG
Lettland

oder

ELEKTROS IRANGA
Tinklu g. 29 a
LT-5319 Panevezys
Telefonnummer +370 (45)
582 828
Faxnummer
info@eliranga.lt

LU Luxemburg
Bitte kontaktieren Sie
Weidmüller Benelux B. V.
Niederlande

LV Lettland
SIA Abi4
Daugavgrivas 31b
Riga, LV-1007
Telefonnummer +371 674
70999
Faxnummer +371 676
24562
abi_4@tvnet.lv

Repräsentanz Büro
Weidmüller Interface GmbH
& Co. KG
Udens str. 12-118
Riga, LV-1007
Telefonnummer +371
29254766
Faxnummer +371 674
65637
ilgonis.rudaks@weidmueller.com
www.weidmueller.com

MA Marokko
Sofimed
137, Bd Moulay Ismail Roches
Noires
20290 Casablanca
Telefonnummer
Faxnummer
contact@sofimedmaroc.com

MD Moldawien
BERHORD A & D srl
79/1, str. Milescu Spartaru
MD-2075 Chisinau
Moldova
Telefonnummer +373 (22)
815002
Faxnummer +373 (22)
815007
atiuleanu@berhord.com
www.ad.berhord.com

ME Montenegro
Bitte kontaktieren Sie
unser Representative Office
Weidmüller Interface GmbH
& Co. KG
Serbien.

MG Madagaskar
Bitte kontaktieren Sie
Phambili Interface
Südafrika

MK Mazedonien
Bitte kontaktieren Sie
unser Representative Office
Weidmüller Interface GmbH
& Co. KG
Serbien

oder

ELEKTRO - SMK dooel
UL. III Makedonska brigada
b.b.
1000 Skopje
Telefonnummer +389
22460295
Faxnummer
Elektro-smk@telekabel.net.mk

MT Malta
E. S. S. Electrical Supplies &
Services Ltd.
San Gwakkin Road
Mriehel

Telefonnummer +356
21255777
Faxnummer +356 21255999
robert.agius@ess.com.mt

MU Mauritius
Mubelo Electrical Ltd.
Office 26, Gateway building,
St Jean Road
Quatre Bornes
Mauritius
Telefonnummer +230
4670989
Faxnummer +230 4654051
richard.mubelo@orange.mu

MW Malawi
Bitte kontaktieren Sie
Phambili Interface
Südafrika

MX Mexiko
W Interconnections S. A.
DE C. V.
Blvd. Hermanos Serdán 698,
Col. San Rafael Oriente
72029 Puebla
Telefonnummer +52 (222)
268 6227
Faxnummer +52 (222) 286
6242
clientes@weidmuller.com.mx

MY Malaysia
Connect Plus Technology
Sdn Bhd
No. 43, Jalan PJS 11/22,
Bandar Sunway
46150 Petaling Jaya
Selangor Darul Ehsan
Telefonnummer +60 3 5633
7363
Faxnummer +60 3 5633
6562
paul@cptech.com.my
www.cptech.com.my

MZ Mosambik
Bitte kontaktieren Sie
Phambili Interface
Südafrika

NA Namibia
Bitte kontaktieren Sie
Phambili Interface
Südafrika

NG Nigeria
Bitte kontaktieren Sie
Weidmüller Interface GmbH
& Co. KG
Südafrika

NL Niederlande
Weidmüller Benelux B. V.
Franciscusweg 221
1216 SE Hilversum
Postfach 1505
1200 BM Hilversum
Telefonnummer +31 35 626
12 61
Faxnummer +31 35 623
20 44
info@weidmuller.nl
www.weidmuller.nl

NO Norwegen
Sivilingenior J.F. Knudtzen AS
Billingstadstadsletta 97
1396 Billingstad
PO Box 160
1378 Nesbru
Telefonnummer +47 66 98
33 50
Faxnummer +47 66 98 09 55
firmapost@fknudtzen.no
www.fknudtzen.no

NZ Neuseeland
Cuthbert S. Steward Ltd.
27 Te Puni Street
Petone
PO Box 38496
Wellington Mail Centre 5054
Telefonnummer (04) 568
6156
Faxnummer (09) 489 1752
cs@cutbertstewart.co.nz

Cuthbert S. Steward Ltd
4 Fred Thomas Drive
Aon Building, Ground Floor,
South Entry
Takapuna
PO Box 100 338
North Shore City 745
Telefonnummer (09) 489
1751
Faxnummer (04) 568 6056
cs@cutbertstewart.co.nz

OM Oman
DAN INTERNATIONAL LLC.
Ghala St. 111
BP 2901
Seeb
Telefonnummer +968
5036 77
Faxnummer +968 5037 55
yedu@danintl.com

PE Peru
IMPEXINCA S.A.C.
Calle Ortiz de Zevallos No.
105, Urb. San Antonio
18
Lima, Miraflores
Telefonnummer +51 1 447
5608
info@impexinca.pe
www.impexinca.pe

J & W CIA. S. A.
Calle 6 Mz. D Lte. 23, Urb.
Ind. Grimanesa
01
Callao
Telefonnummer +51 1 572
2539
Faxnummer +51 1 572 0152
contacto@jwcia.com
www.jwcia.com

PH Philippinen
Enclosure Systems Specialists
Inc.
2276 Don Chino Roces
Avenue Extension
Room 103/105 Narra Building
1231 Makati City
Telefonnummer +63 2 813
8580
Faxnummer +63 2 813 8596
sales_encsys@pltdsl.net
www.enclosuresystemsph.com

PK Pakistan
Automation Controls (Pak)
Apartment No. 33 C III,
Chenab Block, Allama Iqbal
Town
Lahore
Telefonnummer +92 42
37809948
Faxnummer +92 42
37809950
nadeem@acpak.com.pk
www.acpak.com.pk

PL Polen
Weidmüller Sp. z o. o.
ul. Ogrodowa 58
00-876 Warszawa
Telefonnummer +48 22 510
09 40
Faxnummer +48 22 510
09 41
biuro@weidmuller.com.pl
www.weidmuller.pl

PR Puerto Rico
Bitte kontaktieren Sie
W Interconnections Inc.
USA

PT Portugal
Weidmüller Sistemas de
Interface S. A.
Estrada Outeiro Polima, R.
Augusto Dias da Silva, Lote
B - Esc. 2
São Domingos de Rana
2785-515 Abóboda
Telefonnummer +351 214
459 191
Faxnummer +351 214
455 871
weidmuller@weidmuller.pt
www.weidmuller.pt

PY Paraguay
Bitte kontaktieren Sie
CPI SA
Argentinien

QA Katar
Doha Motors
PO Box 145

Telefonnummer +974
4651441
Faxnummer +974 4654579
dmtctech@qatar.net.qa
<http://www.dohamotorsgroup.com/td.html>

Petroleum Technology Co.
W.L.L.
PO Box 16069
5th Floor Toyota tower
Telefonnummer +974
44419603
Faxnummer +974 44419604
petrotec@qatar.net.qa
www.petrotec.com.qa

RO Rumänien
Repräsentanz Büro
Weidmüller Interface GmbH
& Co. KG
Ionescu Crum Street, No.
1, 1st Tower, 1st Floor,
Office 4
500446 Brasov - Brasov
Business Park
Telefonnummer +40 (268)
446 222
Faxnummer +40 (262)
205 410
claudiu.totea@weidmueller.com
www.weidmueller.com

RS Serbien
Repräsentanz Büro
Weidmüller Interface GmbH
& Co. KG
Ustanicka 189, III sprat
lokal 7a
11050 Beograd
Telefonnummer +381
112885274
Faxnummer +381
112885274
zoran.rabrenovic@weidmueller.com

TeLa Elektrik d.o.o.
Ul. Dr. Drage Ljočić 6
Beograd
Telefonnummer +381 11
2772 415
Faxnummer +381 11 2772
850
office@tela.rs
www.tela.rs

RU Russland
OOO Weidmüller
Warshavskoye highway, 25
A. bld. 6
Moskau
117105
Telefonnummer +7 (495)
771-69-40
Faxnummer +7 (495) 771-
69-41
Info@weidmueller.ru
www.weidmueller.ru

SA Saudi-Arabien
Al Abdulkarim Holding Co.
P.O. Box 4
Dammam 31411
Telefonnummer +966 3
8337110
Faxnummer +966 3
8829547
E-Mail salehsk@akh.com.sa
www.weidmueller.ae

Saudi Electric Supply
Company (SESCO)
P.O. Box 32 98
Al Khobar 31952
Telefonnummer +966 3
8829546 Ext. 3030
Faxnummer
www.sesco-gex.com

SE Schweden
Weidmüller AB
Axel Danielssons väg 271
BOX 31025
SE-200 49 Malmö
Telefonnummer +46 77-143
00 44
Faxnummer +46 40-37 48 60
info@weidmuller.se
www.weidmuller.se

SG Singapur
Weidmüller Pte. Ltd.
70 Bendemeer Road
04-03 Luzerne Building
Singapore 339940
Telefonnummer +65 6841
5311
Faxnummer +65 6841 5377
info@weidmuller.com.sg
www.weidmuller.com.sg

SI Slowenien
Elektrospoji d. o. o.
Stegne 27
SI- 1000 Ljubljana
Osrednjeslovenska
Telefonnummer +386 1 511
3810
Faxnummer +386 1 511
1604
info@elektrospoji.si
www.elektrospoji.si

SK Slowakei
ELEKTRIS s.r.o.
Elektrárnská 1
831 04 Bratislava
Telefonnummer +421 2/4920
0113
Faxnummer +421 2/4920
0119
bratislava@elektris.sk

SV El Salvador
Prestegard Electro
11 Avenida Norte No. 240
Edificio Salazar No. 2
San Salvador
Telefonnummer +503 2271
1690
Faxnummer +503 2221
3851
prestegard@navegante.com.sv

SY Syrien
Bitte kontaktieren Sie
Weidmüller Middle East FZE
Vereinigte Arabische Emirate

SZ Swasiland
Bitte kontaktieren Sie
Phambili Interface
Südafrika

Adressen weltweit

Let's connect.

TH Thailand
Pisanu Engineering Co. Ltd.
Kwang Dingaeng, Khet
Dingaeng
800/2 Soi Trakulsuk, Asoke-
dindaeng Road
Dindaeng, Bangkok
10400
Telefonnummer +66 2 248
2896
Faxnummer +662 105 6301
ecsales@pisanu.co.th
www.pisanu.co.th

Repräsentanz Büro
Weidmüller Pte. Ltd.
37/F, Sathorn Square Building
98 North Sathorn Road
Bangkok, Silom Bangrak
10500
Telefonnummer +66 2 105
6300
Faxnummer +66 2 642 9220
info@weidmuller.com.sg

TN Tunesien
Bitte kontaktieren Sie
Weidmüller E. U. R. L.
Frankreich

TR Türkei
Weidmüller Elektronik Ticaret
Ltd. Sirketi
Kavacak Mah. Orhan Veli Kanik
Caddesi 9/1
34810 Beykoz / Istanbul
Telefonnummer +90 (216)
537 10 70
Faxnummer +90 (216) 537
10 77
info@weidmuller.com.tr
www.weidmuller.com.tr

TW Taiwan
Weidmüller (Hong Kong)
Limited
No. 3, Lane 89, ChungYang
N. Rd
24148 SanChuang City,
Taipei
Telefonnummer +886 921
949 751
roy.lin@weidmueller.com.hk

TZ Tansania
Bitte kontaktieren Sie
Phambili Interface
Südafrika

UA Ukraine
LLC WM UKRAINE
Levanevskogo str. 6
Kiev
3058
Telefonnummer +38 044
490 32 48
Faxnummer
info@wm-ua.com.ua
wm-ua.com.ua/
Repräsentanz Büro
Weidmüller Interface GmbH
& Co. KG
Z, office 303
7-D, Zdolbunivska str.
Kiev, 2081
Telefonnummer (Mobil) +38
050 440 25 24
info.ua@weidmueller.com

US USA
W Interconnections Inc.
821 Southlake Boulevard
Richmond Virginia 23236
Telefonnummer +1 (804)
794-2877
Faxnummer +1 (804) 379-
2593
info@weidmuller.com
www.weidmuller.com

UY Uruguay
REWO Uruguay S. A.
AV. Bolivia 2001 Esq
Rocafuerte
11300 Carrasco Montevideo
Telefonnummer +598 2604
8439
Faxnummer +598 2604
8439
rewo@rewouruguay.com.uy

UZ Usbekistan
Bitte kontaktieren Sie
OOO Weidmüller
Russland

VE Venezuela
Somerinca C. A.
Corazon de Jesus - 3ra
Transversal con calle el
Carmen- Los Dos Caminos
Caracas 1070-A
Telefonnummer +58
2122352748
Faxnummer +58
2122399341
klocmoeller@cantv.net
www.somerinca.com

VN Vietnam
AUMI Industrial Equipment &
Automation Company Limited
E1, La Thanh Hotel
218 Doi Can Street
Lieu Giai Ward, Ba Dinh
District
Hanoi City
Telefonnummer +84 4
37628601
Faxnummer +84 4
62661391
aumi@aumi.com.vn
www.aumi.com.vn

Repräsentanz Büro
Weidmüller Pte. Ltd.
Level 16 Saigon Tower
Building
29 Le Duan Street
District 1
Ho Chi Minh
Telefonnummer +848 3520
7717
Faxnummer +848 3520
7604
info@weidmuller.com.sg

ZA Südafrika
Phambili Interface
PO Box 193
1609 Johannesburg, Edenvale
5 Bundo Road, Sebenza
1610 Johannesburg
Telefonnummer +27 (11)
4521930
Faxnummer
info@weidmuller.co.za
www.weidmuller.co.za

Repräsentanz Büro
Weidmüller Interface GmbH
& Co. KG
210 Amarand
Avenue, Pegasus Building
181 Pretoria, waterkloof Glen
ext 2 -
Telefonnummer +27 12 003
2906
Faxnummer +27 (11)
4526455
Jacques.Vosloo@weidmueller.
com
www.weidmueller.com

ZM Sambia
Bitte kontaktieren Sie
Phambili Interface
Südafrika

ZW Simbabwe
Bitte kontaktieren Sie
Phambili Interface
Südafrika

