

PoE Splitter Adapter

Power over Ethernet

PART NUMBER	DESCRIPTION
POE-22001T	Power over Ethernet Splitter Adapter

Specifications

Standard:

IEEE802.3 10Base-T
IEEE802.3u 100Base-TX
IEEE802.3af Power over Ethernet

Power Jack Diameter:

5.5 x 2.0mm, 5.5 x 2.5mm

DIP:

DIP 5V, 7.5V, 9V, and 12V

Connector:

Data and Power In: 1 x RJ-45, Data pin 1,2,3,6

Power Pin:

4,5(V+), 7,8(V-) and 1,2(V+), 3,6(V-)

Data Out:

1 x RJ-45, Data pin 1,2,3,6

Power Out:

5V, 7.5V, 9V, and 12V (2A@5V, Maximum)

Network Cable:

10Base-T: 4-pair UTP/STP Category 3/5e/6 cable,
EIA/TIA-568 100-ohm (up to 100m)
100Base-TX: 4-pair UTP/STP Category 5e/6 cable, EIA/TIA-
568 100-ohm (up to 100m)

LED:

System: power (green)

Power Input:

DC 48V

Operating Environment:

0° ~ 40°C (32° ~ 104°F), 90% Humidity (non-condensing)

Dimension:

80mm x 55mm x 26mm (L x W x H) 3.5" X 2.16"
X1.06"

EMI & Safety:

FCC Class B, CE, CE/EN60950



908 Canada Court
City of Industry, CA 91748 U.S.A.
Phone: 626.964.7873 or 800.346.6668 **Fax:** 626.964.7880
www.unicomlink.com e-mail: info@unicomlink.com

©UNICOM 2007. UNICOM is a trademark of UNICOM Electric, Inc. All rights reserved.
Specifications subject to change without notice.