

REV. H

Do not scale
from this print

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES ARE:	TITLE:	DWG NO:
ONE PLACE DECIMALS $\pm .1$ [3]	THREE PLACE DECIMALS $\pm .005$ [.13]		ANGLES $\pm 2^\circ$	.100 [2.54] C.L. SHUNT STRIP ASSEMBLY	MNT-1XX-XX-X
TWO PLACE DECIMALS $\pm .01$ [2.5]	FOUR PLACE DECIMALS $\pm .0020$ [.051]				SHEET 1 OF 1

MNT-1XX-XX-X

NO. OF POSITIONS
01 THRU 20


PLATING SPECIFICATION

-T = TIN: SPECIFY -T IN CONTACT SUFFIX -X
 -G = GOLD: SPECIFY -G IN CONTACT SUFFIX -X
 -H = HEAVY GOLD: SPECIFY -H IN CONTACT SUFFIX -X





COLOR SPECIFICATION

SPECIFY COLOR IN BODY SUFFIX -XX

BK = BLACK
 RD = RED
 BL = BLUE
 YW = YELLOW
 OR = ORANGE



SEE NOTE 3



NOTES:

- MULTI-CUT WIDTH TOLERANCED TO $\pm .005$ [.13]
 $\pm .015$ [.38]
 ROTO-CUT WIDTH TOLERANCED TO $\pm .010$ [.25].
- MIN. RETENTION 24 oz.
- ENDWALL AFTER CUTTING $.0245+/- .010$ [.622+/- .25].

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
 CONFIDENTIAL AND PROPRIETARY TO
 SAMTEC INC. AND SHALL NOT BE
 REPRODUCED OR TRANSFERRED TO
 OTHER DOCUMENTS OR DISCLOSED TO
 OTHERS OR USED FOR ANY PURPOSE
 OTHER THAN THAT FOR WHICH IT WAS
 OBTAINED WITHOUT THE EXPRESSED
 WRITTEN CONSENT OF SAMTEC INC.

BODY: USE MNT-100-XX
 CONTACT: USE C-37-X

samtec

MISC/MKTG
MNT-MKT

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
 PHONE (812) 944-6733 P.O. BOX 1147
 CODE 55322

MADE BY: KOLB 2-20-89
 CHECKED BY: McCARTIN

ENG.
 APPROVAL
 D.E.M.

MNT-1XX-XX-X
 SHEET 1 OF 1