


Brt Metal Test Clips

13AC120, 13AC121, 13AC122, 13AC123, 13AC124

KOBICONN

Brt Metal Test Clips

13AC120, 13AC121, 13AC122, 13AC123, 13AC124



Dimensions: mm (In.)

Mouser Stock No.	Description
13AC120	Miniature Alligator Clip, Less Cover
13AC121	Red Cover Only
13AC122	Black Cover Only
13AC123	Green Cover only
13AC124	Yellow Cover Only

SPECIFICATIONS	
Jaw Spread:	8mm Max.
Breakdown Voltage:	2000VAC for 1 Minute
Insulating Temperature Max.:	100°C, 10 hrs
Insulating Temperature Min.:	-20°C, 10 hrs
Extension:	1.2 ~ 1.5 kg/mm²
Water Absorption:	0.5% WF
Insulation Resistance:	100MΩ @ 500VDC

Date Last Revised: 10-24-05

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300802

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[13AC124](#) [13AC120](#) [13AC122](#) [13AC121](#)

Other:

[13AC123](#)